

electronic pocket Vernier callipers

IP67

ATORN

Application

For measuring external, internal, step and depth dimensions.

Version

- ON/OFF
- Zero setting at any position
- mm/inch changeover
- AUTO OFF
- ABS function
- Protection rating: IP67
- Keeptronic system
- High-contrast display

Advantage

- key lock to prevent unintentional adjustment
- Simple and reliable measurement reading thanks to large and high-contrast display
- Switched on using the ON button or automatically switched on by calliper movement

Delivery

In a case, with battery (1 x 3 V lithium, type CR 2032)



Art. no.	31173 204
Min./max. length measuring range	0-150 mm
Data transmission type	No
Depth gauge rod	Round
IP protection class	IP 67
Length of jaw	40 mm
Digit height	11 mm
Length of cross tips	16 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Depth gauge rod thickness	1.5 mm
Type of locating	With locking screw
Preset function	Yes
Calibration Group	A
ISO	13385-1

EAN-Code

405029366855 1