

Product information

90 31 02 SB

KNIPEX TubiX® Pipe cutter



Faster, easier and more precise: cuts copper, brass and stainless steel pipes

- QuickLock one-hand locking mechanism: independent holding and clamping on the tube
- Easy one-handed pushing for quick adjustment to different tube sizes
- Comfortable: easy cutting due to high-quality needle bearings in the cutting wheel and guide rolls
- Cuts pipes from Ø 6 - 35 mm (1/4" - 1 3/8") with wall thickness up to 2 mm
- Cutting wheel made of high-grade ball-bearing steel
- Practical quick replace system for the cutting wheel – with spare wheel stored under the feeding barrel
- With precision-ground deburring tool, easy to remove
- For the electric trade: Also suitable to cut rigid steel conduits
- Light and durable metal enclosure of magnesium



General	
Article No.	90 31 02 SB
EAN	4003773084686
Weight	375 g
Dimensions	180 x 65 x 40 mm
Reach	no
RohS	no
Technical details	
Cutting capacities (diameter)	Ø 6 – 35 mm
Cutting capacities (diameter)	Ø 1/4 – 1 3/8 Inch
Classification	
eCl@ss 5.1.4	21040601
ETIM 5.0	EC000148
ETIM 6.0	EC000148
proficl@ss 6.0	AAB927c006
Spare Parts	
90 39 02 V01	Cutting wheel INOX Cu for 90 31 02,
90 39 02 V02	Deburring tool for 90 31 02,
90 39 02 V03	5 x Spare cutting wheel INOX Cu for KNIPEX TubiX® 90 31 02,

technical change and errors excepted









