

## Electronic quick probe for internal measurements

For measuring bores, recesses and internal grooves

Kroepflin  
Längenmesstechnik

### Application:

For measuring bores, recesses and internal grooves.

### Execution:

- Large, high-contrast LCD display (digit size 8.5 mm)
- Combined digit and scale display
- mm/inch switch-over
- Measuring mode ABSOLUTE
- Measured value classification (red/green display)
- 1 fixed and 1 movable measuring arm
- Digital version: Scale interval can be switched: 0.001/0.002/0.005/0.01/0.02/0.05 mm

### Advantage:

- Measured result can be read directly

### Delivery:

With traceable test certificate in box



<b>Art. no.</b>	<b>33261 071</b>
<b>Brand</b>	KROEPLIN
<b>Manufacturer Part Number</b>	L220
<b>IP protection class</b>	IP 67
<b>Min./max. length measuring range</b>	20-40 mm
<b>Digit increment</b>	0.01 mm
<b>Display</b>	Digital
<b>Measuring depth</b>	85 mm
<b>Type</b>	L220
<b>Measuring arrangement</b>	4
<b>Measuring contact length movable</b>	7.3 mm
<b>Measuring contact length fixed</b>	7.3 mm
<b>Number of rechargeable batteries/batteries</b>	2 PCS
<b>Battery designation</b>	Micro AAA; R03; UM4
<b>Gross Weight</b>	0.270 kg
<b>Product Group</b>	332