

Slides DZ 0522, Width 26.5 mm, to 180 kg, Over Extension

Material:

Slide elements: Cold-rolled steel, bright zinc-plated.

Ball retainers: Cold-rolled steel, zinc-plated.

Balls: Hardened steel.


Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Heavy-duty construction.
- Shock blocks offering protection against shock and vibration.
- Protective shroud prevents excessive contamination of the ball tracks.
- Mounting plates on inner and outer members.
- Service life 10,000 cycles (to 140 kg up to 40,000 cycles).
- Temperature range: -20°C to +110°C.

Ordering details: e.g.: Prod. No. 649 058 59, Slides DZ 0522



Accuride



* For slide length 900 mm there are 4 holes with distance A.

Product No. per Pair	Slide Length mm	Travel +/-3.2 mm	A mm	Overall Length mm	Load Rating per Pair kg	Weight per Pair kg
649 058 59	457	534	194,0	481	180	9,74
649 058 61	600	625	265,0	624	180	12,68
649 058 62	900	907	276,5	924	150	19,24

Note

Recommended mount: M6 screws on the inner, extending member, M8 screws on the outer fixed member.

Use all mounting positions to achieve the max. load rating. The cabinet and drawer must be designed to minimise any deflection and torsion of the slide.

Overall length = slide length + 24 mm.

Selection Tool
on the Internet at www.maedler.de
in the section **MÄDLER®-Tools**