

HSSE Co 5 narrow disc milling cutter

Type N

ORION[®]

Application:

For slot milling and cutting

Version:

- Type D
- Coarse cross-toothing
- Cutting on 3 sides
- Bore with longitudinal groove to DIN 138



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	27	22	17	20	11	195	195	160	170	30	30	183		23	18	18	10		

Art. no.	14105 395
Type	N
Number of cutting edges	24 PCS
Milling cutter design standard	DIN 1834
Cutting edge diameter	100 mm
Bore diameter	32 mm
Width of cutting edge	4 mm
fz steel 700	0.04 mm

EAN-Code

4053625035311