




www.weka-holzbau.com



## Gartenhaus










123.3021.40001  
123.3021.43001  
123.3021.45001  
123.3021.46001








123.3024.40001  
123.3024.43001  
123.3024.45001  
123.3024.46001









123.3030.40001  
123.3030.43001  
123.3030.45001  
123.3030.46001



## Montage-, Bedienungs- und Wartungsanleitung















Pos	Bild	Abmessung ( mm )	Anzahl ( Stück)		
			123.3021.4x0001	123.3024.4x0001	123.3030.4x0001
1	R002.0650.2050 R002.0650.2350 R002.0650.2950 	40/60/2050 40/60/2350 40/60/2950	6 - -	- 6 -	- - 6
2	R002.0350.2350 R002.0350.2700 R002.0350.3200 	45/146/2350 45/146/2700 45/146/3200	1 - -	- 1 -	- - 1
3	R002.0091.2950 	15,5/96/2950	23	26	33
4	R002.0091.1962 	15,5/96/1962	54	60	72
5	R002.0530.1775 	15/45/1775	3	4	4
6	R002.0425.1950 R010.0425.1950 	18,5/70/1950	8	8	8
7	G100.07.0070 G100.07.1020 	18,5/146/2050	4	4	4



Pos	Bild	Abmessung ( mm )	Anzahl ( Stück)		
			123.3021.4x0001	123.3024.4x0001	123.3030.4x0001
8		18,5/176/260	2	2	2
9		40/40/1930	4	4	4
10		28/564/2950	2	2	2
11		28/121/2950	16	16	16
12		28/121/2050 28/121/2350 28/121/2950	32 - -	- 32 -	- - 32
13		28/121/2350 28/121/2700 28/121/3200	2 - -	- 2 -	- - 2
14		28/63/2950	2	2	2

Pos	Bild	Abmessung ( mm )	Anzahl ( Stück)		
			123.3021.4x0001	123.3024.4x0001	123.3030.4x0001
15	R002.0035.0443 R208.0035.0443 R211.0035.0443 R212.0035.0443 	28/121/443	32	32	32
16	R002.0035.1572 R208.0035.1572 R211.0035.1572 R212.0035.1572 	28/121/1572	9	9	9
17	B100.12.2370 B100.12.2330 B100.12.2350 E100.12.0002 	60/965/1810	1	1	1
18	B100.11.1170 	52/692/795	1	1	1
19	R002.0181.1805 	15/28/1805	3	3	3
20	B100.03.0062 B100.03.1062 	35/60/990	1	1	1
21	G126.10.0031 	18,5/45/880	1	1	1
22	G100.01.0006 	15/25/710	1	1	1


Pos	Bild	Abmessung ( mm )	Anzahl ( Stück)		
			123.3021.4x0001	123.3024.4x0001	123.3030.4x0001
23	G100.01.0006 	15/25/990	1	1	1
24	-	-	-	-	-
25	G105.01.0006 	28/60/300	4	4	4

M100.101		Abmessung ( mm )	Anzahl ( Stück )		
			123.3021.4x0001	123.3024.4x0001	123.3030.4x0001
Pos	Bild				
M1	K001.8050.0004 	5,0 x 80	20	20	20
M2	K001.6040.0004 	4,0 x 60	350	350	350
M3	K001.4040.0004 	4,0 x 40	150	150	150
M4	K001.3030.0004 	3,0 x 30	30	30	30
M5	K002.2050.0004 	5,0 x 20	24	24	24
M6	K010.5022.0001 	2,2 x 55	700	700	700
M7	K011.1320.0001 	2,0 x 13	600	600	600
M8	K075.2100.0002 	32/32/170	2	2	2


M100.034		Abmessung ( mm )	Anzahl ( Stück)		
			123.3021.4x001	123.3024.4x001	123.3030.4x001
Pos	Bild				
M9	K001.4040.0004 	4,0 x 40	26	26	26
M10	K010.3016.0001 	1,6 x 30	16	16	16
M11	K036.3135.0001 	0/0/65	1	1	1
M12	K045.1270.0001 		1	1	1

M100.032		Abmessung ( mm )	Anzahl ( Stück)		
			123.3021.4x001	123.3024.4x001	123.3030.4x001
Pos	Bild				
M13	K001.4040.0004 	4,0 x 40	8	8	8
M14	K046.2860.0006 		1	1	1


1.



2.




3.








1





2

	M1 5,0 x 80
	M2 4,0 x 60




**3**


	M6 2,2 x 55



**A-A**







**B-B**









5




6


	M1	5,0 x 80
	M2	4,0 x 60












7




8




9





A=A



10





11






12







	M6	2,2 x 55




13





∅3mm




14


	M3 4,0 x 40
--	-------------




15





16



	M13 4,0 x 40
---	--------------



17





18








19




20




21


	M9	4,0 x 40






22



23

	M3	4,0 x 40













[www.weka-holzbau.com](http://www.weka-holzbau.com)

## **WEKA Holzbau GmbH**

Johannesstr. 16, 17036 Neubrandenburg

Tel.: +49 (0)395 42908-0

Fax: +49 (0)395 42908-83

Mail: [info@weka-holzbau.com](mailto:info@weka-holzbau.com)

Web: [www.weka-holzbau.com](http://www.weka-holzbau.com)

© Copyright HRB 3662  
MA Art.-Nr.: 800.0286.18.44