



5: EMC / HF Gaskets

5.1.3 HF Gaskets (A)



5.1.3.1 HF Gaskets (A)

- D-shaped
- Polyurethane foam core
- Conductive fabric (Ni+Cu plated)
- Self-adhesive




Width		Thickness		Length		Packing Units	Part-No.
mm	inch	mm	inch	mm	inch		
6.35	0.25	3.56	0.14	142.5	5.6	1 pc.	7820-90
				245.0	9.65	1 pc.	7820-91
				88.0	3.46	1 pc.	7820-92

5.1.4 EMC Gaskets (B) Stainless Steel




5.1.4 EMC Gasket (A and B)

- Stainless steel



For size	Length		Part-No.
	mm	inch	
2 U	57.15	2.25	81-062-02
3 U	101.6	4.00	81-062-03
4 U	146.05	5.75	81-062-04
6 U	234.95	9.25	81-062-06
7 U	279.4	11.00	81-062-07
8 U	323.85	12.75	81-062-08
9 U	368.3	14.50	81-062-09

5.1.5 EMC Gaskets (B) Foam Core



5.1.5 EMC-Gaskets (B)

- Polyurethane foam core
- Conductive fabric (Ni+Cu plated)
- Self-adhesive

Description	Part-No.
EMC-gasket rectangular. 2.0 x 7 mm, L = 300 mm	7820-95
EMC-gasket triangular. 2.3 x 10 mm, L = 300 mm	7821-300
EMC-gasket triangular. 2.3 x 10 mm, L = 2000 mm	7821-2000