

## Product information


# 35 42 115 ESD

## Electronics Pliers ESD

DIN ISO 9655 DIN EN 61 340-5



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Handles with two-colour multi-component grips black/grey
- 45° bent, half-round jaws
- Ball bearing chrome steel, oil hardened




### General

Article No.	35 42 115 ESD
EAN	4003773024866
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 65 x 17 mm
Standard	DIN ISO 9655 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Jaw length (B)	22.5 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	2.0 mm
Tips thickness (F)	1.5 mm
Head width (A)	11.0 mm
Dimensions angle	45 °
ESD	yes



technical change and errors excepted

