

GROUND CLAMP

Description

200A SHEET WEIGHT CLAMP . Max intensity. At 35%: 200A. Weight: 220 g • Cable: 25 mm² . Light and economical model. With shunt. . 400A SHEET GROUND CLAMP . Max intensity. At 35%: 400A. Weight: 360 g • Cable: 70 mm² . Light and economical model. With shunt. . 350A BRASS ALLIGATOR GROUND CLAMP . Max intensity. At 35%: 350A. Weight: 400 g • Cable: 50 mm² . Large contact surface. Small footprint. . 600A BRASS ALLIGATOR GROUND CLAMP . Max intensity. At 35%: 600A. Weight: 640 g • Cable: 95 mm² . Large contact surface. Small footprint. . 300A SPRING GROUND CLAMP . Max intensity. At 35%: 300A. Weight: 460 g • Cable: 50 mm² . Brass body. Very effective clamping. . GROUND GASKET CLAMP 500A . Max intensity. At 35%: 500A. Weight: 760 g • Cable: 95 mm² . High clamping power/ Cable fixing by screw.



Characteristics

Ref.	EAN	Type	Max intensity A	Material	Model	Cable diameter mm ²
853778	3660338097874	Earth clamp	200	Sheet metal	Sheet metal ground clamp 200A	25