

Product information

90 31 02 SB

KNIPEX TubiX® Pipe cutter



- QuickLock one-hand locking mechanism: independent holding and clamping on the tube
- Easy one-handed pushing for quick adjustment to different tube sizes
- Comfortable: easy cutting due to high-quality needle bearings in the cutting wheel and guide rolls
- Cuts pipes from Ø 6 - 35 mm (1/4" - 1 3/8") with wall thickness up to 2 mm
- Cutting wheel made of high-grade ball-bearing steel
- Quick replacement of the cutting wheel without any tools — spare cutting wheel stored in the handle
- Removable, precision-ground deburring tool
- For the electric trade: Also suitable to cut rigid steel conduits
- Light and durable metal housing of magnesium



General

Article No.	90 31 02 SB
EAN	4003773084686
Weight	375 g
Dimensions	180 x 65 x 40 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities (diameter)	Ø 6 – 35 mm
Cutting capacities (diameter)	Ø 1/4 – 1 3/8 Inch

technical change and errors excepted











