

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 745
Brand	AMF
Manufacturer Part Number	85803
DIN	787
Thread dimension	M20
Groove width	20 mm
Length excluding head	160 mm
Outer diameter	19.7 mm
Thread length	110 mm
Length of head	32 mm
Head height	12 mm
Gross Weight	0.614 kg
Product Group	260

EAN

4020772085803