


Inverto Direct/Indirect *Inverto Dir/Ind NW Eb Black* 3080037



Product features

- Surface Wall mounted direct / indirect luminaire, wire to base with pluggable connection for easy installation, suitable for looping, black coloured aluminium housing, 3233lm (2 x 1616lm), 30W, 107lm/W, 4000K, 350mA, CRI:80, 40° beam Angle, non-dimmable, IP65, IK07, lifespan: 60,000hrs (L80:B20), 23.00x32.2x11.5mm.




PRODUCT OVERVIEW

Product name	Inverto Dir/Ind NW Eb Black
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted
Environment	Internal/External
General application	Hospitality
ETIM Class	EC002892
E-number SE	7702875
Warranty	5 years
Fixture luminous flux (lm)	3233
Luminaire efficacy (lm/W)	107
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Consistency (SDCM)	3
Beam Angle (°)	40
Photobiological Risk Group	RG1
Total power consumption (W)	30
Electrical protection	Class II
Control gear type	Electronic ballast
Dimmable	No
Dimming method	N/A
Housing colour	RAL 9005 - Jet black
IP rating	IP65
IK rating	IK07
Product EAN number	8711971800378

PHOTOMETRY

Inverto Direct/Indirect *Inverto Dir/Ind NW Eb Black* 3080037



TECHNICAL DRAWINGS

