

Pneumatic impact screwdriver 9012 M-1



Application:

For heavy-duty screw-driving tasks.

Execution:

- 3 power levels in clockwise rotation, 1 power level in anti-clockwise rotation
- Exhaust air discharged downwards through the handle
- Thermally insulated handle

Advantage:

- One-handed operation for left-handed and right-handed users
- Ultra compact design optimised for working in confined spaces

Delivery:

Includes coupling plug



Art. no.	75065 016
Brand	HAZET
Manufacturer Part Number	9012M-1
Model	9012M-1
Suitable for screw	M16
Max. tightening torque	678 Nm
Max. releasing torque	1200 Nm
Max. idle speed	8800 rpm
Air consumption	127 l/min
Tool holding device	1/2-inch external square
Hammer mechanism system	Jumbo hammer mechanism
Length	80 mm
Connection thread	G 1/4 inch
Inner hose diameter	10 mm
Operating pressure	6.3 bar
Sound-pressure level	92.2
Weight	1.27 kg
With right/left-hand rotation	Yes
Gross Weight	1.592 kg
Product Group	738

EAN

4000896218356