



**NOTE:**

**1. Electrical test:**

- (1). 100% open short & miss wire test
- (2). Insulation resistance: DC 100V 0.01S 5M ohm
- (3). Contactor resistance: 2 ohm Max.
- (4). Mac book pro + LG Monitor TEST: 3840\*2160@60Hz
- (5). Transmission rate : 10Gbps Current rate: 5A
- (6). Supports USB power delivery 3.1 (EPR 48V 5A) 240W

**2. ROHS & REACH COMPLIANT**

**3. PRINTING: SUPER HIGH SPEED USB Revision 3.2**

**MATERIAL LIST:**

⑤	OUT MOLD	PVC Mouldling	2	
④	INNER MOLD	LD-PE	2	
③	E-mark	GEN2*2 20Gbps 5A	1	
②	TYPE C	USB C/M SOLDER TYPE, BLACK PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING+IRON SHIELD	2	
①	CABLE	USB 3.2 CABLE [32AWG*1P+D+AL+MY]*4C+32AWG*1P+32AWG*4C+23AWG*2C+AB TPE/BLACK OD: 4.5±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK

<b>Desc.</b>	<b>ROLINE USB 3.2 Gen 2x2 (20Gbit/s) Cable, CM-CM, 240W, black 1m</b>
<b>Item No.</b>	<b>11.02.9076</b>

**SECOMP**

			2022-02-14	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.