



MOSA M8 FEMALE 0° FIELD-WIREABLE (IDC)3-pol. 0.25...0.5mm²

Female straight

3-pole

Insulation displacement technology

Connection cross section: 0.25...0.5 mm²[Link to Product](#)**Illustration**



Product may differ from Image

Approvals



Form

08361

Technical Data

Operating voltage	max. 32 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.25...0.5 mm ² (conductor diameter min. 0.1 mm)
Sealing range (cable diameter)	4...5.1 mm
Wire isolation	PVC, PP, TPE
Outer wire diameter	1.2...1.6 mm
Protection	IP67 inserted and tightened (EN 60529)

General data

Temperature range	-25...+85 °C
Dimensions H × W × D	48×13×13 mm

Commercial data

country of origin	DE
customs tariff number	85369010

minimum order quantity

1