

## Slides DZ 2730, Width 19.0 mm, to 30 kg, Full Extension

### Material:

Slide elements: Cold-rolled steel, bright zinc-plated.

Ball retainers: Cold-rolled, zinc-plated steel.

Balls: Hardened steel.


Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Compact profile.
- Low height.
- Service life 80,000 cycles.
- Temperature range: -20°C to +70°C.



Accuride

Ordering details: e.g.: Prod. No. 649 029 20, Slides DZ 2730



| Product No.<br>per Pair | Slide Length<br>mm | Travel<br>+/-3.2<br>mm | A<br>mm | B<br>mm | C<br>mm | D<br>mm | Load Rating<br>per Pair<br>kg | Weight<br>per Pair<br>kg |
|-------------------------|--------------------|------------------------|---------|---------|---------|---------|-------------------------------|--------------------------|
| 649 029 20              | 200                | 205,5                  | -       | -       | 128     | 160     | 22                            | 0,60                     |
| 649 029 25              | 250                | 255,0                  | -       | -       | 160     | 192     | 25                            | 0,74                     |
| 649 029 30              | 300                | 304,0                  | -       | -       | 224     | 256     | 28                            | 0,90                     |
| 649 029 35              | 350                | 353,0                  | -       | -       | 256     | 288     | 30                            | 1,06                     |
| 649 029 40              | 400                | 402,0                  | 192     | 224     | 320     | 352     | 30                            | 1,22                     |
| 649 029 45              | 450                | 452,0                  | 224     | 256     | 384     | 416     | 28                            | 1,38                     |
| 649 029 50              | 500                | 501,0                  | 256     | 288     | 416     | 448     | 25                            | 1,54                     |
| 649 029 55              | 550                | 550,0                  | 256     | 288     | 480     | 512     | 22                            | 1,68                     |
| 649 029 60              | 600                | 599,0                  | 288     | 320     | 512     | 544     | 20                            | 1,84                     |

### Note

Recommended mount: M4 screw.

Max. head. height 2,5mm/Ø9,6mm.

Use all mounting positions to achieve the max. load rating.

The load capacity was tested with a rail spacing of 450 mm.

**Selection Tool**  
on the Internet at [www.maedler.de](http://www.maedler.de)  
in the section **MÄDLER®-Tools**