

Flexible shaft

Speed range 7,500-30,000 rpm, 8 mm

metabo[®]

Application:

Extension for grinding and milling work.

Execution:

- Ball bearings at both ends
- Clamping bore 8 mm



Art. no.	70309 205
Brand	METABO
Manufacturer Part Number	630980000
Model	30980
Manufacturer Article Number	630980000
Min./max. rotation speed	7500-30000 rpm
Max. clamping diameter	8 mm
Wave length	1.3 m
Collet chuck diameter	8 mm
Gross Weight	0.918 kg
Product Group	745

EAN

4007430423689