

Product information

86 05 150

Pliers Wrench

Pliers and a wrench in a single tool



- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings - working directly on chrome!
- Also excellent for gripping, holding, pressing and bending workpieces
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Fast adjustment by pushing a button directly on the workpiece
- No unintentional shift of the gripping jaws and no slipping of the joint
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened




General

Article No.	86 05 150
EAN	4003773069928
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	193 g
Dimensions	150 x 50 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw thickness (joint) (B2)	7.0 mm
Joint thickness (B3)	10.5 mm
Tips thickness (B1)	4.7 mm
Adjustment positions	14
Capacities for nuts	Ø 1 Inch
Capacities for nuts	27 mm



technical change and errors excepted

