

Ratchet cable cutters

For diameters up to 32 or 52 mm, with 2-component grip covers



Application:

For cutting copper and aluminium cables.

Execution:

- Special-grade tool steel, oil-hardened
- Hardened, precision-ground blades
- Not suitable for steel wire and piano wire

Advantage:

- Cut smoothly and cleanly without crushing
- One-handed operation using ratchet principle, low force required thanks to optimum transmission ratios
- 2-speed gear ring drive for simple cutting
- Simple to use thanks to low weight and compact design; even possible to use in confined spaces
- With pinching guard to prevent crushing injuries



Art. no.	53102 020
Brand	KNIPEX
Manufacturer Part Number	95 31 280
Length	280 mm
Max. medium wire diameter cutting capacity	52 mm
Material of handle	2-component plastic
Gross Weight	0.800 kg
Product Group	535

EAN

4003773043942