


## LED Indicator Light



Material of Body:	Chrome Plated Brass
Colour:	Red & Green
Lens:	White
Voltage:	12V
Voltage Breakdown:	AC 500V /min
Insulation Resistance:	DC 500V 100Mohm or more
Operating Temperature:	-20°C to +75°C
Terminals:	Lead Wires (UL 1007 AWG24)
Thread:	Ø 6.00mm x L 8.0mm Pitch = 0.75mm
Mounting Hole:	Ø6.2mm