

Electronic dial gauge

MarCator 1086 Ri



Application:

For static measurements of lengths and length differences

Execution:

- Factor adjustable
- Large and high-contrast LCD display
- Digit height 11 mm
- With Integrated Wireless
- Permissible deviation MPEp for increment 0.0005=2 µm, for increment 0.01=20 µm
- mm/inch changeover

Advantage:

- LOCK function (key lock)

Delivery:

In case with CR 2450 battery



Art. no.	33166 840
Brand	MAHR
Manufacturer Part Number	4337625
Length measuring range	25 mm
Digit increment	0.0005 mm
Min./max. measurement force	0.65-1.15 N
Error limit	4 µm
Repeat accuracy	2 µm
Data transmission type	multiCOM/MarConnect
IP protection class	IP 42
Absolute function	Yes
Automatic switch-off	Yes
Preset function	Yes
Tolerance value entry	Yes
Number of rechargeable batteries/batteries	1 PCS
Rechargeable battery/battery capacity	540 mAh
Battery voltage	3 V
Weight of rechargeable battery/battery	0.006 kg
Battery designation	3V CR2450N lithium
Rotating housing	Yes
Reversible counting direction	Yes
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	0.250 kg
Product Group	305

EAN

4059192014544