

[IMAGE]

### Product Information

Product Category	HEATING
Unit Barcode	5016368000243
Outer Carton Barcode	
Commodity Code	8516293100
Country of Origin	CHINA
Primary Colour	WHITE
Finish	PLASTIC
Primary Material	PLASTIC
Warranty	1
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

### General Product Specification

Voltage	230
Frequency	50
Wattage	2000
Rated Current	8.7
Fuse Rating	13
Plug Type	BS 1363
Cable Diameter	1
Cable Length	1.4
Class	CLASS II
Conformity Markings	CE+UKCA

### Packaging & Shipping Information

Product Dimensions H x W x D (mm)	187	540	138
Packaged Dimensions H x W x D (mm)	230	565	153
Outer Carton Dimensions H x W x D (mm)	475	575	325
Outer Carton Qty.	4		
Unit Weight (Kg)	2.4		
Unit Packaged Weight (Kg)	2.8		
Carton Weight (Kg)	12		
EPS (Kg)	0.03	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.244	Card / Paper (Kg)	0.27
Aluminium (Kg)		Steel (Kg)	

### Category Specific Technical Information

HT Max Timer	1440	Nominal Output	2000
Annual Consumption		Number of Speeds	N/A
Anti Frost	NO	Oscillation	YES
Auto Shutoff	YES	Overheat Protection	YES
BEAB Approved	NO	Power Indicator	YES
Castors	NO	Programmable Timer	YES
Control Type		Remote Control	YES
Display Type	LED	Room Size	20
Energy Efficiency Indec		Steady Grip Feet	NO
ERP Rated Off Power	0	Temperature Display	YES
ERP Standby	0.392	Temperature Range	#####
Fuel Type	ELECTRIC	Thermostat Type	DIGITAL
Gas Connection		Thermostatic Cutoff	YES
Heat Resistant Handle	YES	Thickness	2.3
Heat Resistant Housing	YES	Timer Type	DIGITAL
Heat Up Time		Tip Over Switch	NO
Heater Power	2000	Tumble Dryer	NO
Machine Washable	NO	Voice Assistant	NO
No. of Settings	3	Wa Mountable	YES
No. of Temp Settings		WiFi Capability	NO