

Quick coupling plug KS2-CK-3

FESTO

Part number: 4091



Data sheet

Feature	Value
Nominal width	2 mm
Type code	KS2
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	68 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	4 g
Pneumatic connection 1	CK-3
Note on materials	RoHS-compliant