



VT-754 WALL LAMP -MATT WHITE(FROST GLASS)

Dimensions
245x180x93mm

SKU:7077

3 YEARS
WARRANTY



Technical Information

Holder Type: **E27**

IP Rating: **IP44**

Rated Load: **Max 40W**

Dimmable: **No**

Unit Color: **Matt White**

Warranty (Years): **3**

Body Type: **Aluminium + Glass**

Input Power: **AC:220-240V,50Hz**

Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

Packaging

Unit Details

Gross Weight(GW) Kgs	1.53
Unit CBM	0.0045

Listing Details

EAN Code	3800157616300
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	300

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES