

## Product information

# 62 12 120

## Electronics Oblique Cutting Nipper

DIN ISO 9654

- With cutting edges for soft and medium hard wire
- Without bevel, for flush cutting
- Low-friction double spring for gentle and even opening
- Sturdy, zero backlash box joint
- The polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- Ball bearing chrome steel, oil hardened




### General

Article No.	62 12 120
EAN	4003773048008
Head	polished
Handles	with multi-component grips
Weight	70 g
Dimensions	120 x 67 x 17 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities soft wire (diameter)	Ø 0.3 – 1 mm
Cutting capacities medium hard wire (diameter)	Ø 0.7 mm
Jaw length (B)	10 mm
Jaw thickness (joint) (D)	7.5 mm
Cutting edge length mm (C)	17 mm
Head width (A)	11 mm



technical change and errors excepted

