



## **Datasheet**

## RS PRO LED Weatherproof – 5ft


Stock No: 2105499



Model:	5' 40W 600mm Polycarbonate Weatherproof IP65
Length	1500mm
Width	96mm
Height	83mm
Weight	13.6kg

## **Features & Benefits:**

- Suitable for industrial and commercial applications
- Energy savings of up to 50%, compared to fluorescent fittings
- ENEC Approved Driver
- Wide Voltage range (100-240V), with built in low voltage protection device
- Operating temp of -25°C to +50°C
- Improved install design. 2-part fitting allows for quicker installation
- Supplied with tamper proof, stainless steel clips
- Compatible with besa box mounting.



Model:	5′ 40W 600mm Polycarbonate Weatherproof IP65
Operating Wattage	40W
Operating Voltage	100-240V 50-60Hz
Power Factor	≥0.9
Colour Temperature	6500K
Luminous Flux	4800Lm
Luminous Efficiency	120Lm/W
CRI	≥80
Lifespan	50,000 Hrs
IP rating	IP65
IK Rating	IK08



