

LED cold light source F5 100

With outstanding light output of up to 1400 lm



Application:

Fibre optic light source impresses with its excellent light output. Ideal for stereomicroscopic and endoscopic inspection tasks requiring good illumination. Due to the low heat generation, also suitable for heat sensitive objects.

Execution:

- Robust metal housing
- Long-lasting, energy-efficient LED light source
- high-contrast OLED display (dimnable)
- Strobe head function with trigger input
- remote control via USB and foot switch
- High-quality white light for optimal illumination
- Filter insert for different filters

Advantage:

- comprehensive menu and setting options with stroboscope function
- latest fibre optic light source with 1400-lumen light output
- infinite brightness regulation from 1 - 100% (flicker-free)
- Brightness, shutter/strobe parameters individually configurable
- Intelligent fan control for minimal noise emission



Art. no.	41613 639
Brand	PHOTONIC
Manufacturer Part Number	10140 + ELN-3.001
Model	F5100
Lamp type	LED
Colour temperature	6500 K
ESD bush	Yes
Life time of illuminant	25000 h
Input voltage	24 V/DC
Min./max. nominal voltage	100 / 240 V/DC
Gross Weight	3.400 kg
Product Group	412