

Features

- Cable ties in high industrial quality with rounded edges to prevent cable damage
- Inclined tip to indicate usage direction and quick installation time
- Halogen free



Specification

| | |
|---------------------------|------------------|
| Material | Polyamide |
| Band Closure | Plastic lip/-cam |
| UV-Stable acc. ASTM D6779 | Yes |
| Transparent | No |
| Solvable Fastener | No |
| Text Strip | None |
| Type of Fastening | None |
| Surface Protection | Untreated |
| Operating Temperature | -40 ... 85 °C |

| RND Type | Bundle Diameter min. | Bundle Diameter max. | Max. Tensile Force | Colour | Length | Width |
|---------------|----------------------|----------------------|--------------------|---------|--------|--------|
| RND 475-00895 | 2 mm | 21 mm | 80 N | Natural | 102 mm | 2.5 mm |
| RND 475-00896 | 2 mm | 21 mm | 80 N | Black | 102 mm | 2.5 mm |
| RND 475-00897 | 2 mm | 49 mm | 220 N | Natural | 186 mm | 4.8 mm |
| RND 475-00898 | 2 mm | 49 mm | 220 N | Black | 186 mm | 4.8 mm |
| RND 475-00899 | 2 mm | 81 mm | 220 N | Natural | 286 mm | 4.8 mm |
| RND 475-00900 | 2 mm | 81 mm | 220 N | Black | 286 mm | 4.8 mm |
| RND 475-00901 | 3 mm | 101 mm | 540 N | Natural | 368 mm | 7.6 mm |
| RND 475-00902 | 3 mm | 101 mm | 540 N | Black | 368 mm | 7.6 mm |
| RND 475-00903 | 2 mm | 106 mm | 220 N | Natural | 371 mm | 4.8 mm |
| RND 475-00904 | 2 mm | 106 mm | 220 N | Black | 371 mm | 4.8 mm |