

Slides DZ 2002, width 9.5 mm, up to 35 kg, extension in both directions

Material:

Slide elements: Cold-rolled, bright zinc-plated steel.


Ball retainers: Cold rolled, zinc-plated steel.

Balls: Hardened steel.

Telescopic precision ball bearing slides for applications in the industrial and electronics sector.

- Hold-in in the centre position.
- Forward and return slide. For applications, that require access from both sides of a sliding unit.
- Fasteners included.
- High service life 50,000 cycles.
- Temperature range: -20°C to +70°C.

Ordering Details: e.g.: Product No. 649 003 30, Slides DZ 2002



Product No. per pair	Slide Length mm	Travel +/-3.2 mm	A mm	B mm	C mm	D mm	Load Rating Pair kg	Weight Pair kg
649 003 30	305	222	-	136,7	247,7	153,4	35	0,59
649 003 35	356	272	-	187,5	298,5	204,2	35	0,69
649 003 40	406	298	-	238,3	349,3	255,0	35	0,78
649 003 45	457	323	200,2	289,1	400,1	305,8	35	0,89
649 003 50	508	374	225,6	339,9	450,9	356,6	32	1,00
649 003 55	558	399	251,0	390,7	501,7	407,4	31	1,08
649 003 60	610	425	276,4	441,5	552,5	458,2	29	1,19
649 003 65	660	476	301,8	492,3	603,3	509,0	27	1,28
649 003 70	711	501	327,2	543,1	654,1	559,8	24	1,38

Note

Recommended fastening: M4 screw.

Use all mounting positions to achieve the max. load rating.

