

Pneumatic ratchet screwdriver MDR 2101

**MANNESMANN
DEMAG**

Application:

For use in confined spaces

Execution:

- Thermally insulated soft handle
- Exhaust air duct can be rotated 360°



Art. no.	75061 205
Brand	MANNESMANN DEMAG
Manufacturer Part Number	82400202
Model	MDR 2101
Suitable for screw	M10
Max. tightening torque	160 Nm
Max. idle speed	180 rpm
Air consumption	10.8 l/s
Tool holding device	3/8-inch external square
Connection thread	NPT 1/4 inch
Inner hose diameter	10 mm
Sound-pressure level	84 dB
Valve design	Lever valve
Length	270 mm
Weight	1.3 kg
With right/left-hand rotation	Yes
Gross Weight	1.318 kg
Product Group	7AA

EAN

4251757302718