

SNP42NGHS0C2



Article Number: 191-00008

Snapper Hose Clamps, 1.741"/2.018" Min/Max Diameter, PA66GF13%, Black, 100/pkg



Download spec sheet

Base Data

Local Order Number SNP42NGHS0C2

Type SNP42N

Color Black (BK)

Features and Benefits

- Designed for quick, ratcheted installation and can be released and reused.
- Heat stabilized material is suitable for high temperature applications.

Product Description HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

Short Description Snapper Hose Clamps, 1.741"/2.018" Min/Max Diameter, PA66GF13%, Black, 100/pkg

Product Dimensions

Fixation Method Plug-in mounting

Variant Closed

Width W2 (Imperial) 0.287 "

Width W2 (Metric) 7.29 mm

Bundle Diameter Min. (Imperial) 1.75 "

Bundle Diameter Min. (Metric) 45.5 mm

Bundle Diameter Max. (Imperial) 2.06 "

Bundle Diameter Max. (Metric) 52 mm

Diameter Min. (Imperial) 1.741 "

Diameter Min. (Metric) 44.22 mm

Diameter Max. (Imperial) 2.018 "

Diameter Max. (Metric) 51.26 mm

Wall Thickness WT (Imperial) 0.069 "

Wall Thickness WT (Metric) 1.717 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 800

Material and Specifications

Material Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)

Material Shortcut PA66GF13

Flammability UL94 HB

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS Compliant Yes