

## Product Datasheet


|                           |  |
|---------------------------|--|
| <b>Product code:</b>      | <b>00.SA.0</b>   |
| <b>Product type:</b>      | High precision tweezers  |
| <b>Made in:</b>           | Switzerland  |
| <b>Description:</b>       | Type 00 high precision tweezers are suitable to applications which require holding a component firmly. |
| <b>Tip description:</b>   | straight, thick, squared, strong, superior finish  |
| <b>Coating/finishing:</b> | Sandblasted  |
| <b>Body material:</b>     | Anti-Magnetic Anti-Acid Stainless Steel (SA)   |

**Picture:**



|                            |        |                       |
|----------------------------|--------|-----------------------|
| <b>Tweezer dimensions:</b> | OAL    | 120.0 mm – 4.724 inch |
|                            | Width  | 10.0 mm – 0.394 inch  |
|                            | Height | 12.0 mm – 0.472 inch  |

**Tip details:**



|                        |               |                      |
|------------------------|---------------|----------------------|
| <b>Tip dimensions:</b> | Tip width     | 0.85 mm – 0.033 inch |
|                        | Tip thickness | 0.50 mm – 0.020 inch |