



RoHS
Compliant



Maximum Ratings:

Characteristic	Symbol	Rating	Unit
Collector - Base Voltage	V_{CBO}	180	V
Collector - Emitter Voltage	V_{CEO}	160	
Emitter - Base Voltage	V_{EBO}	6	
Continuous Collector Current	I_C	600	A
Total Device Dissipation ($T_A = +25^\circ\text{C}$), Derate above 25°C	P_D	625	mW
		5	mW/ $^\circ\text{C}$
Total Device Dissipation ($T_C = +25^\circ\text{C}$), Derate above 25°C		1.5	W
		12	mW/ $^\circ\text{C}$
Operating Junction Temperature, Range	T_J	-55 to +150	$^\circ\text{C}$
Storage Temperature Range	T_{stg}		
Thermal Resistance, Junction-to-Case	R_{thJC}	83.3	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Ambient (Note-1)		200	

Note:

1. R_{thJA} is measured with the device soldered into a typical printed circuit board.

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ Unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Max	Unit
-----------	--------	-----------------	-----	-----	------

OFF Characteristics

Collector - Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = 100\mu\text{A}, I_E = 0$	180	-	V
Collector - Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 1\text{mA}, I_B = 0$, Note 2	160		
Emitter - Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = 10\mu\text{A}, I_C = 0$	6		
Collector Cut - Off Current	I_{CBO}	$V_{CB} = 120\text{V}, I_E = 0$	-	50	nA
		$V_{CB} = 120\text{V}, I_E = 0, T_A = +100^\circ\text{C}$			uA
Emitter Cut - Off Voltage	I_{EBO}	$V_{EB} = 4\text{V}, I_C = 0$			

ON Characteristics (Note 2)


DC Current Gain	h_{FE}	$V_{CE} = 5\text{V}, I_C = 1\text{mA}$	80	-	-
		$V_{CE} = 5\text{V}, I_C = 10\text{mA}$		250	
		$V_{CE} = 5\text{V}, I_C = 50\text{mA}$	30	-	
Collector - Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 10\text{mA}, I_B = 1\text{mA}$	-	0.15	V
		$I_C = 50\text{mA}, I_B = 5\text{mA}$		0.2	
Base - Emitter On Voltage	$V_{BE(sat)}$	$I_C = 10\text{mA}, I_B = 1\text{mA}$			
		$I_C = 50\text{mA}, I_B = 5\text{mA}$			

Small-Signal Characteristics

Current Gain Bandwidth Product	f_T	$V_{CE} = 10\text{V}, I_C = 10\text{mA}, f = 100\text{MHz}$	100	300	MHz
Output Capacitance	C_{obo}	$V_{CB} = 10\text{V}, I_E = 0, f = 1\text{MHz}$	-	6	pF
Input Capacitance	C_{ibo}	$V_{BE} = 0.5\text{V}, I_C = 0, f = 1\text{MHz}$		20	
Small-Signal Current Gain	h_{fe}	$V_{CE} = 10\text{V}, I_C = 1\text{mA}, f = 1\text{kHz}$	50	200	-
Noise Figure	NF	$V_{CE} = 5\text{V}, I_C = 250\mu\text{A}, f = 1\text{kHz}, R_s = 1\text{k}\Omega$	-	8	dB

Note:

2. Pulse Test : Pulse Width = 300 μs , Duty Cycle = 2%



Dimensions	A	B	C	D	E	F	G	H	K
Min.	4.32	4.45	3.18	0.41	0.35	5°	1.14	1.14	12.7
Max.	5.33	5.2	4.19	0.55	0.5		1.4	1.53	-

Dimensions : Millimetres

Part Number Table

Description	Part Number
Transistor, NPN, 0.6A, 160V, TO-92	2N5551

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.