San Ace 40 9HVA type

High Static Pressure Fan

Features

High Static Pressure and High Airflow

This fan delivers a maximum static pressure of 2300 Pa and a maximum airflow of 1.05 m³/min.

Compared with our current model,* the maximum static pressure has increased by 2.1 times and the maximum airflow has increased by 1.3 times.

Energy-saving

Power consumption has been reduced by approximately 20% compared with the current model.*

Space-saving

This fan delivers higher cooling performance than our 40 × 40 × 56 mm Counter Rotating Fan.**

The smaller fan size provides enhanced design flexibility.

- * Current model: San Ace 40 9HV type $40 \times 40 \times 28$ mm DC Fan (model no. 9HV0412P3K001). ** San Ace 40 9CRV type $40 \times 40 \times 56$ mm Counter Rotating Fan (model no. 9CRV0412P5J201).





40 x 40 x 28 mm

Specifications

The models listed below have ribs and pulse sensors with PWM control function.

Model no.	Rated voltage [V]	Operating voltage range [V]	PWM duty cycle* [%]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. a [m³/min]		Max. stat [Pa]	ic pressure [inchH ₂ O]	SPL [dB(A)]	Operating temperature [°C]	Expected life [h]
9HVA0412P3J001	12	10.2 to 13.8	100	2.6	31.2	38000	1.05	37.1	2300	9.24	71	-20 to +70	30000/60°C
			20	0.12	1.4	8000	0.22	7.8	101	0.41	34		(53000/40°C)

^{*} PWM input frequency is 25 kHz; models without specifications at 0% PWM duty cycle have zero fan speed at 0%.

Models with the following sensor specifications are also available as options: Without sensor Lock sensor

Common Specifications


☐ Material · · · · Frame: Plastic (Flammability: UL 94V-0), Impeller: Plastic (Flammability: UL 94V-0) ☐ Expected life Refer to specifications (L10 life: 90% survival rate for continuous operation in free air at 60°C, rated voltage) Expected life at 40°C is for reference only. ☐ Motor protection function · · · · · · Locked rotor burnout protection, Reverse polarity protection ☐ Sound pressure level (SPL) · · · · · · · · At 1 m away from the air inlet ☐ Operating temperature · · · · · · · · · Refer to specifications (Non-condensing) \square Lead wire $\cdots \cdots \oplus \mathsf{Red} \ \ominus \mathsf{Black} \ \mathsf{Sensor} \mathsf{Yellow} \ \mathsf{Control} \mathsf{Brown}$ ☐ Mass · · · · · 57 g

· Operating voltage range

Airflow - Static Pressure Characteristics

· PWM duty cycle (inch H₂O) (Pa) 10 ⊢ 2500 PWM duty cycle 8 2000 Static pressure 1500 - 1000 500 n 0.2 0.4 1.2 (m³/min) 0.6 0.8 1.0 20 30 40

Airflow



20


Airflow

30

40 (CFM)


10

PWM Duty -Speed Characteristics Example



PWM Input Signal Example

Input signal waveform



 $V_{IH} = 4.75 \text{ to } 5.25 \text{ V} \quad V_{IL} = 0 \text{ to } 0.4 \text{ V} \\ PWM \text{ duty cycle (\%)} = \frac{T_1}{T} \times 100 \qquad PWM \text{ frequency } 25 \text{ (kHz)} = 0.00 \text{ (kHz)}$ Current source (Isource) = 1 mA max. (when control voltage is 0 V) Current sink (Isink) = 1 mA max. (when control voltage is 5.25 V)


Control terminal voltage = 5.25 V max. (when control terminal is open)

When the control terminal is open,

fan speed is the same as when PWM duty cycle is 100%.


Either TTL input, open collector or open drain can be used for PWM control input signal.

Example of Connection Schematic




Specifications for Pulse Sensors

Output circuit: Open collector




Output waveform (Need pull-up resistor)

In case of steady running




Dimensions (unit: mm)



Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)

Inlet side, Outlet side



Notice

- ●Please read the "Safety Precautions" on our website before using the product.
- The products shown in this catalog are subject to Japanese Export Control Law. Diversion contrary to the law of exporting country is prohibited.
- For protecting fan bearings against electrolytic corrosion near strong electromagnetic noise sources, we provide effective countermeasures such as Electrolytic Corrosion Proof Fans and EMC guards. Contact us for details.

https://www.sanyodenki.com

SANYO DENKI CO., LTD. 3-33-1 Minami-Otsuka, Toshima-ku, Tokyo 170-8451, Japan TEL: +81 3 5927 1020 The names of companies and/or their products specified in this catalog are the trade names, and/or trademarks and/or registered trademarks of such respective companies. "San Ace" is a trademark of SANYO DENKI CO.,LTD.