

Weldon surface chucks

In accordance with ISO 12164 (DIN 69893)

ORION[®]

Application:

For clamping tools with straight shanks and clamping surfaces in line with DIN 1835 B.

Execution:

- All tapers and tolerances are precision-ground.
- Taper tolerance AT3.
- Strength HRC 57-60.
- Core strength 1,000-1,200 N/mm².
- With Balluff chip hole.
- All functional surfaces machined.

Advantage:

- Prevents the tool from slipping while maintaining high concentricity.

Delivery:

1x surface chuck (Weldon) in accordance with ISO 12164 (DIN 69893).



Art. no.	23157 218
Brand	ORION
Manufacturer Part Number	23157218
Tool holding device	HSK 63
Clamping diameter	18 mm
Projecting length	80 mm
Length	54 mm
Outer diameter	50 mm
Coolant supply	Internal axial
Balancing quality	G 6.3 at 15 rpm
Gross Weight	1.390 kg
Product Group	2AV

EAN

4053625292110