

Shrink-fit chuck

In accordance with ISO 7388-1 (DIN 69871)

diebold

Application:

For precise clamping of tools with straight shank h6.

Execution:

- Concentricity tolerance of hollow shank taper for location hole dia.< 0.003 mm.
- Clamping diameter for h6 shank tolerance.
- For higher speeds, fine balancing is necessary.
- Required pull stud no. 23690.

Delivery:

1x shrink-fit chuck in accordance with ISO 7388-1 (DIN 69871).



Art. no.	23425 510
Brand	DIEBOLD
Manufacturer Part Number	72.060.500.100
Tool holding device	SK 40
Clamping diameter	6 mm
Projecting length	80 mm
Tapered diameter	21 mm
Clamp in depth	36 mm
Form	AD
Concentricity tolerance	0.003 mm
Max. adjustment travel	10 mm
Coolant supply	Internal axial
Balancing quality	G 2.5 at 25 rpm
Gross Weight	1.044 kg
Product Group	297