

PRODUCT SPECIFICATION

Brand	Kasp
Product Range	Stainless Steel Padlock
Catalogue number	150
Date	16/09/2009

Range Description

Closed Shackle Stainless Steel Padlock

Features

Manufactured from a solid block of marine grade stainless steel, the robust Kasp 150 series is capable of meeting the stringent demands of high security industrial applications whilst offering the reassurance of an entirely corrosion resistant construction.

The 5-pin anti-pick cylinder is designed to withstand intelligent picking and manipulation methods, whilst the 9mm stainless steel shackle is secured in the locked position by 2 ball bearings, universally accepted as one of the most secure locking mechanisms available.

- Rust free internal components & drainage system – extra resistance against corrosion
- Closed Shackle – Additional protection from shackle attack
- Double ball bearing locking mechanism – Extra strength to resist torsion & pull attack
- 5 pin cylinder with anti pick mushroom pins – Extra protection against picking
- Paracentric keyway – extra protection against manipulation
- Weather rating: 3



Item Number	Item Description	EAN No	Commodity code	Carton Qty
K15050D	Stainless Steel Padlock – 50mm	5013969901856	83011000	6

Technical product information	<p>Body – Stainless Steel</p> <p>Shackle – Stainless steel</p> <p>Key differs - 1988</p> <p>Re-keyable – No</p> <p>Security rating:</p> <table border="1"> <tr> <th>Item</th> <th>Security rating</th> </tr> <tr> <td>K15050D</td> <td>11</td> </tr> </table> <p>Shackle Dimensions:</p> <table border="1"> <thead> <tr> <th rowspan="2">Dimensions mm</th> <th colspan="3">Shackle</th> <th>Body</th> </tr> <tr> <th>Dia</th> <th>Internal width</th> <th>Internal height</th> <th>Width</th> </tr> </thead> <tbody> <tr> <td>K15050D</td> <td>9</td> <td>19</td> <td>20</td> <td>50</td> </tr> </tbody> </table> <p>Use environment- Harsh outdoor use</p> <p>Recommended applications- Garages, Shutters, Vehicles, site gates</p>	Item	Security rating	K15050D	11	Dimensions mm	Shackle			Body	Dia	Internal width	Internal height	Width	K15050D	9	19	20	50
Item	Security rating																		
K15050D	11																		
Dimensions mm	Shackle			Body															
	Dia	Internal width	Internal height	Width															
K15050D	9	19	20	50															
Standards compliance	None applicable																		
User health and safety information	None applicable																		
RoHS/WEEE compliance	This product does not fall within the scope of RoHS or WEEE regulations																		
Material safety data	None applicable																		
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered																		
Country of origin	China																		

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K15050D	50	20	73	365	140	25	170	402

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K15050D	145	215	100	2512		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K15050D	31	Blister	6	Backing card			100	Box