

4-1564528-1 ✓ ACTIVE

AMP | Heavy Duty Sealed Connector Series

TE Internal #: 4-1564528-1

Heavy Duty Sealed Connector Series, Housing for Male Terminals, Wire-to-Wire, 16 Position, 6mm / 4mm [.236in / .157in] Centerline, Sealable, Blue

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings > HEAVY DUTY SEALED CONNECTOR HOUSINGS



Connector & Housing Type: **Housing for Male Terminals**

Mating Tab Width: **1.6 mm, 2.8 mm** [.063 in, .11 in]

Connector System: **Wire-to-Wire**

Number of Positions: **16**

Centerline (Pitch): **4 mm, 6 mm** [.157 in, .236 in]

[All HEAVY DUTY SEALED CONNECTOR HOUSINGS \(186\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	Yes
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	16
Number of Rows	2

Electrical Characteristics

Operating Voltage	60 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 60 V

Body Features

Cable Exit Angle	Other
Body Material	PBT GF
Primary Product Color	Blue

Contact Features



Mating Tab Width	1.6 mm, 2.8 mm [.063 in][.11 in]
------------------	----------------------------------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	4 mm, 6 mm [.157 in][.236 in]
--------------------	-------------------------------

Dimensions

Product Width	27 mm [1.063 in]
Product Length	52.6 mm [2.071 in]
Product Height	48.1 mm [1.894 in]
Row-to-Row Spacing	6 mm [.236 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C [158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
Operating Temperature Range	-40 – 140 °C [-40 – 284 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	200
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>











EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-H3399-B128 HEAVY DUTY SEALED CONNECTOR BACKSHELLS</p>	 <p>TE Part # CAT-H3399-CH8172 HEAVY DUTY SEALED CONNECTOR HOUSINGS</p>	 <p>TE Part # CAT-H3399-C1748 HEAVY DUTY CONNECTORS PROTECTION CAPS</p>	 <p>TE Part # CAT-T4827-T273 TIMER, RECEPTACLE AND TAB</p>
 <p>TE Part # 964972-1 EINZELLEITERDICHTUNG</p>	 <p>TE Part # 828905-1 SINGLE-WIRE-SEAL(5MM HOLE)</p>	 <p>TE Part # 2317070-1 SLIDE, HDSCS, PIN HSG ASSY</p>	 <p>TE Part # 2-964269-2 TAB A 1.6x0.6 CONTACT CF SWS Ag</p>

Also in the Series | Heavy Duty Sealed Connector Series



Automotive Connector Caps & Covers (20)



Automotive Housings(189)



Automotive Seals & Cavity Plugs(1)




Insertion & Extraction Tools(1)



Other Automotive Connector Accessories(22)

Customers Also Bought



TE Part #4-968970-1
AMP MCP, UNSEALED CONNECTOR HOUSING



TE Part #5053256106
Single Wall RNF-100 Spool HS Tubing




TE Part #2-962841-2
TIMER, RECEPTACLE AND TAB




TE Part #2-66741-0
TYPE XII FEMALE CONTACT




TE Part #2066046-3
2 POS MINI FUSE BOX ASSY




TE Part #708473-2
XCT 35-8 EQ



TE Part #3002083001
ACW0219-1.00-92(NS)



TE Part #CD89943001
ACW0219-1.50-3(NS)



TE Part #6457236005
Single Wall RNF-100 Piece HS Tubing

Documents



Product Drawings

[16POS, MIXED,TAB HSG,ASSY](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_4-1564528-1_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1564528-1_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1564528-1_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HDSCS Catalog](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English