

Ersa tool holders and cleaning sponges

0A04



0A05



0A08MSET



0008M



Soldering and desoldering devices are heating devices and, depending on the application, can attain high temperatures during operation. This equipment must never be operated without supervision; during longer interruptions of work they should be switched off and always be stored in suitable tool holders.

Most of the Ersa tool holders are made of metal or heat-resistant duroplastic, and most are antistatic.

Most holders have a viscous sponge for tip cleaning, as well as options for conveniently resting and storing soldering and desoldering tips.


0A17



0A18



0A42



0A45



0A52



3N194



0A53



0A54



0A55



0A56



0A57



0003B



0004G





















Order no.	Description	for
0A04	Tool holder A 04	Soldering irons from 50 W – 150 W output; ISOTYP and 0185PZ soldering irons
0A05	Tool holder A 05	Medium-sized and small soldering irons
0A08MSET	Dry sponge 0008M with container	Dry cleaning of soldering tips (especially for lead-free)
0A17	Tool holder A 17	Soldering irons with an output ranging from 200 W – 550 W
0A18	Tool holder A 18	Soldering irons of the MULTITIP series; TIP 260 soldering iron
0A39	Tool holder A 39	RT 80 soldering iron (fig. see page 14)
0A42	Tool holder A 42, antistatic	TIP TOOL, POWER TOOL, ERGO TOOL, MICRO TOOL and TECH TOOL soldering irons
0A43	Tool holder A 43, antistatic	CHIP TOOL (fig. see page 20)
0A44	Tool holder A 44, antistatic	X-TOOL desoldering iron (fig. see page 25)
0A45	Universal holder A 45	832 tip series (C8 – C18, MD, QD, ZD models), solder wire feed unit and solder fume extraction
0A52	Tool holder A 52, antistatic	i-TOOL, i-TOOL NANO soldering irons
0A53	Tool holder A 53	i-TOOL PICO soldering iron
0A54	Tool holder A 54, antistatic	CHIP TOOL VARIO desoldering tweezers
0A55	Tool holder A 55, antistatic	i-TOOL AIR S hot-air iron
0A56	Tool holder A 56, antistatic	X-TOOL VARIO desoldering iron
0A57	Tool holder A 57, antistatic	i-TOOL HP soldering iron
3N194	Rubber support disk 3 N 194	MULTITIP, MULTI-PRO, Ersa 30 S soldering irons
05H03	SMD soldering and desoldering tip holder	Soldering and desoldering tips of the 212, 422 and 452 series
06156	Sponge container G156	INDEPENDENT 75 and INDEPENDENT 130 gas soldering irons
0003B	Blue viscose sponge, 55 x 55 mm	Tool holders 0A09, 10, 13, 16, 24, 25, 28, 29, 30, 34, 35, 36, 39, 41 – 45, 48
0004G	Viscose sponge, 34 x 65 mm	Tool holders 0A05, 0A21 and 0A26
0006G	Sponge, ø 36 mm	Sponge container 06156 for the INDEPENDENT 75 / 130 gas soldering irons
0008M	Dry sponge 0008M	Dry sponge holder 0A08MSET

ERSADUR long-life soldering tip series 102

■ All i-CON soldering stations with soldering irons i-TOOL, i-TOOL NANO, i-TOOL PICO

Large selection ranging from 0.2 mm to 25 mm

Lead-free
Bleifrei
SAFE 

<p>0102PDLF02</p>  <p>pencil point, 0.2 mm \varnothing</p>	<p>0102PDLF03L</p>  <p>pencil point, extended, 0.3 mm \varnothing</p>	<p>0102PDLF04</p>  <p>pencil point, 0.4 mm \varnothing</p>
<p>0102PDLF04L</p>  <p>pencil point, extended, 0.4 mm \varnothing</p>	<p>0102PDLF05L</p>  <p>pencil point, extended, 0.5 mm \varnothing</p>	<p>0102PDLF06</p>  <p>pencil point, 0.6 mm \varnothing</p>
<p>0102PDLF06L</p>  <p>pencil point, extended, 0.6 mm \varnothing</p>	<p>0102PDLF07</p>  <p>pencil point, 0.7 mm \varnothing</p>	<p>0102PDLF08L</p>  <p>pencil point, extended, 0.8 mm \varnothing</p>
<p>0102PDLF10</p>  <p>pencil point, 1.0 mm \varnothing</p>	<p>0102CDLF04</p>  <p>chisel-shaped, 0.4 mm</p>	<p>0102CDLF12/ 0102CDLF16</p>  <p>chisel-shaped, 1.2 mm/1.6 mm</p>
<p>0102CDLF18L</p>  <p>chisel-shaped, extended, 1.8 mm</p>	<p>0102CDLF20</p>  <p>chisel-shaped, 2.0 mm</p>	<p>0102CDLF24</p>  <p>chisel-shaped, 2.4 mm</p>
<p>0102CDLF24L</p>  <p>chisel-shaped, extended, 2.4 mm</p>	<p>0102CDLF32</p>  <p>chisel-shaped, 3.2 mm</p>	<p>0102CDLF50</p>  <p>chisel-shaped, 5.0 mm</p>

Dimensions without pre-tinning