



**SAFETY DATA SHEET**  
ANTI-SEIZE SPRAY

Page: 1

Compilation date: 15/09/2014

Revision No: 9

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** ANTI-SEIZE SPRAY

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Anti-seize agent.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0) 113 232 2600

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** Aquatic Chronic 2: H411; Aquatic Chronic 3: H412; Flam. Aerosol 1: H222; Skin Irrit. 2: H315; -: H229

**Classification under CHIP:** F+: R12; N: R51/53; -: R67

**Most important adverse effects:** Extremely flammable aerosol. Pressurised container: May burst if heated. Causes skin irritation. Toxic to aquatic life with long lasting effects. Harmful to aquatic life with long lasting effects.

**2.2. Label elements**

**Label elements under CLP:**

**Hazard statements:** H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

H315: Causes skin irritation.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

**Signal words:** Danger

[cont...]

# SAFETY DATA SHEET

## ANTI-SEIZE SPRAY

Page: 2

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark

GHS09: Environmental



**Precautionary statements:** P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P251: Pressurized container: Do not pierce or burn, even after use.

P210: Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P211: Do not spray on an open flame or other ignition source.

P285: In case of inadequate ventilation wear respiratory protection.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P264: Wash thoroughly after handling.

P273: Avoid release to the environment.

P332+313: If skin irritation occurs: Get medical advice/attention.

P501: Dispose of contents/container to local/national guidelines.

### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) - REACH registered number(s): EXEMPT

EINECS	CAS	CHIP Classification	CLP Classification	Percent
270-704-2	68476-85-7	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	50-70%

HEPTANE & ISOMERS - REACH registered number(s): 01-2119475515-33-XXXX

295-434-2	92045-53-9	-	Flam. Liq. 2: H225; Aquatic Chronic 2: H411; Skin Irrit. 2: H315; STOT SE 3: H336; Asp. Tox. 1: H304	10-30%
-----------	------------	---	--	--------

DISTILLATES (PETROLEUM), HYDROTREATED HEAVY NAPHTHENIC (NOTE L - < 3% DMSO EXTRACT)

265-097-6	64741-96-4	Substance with a Community workplace exposure limit.	-	2-10%
-----------	------------	--	---	-------

COPPER POWDER

231-159-6	7440-50-8	-	Acute Tox. 4: H302; Aquatic Acute 1: H400; Aquatic Chronic 2: H411	2-10%
-----------	-----------	---	--	-------

[cont...]

# SAFETY DATA SHEET

## ANTI-SEIZE SPRAY

Page: 3

### GRAPHITE POWDER

231-955-3	7782-42-5	Substance with a Community workplace exposure limit.	-	2-10%
-----------	-----------	--	---	-------

### ACETONE

200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	2-10%
-----------	---------	---	--	-------

### CALCIUM CARBONATE

2151-79-6	1317-65-3	Substance with a Community workplace exposure limit.	-	<2%
-----------	-----------	--	---	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat. May cause dizziness.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

### 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Do not use water. Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** Extremely flammable. Forms explosive air-vapour mixture. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

[cont...]

# SAFETY DATA SHEET

ANTI-SEIZE SPRAY

Page: 4

## 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition.

## 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers.

## 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Do not use equipment in clean-up procedure which may produce sparks. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

## 6.4. Reference to other sections

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Smoking is forbidden.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in cool, well ventilated area. Keep away from sources of ignition. Keep away from direct sunlight. Ensure lighting and electrical equipment are not a source of ignition.

**Suitable packaging:** Must only be kept in original packaging.

### 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE)**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1000ppm 1750mg/m3	1250ppm 2180mg/m3	-	-

**HEPTANE & ISOMERS**

UK	500 ppm, 2085 mg/m3	-	-	-
----	---------------------	---	---	---

**DISTILLATES (PETROLEUM), HYDROTREATED HEAVY NAPHTHENIC (NOTE L - < 3% DMSO EXTRACT)**

UK	5 mg/m3	10 mg/m3	-	-
----	---------	----------	---	---

[cont...]

# SAFETY DATA SHEET

## ANTI-SEIZE SPRAY

Page: 5

### COPPER POWDER

UK	1mg/m <sup>3</sup>	2mg/m <sup>3</sup>	-	-
----	--------------------	--------------------	---	---

### GRAPHITE POWDER

UK	-	-	5 mg/m <sup>3</sup>	10 mg/m <sup>3</sup>
----	---	---	---------------------	----------------------

### ACETONE

UK	1210 mg/m <sup>3</sup>	3620 mg/m <sup>3</sup>	-	-
----	------------------------	------------------------	---	---

### CALCIUM CARBONATE

UK	-	-	4 mg/m <sup>3</sup>	-
----	---	---	---------------------	---

### DNEL/PNEC Values

#### Hazardous ingredients:

### COPPER POWDER

Type	Exposure	Value	Population	Effect
PNEC	Fresh water	0.0078 mg/l	-	-
PNEC	Fresh water sediments	87 mg/kg	-	-
PNEC	Marine water	0.0052 mg/l	-	-
PNEC	Marine sediments	676 mg/kg	-	-

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

**Respiratory protection:** Respiratory protection not normally required for normal use in well ventilated areas. Respiratory protection should be used in enclosed spaces, with poor ventilation, for extended repeated use, or where exposure limits may be exceeded. Recommended filter types are A1P2 or A2P2. Gas/vapour filter, type A: organic vapours (EN141).

**Hand protection:** Nitrile gloves.

**Eye protection:** Safety glasses with side-shields.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Aerosol

**Colour:** Dark brown

**Odour:** Characteristic odour

**Evaporation rate:** Fast

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Not miscible

**Viscosity:** Non-viscous

[cont...]

# SAFETY DATA SHEET

ANTI-SEIZE SPRAY

Page: 6

**Boiling point/range°C:** <0  
**Flammability limits %: lower:** 1.8  
**Flash point°C:** <-100  
**Vapour pressure:** >210

**Melting point/range°C:** <-130  
**upper:** 9.4  
**Autoflammability°C:** 430  
**Relative density:** <1

## 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

### 10.4. Conditions to avoid

**Conditions to avoid:** Direct sunlight. Heat. Sources of ignition.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong reducing agents.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

#### Hazardous ingredients:

#### HEPTANE & ISOMERS

DERMAL	RBT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>5000	mg/kg
VAPOURS	HMN	4H LC50	>20	mg/l

#### ACETONE

IVN	RAT	LD50	5500	mg/kg
ORL	MUS	LD50	3	gm/kg
ORL	RAT	LD50	5800	mg/kg

#### CALCIUM CARBONATE

ORAL	RAT	LD50	>2000	mg/kg
------	-----	------	-------	-------

[cont...]

# SAFETY DATA SHEET

## ANTI-SEIZE SPRAY

Page: 7

**Toxicity values:** No data available.

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat. May cause dizziness.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

## Section 12: Ecological information

### 12.1. Toxicity

#### Hazardous ingredients:

##### HEPTANE & ISOMERS

ALGAE	96H ErC50	> 10 - < 100	mg/l
DAPHNIA	96H ErC50	>1 - < 10	mg/l
Daphnia magna	96H ErC50	> 10 - < 10	-
FISH	96H LC50	>1 - < 10	mg/l

##### COPPER POWDER

RAINBOW TROUT ( <i>Oncorhynchus mykiss</i> )	96H LC50	0.19	mg/l
--	----------	------	------

##### ACETONE

BLUEGILL ( <i>Lepomis macrochirus</i> )	LC50	8300	mg/l
---	------	------	------

##### CALCIUM CARBONATE

ALGAE	72H ErC50	>100	mg/l
DAPHNIA	48H EC50	>100	mg/l
FISH	96H LC50	>100	g/l

### 12.2. Persistence and degradability

**Persistence and degradability:** Only slightly biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

### 12.4. Mobility in soil

**Mobility:** Highly volatile. Heavier than air.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

[cont...]

# SAFETY DATA SHEET

ANTI-SEIZE SPRAY

Page: 8

## 12.6. Other adverse effects

**Other adverse effects:** Harmful to aquatic organisms.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

### 14.1. UN number

**UN number:** UN1950

### 14.2. UN proper shipping name

**Shipping name:** AEROSOLS, Flammable

### 14.3. Transport hazard class(es)

**Transport class:** 2

### 14.4. Packing group

### 14.5. Environmental hazards

**Environmentally hazardous:** Yes

**Marine pollutant:** No

### 14.6. Special precautions for user

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.

This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.

H220: Extremely flammable gas.

H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H229: Pressurised container: May burst if heated

[cont...]



# SAFETY DATA SHEET

## ANTI-SEIZE SPRAY

Page: 9

H280: Contains gas under pressure; may explode if heated.

H302: Harmful if swallowed.

H304: May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H400: Very toxic to aquatic life.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

R12: Extremely flammable.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R67: Vapours may cause drowsiness and dizziness.

**Legend to abbreviations:** PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

IC50 = median inhibitory concentration

dw = dry weight

bw = body weight

cc = closed cup

oc = open cup

MUS = mouse

GPG = guinea pig

RBT = rabbit

HAM = hamster

HMN = human

MAM = mammal

PGN = pigeon

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = physico-chemical properties

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.