



Phase busbar, 3-phases, 16qmm, pin, 1m

Part no. Z-SV-16/2P+2N-2TE
Article no. 264914

Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ec@ss8.1-27-37-13-06 [ACN992008])

Number of phases			3
Number of poles			2
Suitable for number of devices			56
Pitch dimensions		mm	17.95
Cross section		mm ²	16
Length		mm	1000
Number of modular spacings			2
Rated permanent current I _u		A	63
Type of electric connection			Pin
Insulated			Yes
Rated surge voltage		kV	0
Conditioned rated short-circuit current I _q		kA	25
Max. rated operation voltage U _e		V	415
Rated short-time withstand current I _{cw}		kA	0
Suitable for devices with N-busbar			Yes
Suitable for devices with auxiliary switch			No