



LV HRC FUSE BASE 690V(1000V) SINGLE-POLE,  
160A, SIZE 0 PAD-TYPE TERMINAL

Model		
product brand name		SENTRON
Design of the product		LV HRC fuse base
General technical data		
Number of poles		1
Size of fuse system / acc. to DIN EN 60269-1		NH0
Usage category		Without
circuit-breaker / Design		3NH31
Electricity		
rated current I <sub>n</sub> / IEC, DIN/VDE / at 40 Cel	A	147.2
Current / with AC / Rated value	A	160
Product details		
Product component / Swivel mechanism		No
Connections		
Tightening torque / with screw-type terminals / maximum	N·m	14
Type of electrical connection • for main current circuit		With flat-type terminal flat connector
Mechanical Design		
Mounting type		fixed mounting
Mounting type / bus-mounting		No

<b>General Product Approval</b>	<b>Declaration of Conformity</b>	<b>Test Certificates</b>
---------------------------------	----------------------------------	--------------------------



KEMA



GOST



UL



EG-Konf.

[Type Test Certificates/Test Report](#)

<b>Shipping Approval</b>	<b>other</b>
--------------------------	--------------



GL

[Environmental Confirmations](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NH3120>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3NH3120/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NH3120](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NH3120)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015