

## Thread limit plug gauge with depth measurement

for standard metric ISO thread, scale interval 0.5 mm

leitech

### Application:

For testing threads and measuring thread depths in one pass.

### Execution:

- Thread inserts hardened and ground
- Black anodised aluminium housing
- Brushed chromium-plated scale
- Direct reading of the thread depth up to three times the thread diameter
- Measuring depth gradation of 0.5 mm on the scale sleeve



<b>Art. no.</b>	<b>32850 140</b>
<b>Brand</b>	LEITECH
<b>Manufacturer Part Number</b>	502903
<b>Thread type</b>	Metric thread
<b>Thread type x nominal diameter x pitch</b>	M14 x 2
<b>Tolerance class</b>	6H
<b>Measuring depth</b>	59 mm
<b>Reading Length Metrology</b>	0,5 mm
<b>Handle size</b>	T 500
<b>DIN</b>	13
<b>Gross Weight</b>	0.400 kg
<b>Product Group</b>	324