

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0347360027](#)  
**Status:** **Active**  
**Overview:** MX64 Sealed Connectors  
**Description:** 2.54mm Pitch MX64 Terminal, Silver Plating, 0.50-0.75mm<sup>2</sup>, Left Reel Payoff, Also used with MX123 Female Receptacle Housing

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31302-480-001 (PDF)</a>
<a href="#">Product Specification PS-33468-001-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification AS-33468-002-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification 313025040-000 (PDF)</a>	



**General**

Product Family	Crimp Terminals
Series	34736
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Left Reel Payoff
Crimp Quality Equipment	Yes
Overview	<a href="#">MX64 Sealed Connectors</a>
Product Name	MX123, MX64
UPC	884982893818

**Physical**

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	0.236/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.06mm
Wire Size AWG	N/A
Wire Size mm <sup>2</sup>	0.50-0.75

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33468-002-001
Packaging Specification	313025040-000, PK-31302-480-001
Product Specification	PS-33468-001-001
Sales Drawing	SD-33468-002-001

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[34736 Series](#)

**Use With**

MX64 Sealed Single Row Crimp Housing  
[31403](#) , MX123 Female Receptacle Housing  
[34566](#) , [34576](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
-------------	-----------

Hand Tool for MX64	<a href="#">638258400</a>
--------------------	---------------------------

ISO Terminal	
--------------	--

FineAdjust Applicator	<a href="#">639025300</a>
-----------------------	---------------------------

for MX64 ISO	
--------------	--

Terminal	
----------	--

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**