

## Solenoid valves VUVS/valve manifold VTUS

FESTO



★ /★ Festo core product range  
Covers 80% of your automation tasks

Worldwide: Always in stock  
Superb: Festo quality at an attractive price  
Easy: Reduces procurement and storing complexity

★ Generally ready for shipping ex works in 24 hours  
Held in stock in 13 service centres worldwide  
More than 2200 product

★ Generally ready for shipping ex works in 5 days  
Assembled for you in 4 service centres worldwide  
Up to  $6 \times 10^{12}$  variants per product series

Look for the star!

## Solenoid valves VUVS/valve manifold VTUS

Key features

FESTO



### Innovative

- A reliable, robust valve with a long service life
- Design principle:
  - Piston spool with sealing ring (VUVS-LK)
  - Disc seat soft-sealing (VUVS-LT)
  - Piston spool with sealing cartridge (VUVS-L)
- Flow rate up to 1800 l/min with VUVS-LK and VUVS-LT
- Flow rate up to 2300 l/min with VUVS-L
- Wide range of valve functions

### Flexible

- Operating voltage can be easily altered by changing the solenoid coil (VUVS-L and VUVS-LT)
- In-line valves can be used as individual valves or manifold valves
- Variable pressure zones
- Wide range of mounting options


### Reliable

- Ergonomic, reliable operation
- Reliable servicing thanks to valves that can be replaced quickly and easily

### Easy to install

- Pre-assembled units on rails
- Individual valves assembled ready for installation
- Common supply manifolds for mounting on one or both sides
- Secure mounting on wall or H-rail

### Product configurator



Configurable product

This product and all its options can be ordered using the configurator.

The configurator can be found under Products on the DVD or at

→ [www.festo.com/catalogue/...](http://www.festo.com/catalogue/)

Enter the type (or part number) in the search field:



- |           |         |
|-----------|---------|
| • VUVS-20 | 576516  |
| • VUVS-25 | 8022014 |
| • VUVS-30 | 8022017 |
| • VTUS-20 | 577304  |
| • VTUS-25 | 8022016 |
| • VTUS-30 | 8022019 |

## Solenoid valves VUVS/valve manifold VTUS



Key features

### Solenoid valves VUVS



In-line valve VUVS-LK as individual valve (piston slide valve)



In-line valve VUVS as individual valve (disk seat valve)




In-line valve VUVS-L as individual valve (piston slide valve)




In-line valves are designed to be used without pneumatic linking. All pneumatic connections are on the valve and can be equipped with fittings/tubing. By using a special seal set, the in-line valves can also be mounted on a manifold rail (pneumatic linking) as semi in-line valves.

### Valve manifold VTUS



### Equipment options

VUVS-LK



- 3/2- and 5/2-way valves, with solenoid coil
- Size 20 (21 mm), size 25 (26.5 mm) and size 30 (31 mm)

### Valve functions

- 3/2-way valve, normal position open, single solenoid:open, monostable:
- Internal pilot air supply
- Reset via pneumatic spring
- Direction of flow not reversible

### 5/2-way valve, single solenoid:

- Internal pilot air supply
- Reset via pneumatic spring
- Direction of flow not reversible

### 5/2-way valve, double solenoid:

- Internal pilot air supply
- Direction of flow not reversible



New

VUVS-LT20, VUVS-LT30

## Solenoid valves VUVS/valve manifold VTUS


Key features

FESTO

Equipment options	Valve functions	
VUVS-LT	<ul style="list-style-type: none"><li>• 3/2-, 2x 3/2- and 5/2-way valves, with or without solenoid coil</li><li>• Size 20 (21 mm), size 25 (26.5 mm) and size 30 (31 mm)</li></ul>	<ul style="list-style-type: none"><li>3/2-way valve, normal position open, monostable:<ul style="list-style-type: none"><li>• Internal/external pilot air supply</li><li>• Reset via mechanical spring</li><li>• Direction of flow not reversible</li></ul></li><li>2x 3/2-way valve, normal position-closed, single solenoid:<ul style="list-style-type: none"><li>• Internal/external pilot air supply</li><li>• Reset via mechanical spring</li><li>• Direction of flow not reversible</li></ul></li></ul>
	<ul style="list-style-type: none"><li>3/2-way valve, normal position closed, single solenoid:<ul style="list-style-type: none"><li>• Internal/external pilot air supply</li><li>• Reset via mechanical spring</li><li>• Direction of flow not reversible</li></ul></li></ul>	<ul style="list-style-type: none"><li>2x 3/2-way valve, 1x normally open, 1x normally closed, monostable:<ul style="list-style-type: none"><li>• Internal/external pilot air supply</li><li>• Reset via mechanical spring</li><li>• Direction of flow not reversible</li></ul></li></ul>
	<ul style="list-style-type: none"><li>2x 3/2-way valve, normal position-open, monostable:<ul style="list-style-type: none"><li>• Internal/external pilot air supply</li><li>• Reset via mechanical spring</li><li>• Direction of flow not reversible</li></ul></li></ul>	<ul style="list-style-type: none"><li>5/2-way valve, single solenoid:<ul style="list-style-type: none"><li>• Internal/external pilot air supply</li><li>• Reset via mechanical spring</li><li>• Direction of flow not reversible</li></ul></li></ul>
		<ul style="list-style-type: none"><li>5/2-way valve, double solenoid:<ul style="list-style-type: none"><li>• Internal/external pilot air supply</li><li>• Reset via mechanical spring</li><li>• Direction of flow not reversible</li></ul></li></ul>

## Solenoid valves VUVS/valve manifold VTUS

Key features

Equipment options	Valve functions
VUVS-L	<p></p> <ul style="list-style-type: none"> <li>• 3/2-, 5/2- and 5/3-way valves, with or without solenoid coil</li> <li>• Size 20 (21 mm), size 25 (26.5 mm) and size 30 (31 mm)</li> </ul> <p>3/2-way valve, normal position open, monostable:        • Internal/external pilot air supply        • Reset via pneumatic/mechanical spring        • Direction of flow can be reversed in the case of external pilot air supply</p> <p>3/2-way valve, normal position closed, single solenoid:        • Internal/external pilot air supply        • Reset via pneumatic/mechanical spring        • Direction of flow can be reversed in the case of external pilot air supply</p> <p>5/2-way valve, single solenoid:        • Internal/external pilot air supply        • Reset via pneumatic/mechanical spring        • Direction of flow can be reversed in the case of external pilot air supply</p>
VUVS-LT	<p>5/2-way valve, double solenoid:        • Internal/external pilot air supply        • Direction of flow can be reversed in the case of external pilot air supply</p> <p>5/3-way valve, mid-position exhausted, pressurised or closed:        • Internal/external pilot air supply        • Reset via mechanical spring        • Direction of flow can be reversed in the case of external pilot air supply</p>
	<p> Note</p> <p>The operating voltage of valves VUVS-L and VUVS-LT can be varied by changing the solenoid coil on the armature guide tube.</p>

### Key features

<ul style="list-style-type: none"> <li>• A maximum of 16 valve positions can be configured in the standard version (for VUVS-L variant only)</li> <li>• A maximum of 12 valve positions can be configured in the compact version (maximum of 10 valve positions for VUVS-LK variant)</li> </ul>	<ul style="list-style-type: none"> <li>• Valve positions 2 ... 10 can be configured in increments of 1, valve positions 10 ... 16 in increments of 2</li> </ul>	<ul style="list-style-type: none"> <li>• Manifold block with a maximum of 10 valve positions</li> <li>• Extension module with 2 valve positions</li> <li>• Common supply manifold with a maximum of 10 valve positions</li> </ul>	<ul style="list-style-type: none"> <li>• Creation of pressure zones (maximum 9 pressure zones in the case of a valve manifold with 16 valve positions)</li> </ul>
---	---	---	---

### Design


Valve replacement	Extension
Each valve is attached to the manifold block using two screws. The appropriate seal is mounted on the valve.	<p>This means that the valves can be easily replaced.</p> <p>Valve positions covered with blanking plates can be replaced with valves at a later date. The dimensions, mounting points and existing pneumatic installations remain unchanged.</p> <p>Extension modules with two valve positions are available for the standard manifold block. A manifold block can be extended with a maximum of three extension modules.</p>

## Solenoid valves VUVS/valve manifold VTUS

Key features


### Standard manifold block (not for VUVS-LK valves)

For 3/2-way valves



- Connection  
Size 20: G3/8  
Size 25: G1/2  
Size 30: G3/4
- For valves with external pilot air supply
- Maximum 10 valve positions


For 5/2- and 5/3-way valves



- Connection  
Size 20: G3/8  
Size 25: G1/2  
Size 30: G3/4
- For valves with external pilot air supply
- Maximum 10 valve positions


### Manifold block extension module for standard manifold block (not for valves VUVS-LK)

For 3/2-way valves



- Connection  
Size 20: G3/8  
Size 25: G1/2  
Size 30: G3/4
- Maximum two valve positions


For 5/2- and 5/3-way valves



- Connection  
Size 20: G3/8  
Size 25: G1/2  
Size 30: G3/4
- Maximum two valve positions


### Compact manifold block

For 3/2-way valves



- Connection  
Size 20: G1/4  
Size 25: G3/8  
Size 30: G1/2
- Maximum 10 valve positions


For 5/2- and 5/3-way valves



- Connection  
Size 20: G1/4  
Size 25: G3/8  
Size 30: G1/2
- Maximum 10 valve positions


### Common supply manifold

Mounting on both sides



- Connection  
Size 20: G3/8  
Size 25: G1/2  
Size 30: G3/4
- Maximum 10 valve positions

Mounting on one side



- Connection  
Size 20: G3/8  
Size 25: G1/2  
Size 30: G3/4
- Maximum 4 valve positions

### Blanking plate for unused valve position



For covering unused valve positions

### Supply plate



For additional air supply and exhaust via a valve position

### Separator for pressure zones



For creating pressure zones (maximum 9 pressure zones permitted)

### Note

A filter must be installed upstream of valves operated in vacuum mode. This prevents any foreign matter in

the intake air getting into the valve (e.g. when operating a suction cup).

# Solenoid valves VUVS/valve manifold VTUS

FESTO

Key features – Pneumatics

## Creating pressure zones and separating exhaust air

Compressed air is supplied and exhausted via the manifold block/supply manifold and via supply plates. The position of the supply plates and duct separations can be freely selected with the VTUS.

A pressure zone is created by isolating the internal ducts between the valve positions using an appropriate separator.

The separator can be used in the following ducts:

- Duct 1
- Duct 3
- Duct 5



- Use a separator if the exhaust air pressures are high
- Use at least one supply plate/supply for each pressure zone
- Pressure zone separation is not possible in ducts 12 and 14 (pilot air supply)

## Duct separation

	Description
	<p>The pressure zones can be freely configured with the VTUS. The following duct separations are possible:</p> <ul style="list-style-type: none"> <li>• Duct 1 closed</li> <li>• Duct 1/3/5 closed</li> <li>• Duct 3/5 closed</li> </ul>
	<p>The number of pressure zones with the VTUS is limited by the number of valve positions on the manifold block/supply manifold. Note that each supply plate occupies one valve position. There must always be at least two valve positions between two separators. In the case of a maximum extension of 16 valve positions, a maximum of 9 pressure zones can be created.</p>


# Solenoid valves VUVS/valve manifold VTUS

Key features – Pneumatics, VUVS-LK

FESTO


## Size 20 – Standard nominal flow rate $q_{nN}$ , with several valves n switched in parallel

For 3/2-way valves



— Standard nominal flow rate per valve on manifold rail compact


For 5/2-way valves



— Standard nominal flow rate per valve on manifold rail compact


## Size 25 – Standard nominal flow rate $q_{nN}$ , with several valves n switched in parallel

For 3/2-way valves



— Standard nominal flow rate per valve on manifold rail compact

For 5/2-way valves




— Standard nominal flow rate per valve on manifold rail compact

## Solenoid valves VUVS/valve manifold VTUS


Key features – Pneumatics, VUVS-LT

### Size 20 – Standard nominal flow rate $q_{nN}$ , with several valves $n$ switched in parallel


For 3/2-way valves



For 5/2-way valves, flow direction 1 → 2



For 5/2-way valves, flow direction 1 → 4




## Solenoid valves VUVS/valve manifold VTUS

Key features – Pneumatics, VUVS-LT

### Size 20 – Standard nominal flow rate $q_{nN}$ , with several valves n switched in parallel


For 2x 3/2-way valves

One valve function per valve position in open switching position



For 2x 3/2-way valves

Both valve functions per valve position simultaneously in open switching position




## Solenoid valves VUVS/valve manifold VTUS

FESTO


Key features – Pneumatics, VUVS-LT

### Size 25 – Standard nominal flow rate $q_{nN}$ , with several valves $n$ switched in parallel


For 3/2-way valves



For 5/2-way valves, flow direction 1 → 2



For 5/2-way valves, flow direction 1 → 4



# Solenoid valves VUVS/valve manifold VTUS


Key features – Pneumatics, VUVS-LT

FESTO

## Size 25 – Standard nominal flow rate $q_{nN}$ , with several valves $n$ switched in parallel


For 2x 3/2-way valves

One valve function per valve position in open switching position



For 2x 3/2-way valves

Both valve functions per valve position simultaneously in open switching position




## Solenoid valves VUVS/valve manifold VTUS

Key features – Pneumatics, VUVS-LT


### Size 30 – Standard nominal flow rate $q_{nN}$ , with several valves $n$ switched in parallel

For 3/2-way valves




- Standard nominal flow rate per valve on manifold rail standard
- - - Standard nominal flow rate per valve on manifold rail compact

### For 5/2-way valves, flow direction 1→2



- Standard nominal flow rate per valve on manifold rail standard
- - - Standard nominal flow rate per valve on manifold rail compact

### For 5/2-way valves, flow direction 1→4



- Standard nominal flow rate per valve on manifold rail standard
- - - Standard nominal flow rate per valve on manifold rail compact



New

VUVS-LT20, VUVS-LT30

## Solenoid valves VUVS/valve manifold VTUS


Key features – Pneumatics, VUVS-LT

FESTO

### Size 30 – Standard nominal flow rate $q_{nN}$ , with several valves n switched in parallel


For 2x 3/2-way valves

One valve function per valve position in open switching position



For 2x 3/2-way valves

Both valve functions per valve position simultaneously in open switching position




# Solenoid valves VUVS/valve manifold VTUS

FESTO


Key features – Pneumatics, VUVS-L

## Size 20 – Standard nominal flow rate $q_{nN}$ , with several valves $n$ switched in parallel

For 3/2-way valves




For 5/2- and 5/3-way valves




## Size 25 – Standard nominal flow rate $q_{nN}$ , with several valves $n$ switched in parallel

For 3/2-way valves



For 5/2- and 5/3-way valves




# Solenoid valves VUVS/valve manifold VTUS

Key features – Pneumatics, VUVS-L


FESTO

## Size 30 – Standard nominal flow rate $q_{nN}$ , with several valves $n$ switched in parallel

For 3/2-way valves



For 5/2- and 5/3-way valves




## Solenoid valves VUVS/valve manifold VTUS


Key features – Pneumatics, VUVS-LT

### Size 20 – Pilot pressure p2 as a function of working pressure p1


For 3/2-way valves



For 5/2-way valves, single solenoid



For 5/2-way valves, double solenoid




# Solenoid valves VUVS/valve manifold VTUS

Key features – Pneumatics, VUVS-LT


FESTO

## Size 25 – Pilot pressure p2 as a function of working pressure p1


For 3/2-way valves



For 5/2-way valves, single solenoid



For 5/2-way valves, double solenoid




## Solenoid valves VUVS/valve manifold VTUS


Key features – Pneumatics, VUVS-LT

### Size 30 – Pilot pressure p2 as a function of working pressure p1


For 3/2-way valves



For 5/2-way valves, single solenoid



For 5/2-way valves, double solenoid



— VUVS-LT30-M52-MZD (0-60°C)  
- - - VUVS-LT30-M52-MZD (-10-0°C)

# Solenoid valves VUVS/valve manifold VTUS

Key features – Pneumatics

FESTO

## Mounting valve manifold VTUS


Sturdy valve manifold owing to:

- Four through-holes for wall mounting
- H-rail mounting

- - Note

Use the thread M4/M5 provided on the manifold block for earthing the valve manifold.


### Wall mounting



Sturdy wall mounting of the manifold block using four through-holes.

[1] Earth terminal

### H-rail mounting



The H-rail mounting VAME-T-M... consists of two mounting clips. These are screwed to the manifold block on the left and right.

The valve manifold VTUS is then lowered onto the H-rail from above (arrow A) and clipped into the H-rail at the bottom (arrow B).

- - Note

- Note the max. tightening torque of the screws for H-rail mounting
- Only horizontal H-rail mounting is permissible
- Mounting only possible on H-rail TH 35... to EN 60715
- Vibration/shock loads are not permissible with H-rail mounting
- Further note on assembly  
→ Assembly instructions for H-rail mounting VAME-T-M...


# Solenoid valves VUVS/valve manifold VTUS

FESTO

Key features – Assembly

## Mounting individual valve VUVS

Wall mounting




For mounting individual valves on a flat surface, e.g. aluminium profile systems.

The solenoid valves are provided with two through-holes for attaching to the wall mounting VAME-B10-20-W.

The relevant screw set is included when the wall mounting VAME-B10-20-W is ordered.

Foot mounting



For mounting individual valves on a flat surface, e.g. aluminium profile systems.

The solenoid valves are provided with two through-holes for attaching to the foot mounting VAME-B10-...-A.

The relevant screw set is included when the foot mounting VAME-B10-...-A is ordered.



**New**  
VUVS-LT20, VUVS-LT30

**FESTO**

## Solenoid valves VUVS/valve manifold VTUS




Product range overview

Valve	Size	Working port	Order code for valves and flow rate [l/min]										→ Page/ Internet
			M32C	M32U	T32C	T32U	T32H	M52	B52	P53C	P53U	P53E	
3/2-way valve VUVS-LK													
A small rectangular solenoid valve with two ports and a central body.	20	G1/8	■ 550	—	—	—	—	—	—	—	—	—	58
	25	G1/4	■ 1000	—	—	—	—	—	—	—	—	—	68
	30	G3/8	■ 1600	—	—	—	—	—	—	—	—	—	78
5/2-way valve VUVS-LK													
A larger rectangular solenoid valve with three ports and a central body.	20	G1/8	—	—	—	—	—	■ 550	■ 550	—	—	—	58
	25	G1/4	—	—	—	—	—	■ 1000	■ 1000	—	—	—	68
	30	G3/8	—	—	—	—	—	■ 1600	■ 1600	—	—	—	78
3/2-way valve VUVS-LT													
A small rectangular solenoid valve with three ports and a central body.	20	G1/8	■ 600	■ 600	—	—	—	—	—	—	—	—	88
	25	G1/4	■ 1000	■ 1000	—	—	—	—	—	—	—	—	101
	30	G3/8	■ 1600	■ 1600	—	—	—	—	—	—	—	—	126
2x 3/2-way valve VUVS-LT													
A large rectangular solenoid valve with six ports and a central body.	20	G1/8	—	—	■ 600	■ 600	■ 600	—	—	—	—	—	88
	25	G1/4	—	—	■ 1000	■ 1000	■ 1000	—	—	—	—	—	101
	30	G3/8	—	—	■ 1600	■ 1600	■ 1600	—	—	—	—	—	127
5/2-way valve VUVS-LT													
A large rectangular solenoid valve with five ports and a central body.	20	G1/8	—	—	—	—	—	■ 500	■ 500	—	—	—	88
	25	G1/4	—	—	—	—	—	■ 1000	■ 1000	—	—	—	101
	30	G3/8	—	—	—	—	—	■ 1800	■ 1800	—	—	—	128

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**



Product range overview





Valve	Size	Working port	Order code for valves and flow rate [l/min]										→ Page/ Internet
			M32C	M32U	T32C	T32U	T32H	M52	B52	P53C	P53U	P53E	
<b>3/2-way valve VUVS-L</b>													
	20	G1/8	■ 700	■ 700	—	—	—	—	—	—	—	—	133
	25	G1/4	■ 1000	■ 1000	—	—	—	—	—	—	—	—	148
	30	G3/8	■ 2300	■ 2300	—	—	—	—	—	—	—	—	166
<b>5/2-way valve VUVS-L</b>													
	20	G1/8	—	—	—	—	—	■ 700	■ 700	—	—	—	133
	25	G1/4	—	—	—	—	—	■ 1300	■ 1300	—	—	—	148
	30	G3/8	—	—	—	—	—	■ 2300	■ 2300	—	—	—	166
<b>5/3-way valve VUVS-L</b>													
	20	G1/8	—	—	—	—	—	—	■ 700	■ 600	■ 600	■ 600	133
	25	G1/4	—	—	—	—	—	—	■ 1200	■ 1000	■ 1000	■ 1000	148
	30	G3/8	—	—	—	—	—	—	■ 2000	■ 1600	■ 1600	■ 1600	166

# Solenoid valves VUVS/valve manifold VTUS

Product range overview

**FESTO**

Design type	Size	Description	➔ Page/ Internet
Manifold block for 3/2-way valves, standard (not for valves VUVS-LK)			
	20	VABM-B10-20E-G38- ... P3	Connection size G3/8
	25	VABM-B10-25E-G12- ... P3	Connection size G1/2
	30	VABM-B10-30E-G34- ... -P3	Connection size G3/4
Manifold block extension module for 3/2-way valves, standard (not for valves VUVS-LK)			
	20	VABM-B10-20EEE-G38- ... -P3	Connection size G3/8
	25	VABM-B10-25EEE-G12- ... -P3	Connection size G1/2
	30	VABM-B10-30EEE-G34- ... -P3	Connection size G3/4
Manifold block for 5/2- and 5/3-way valves, standard			
	20	VABM-B10-20E-G38- ...	Connection size G3/8
	25	VABM-B10-25E-G12- ...	Connection size G1/2
	30	VABM-B10-30E-G34- ...	Connection size G3/4
Manifold block extension module for 5/2- and 5/3-way valves, standard			
	20	VABM-B10-20EEE-G38- ...	Connection size G3/8
	25	VABM-B10-25EEE-G12- ...	Connection size G1/2
	30	VABM-B10-30EEE-G34- ...	Connection size G3/4

Design type	Size	Description	➔ Page/ Internet
Manifold block for 3/2-way valves, compact			
	20	VABM-B10-20S-G14- ... P3	Connection size G1/4
	25	VABM-B10-25S-G38- ... P3	Connection size G3/8
	30	VABM-B10-30S-G12- ... -P3	Connection size G1/2
Manifold block for 5/2- and 5/3-way valves, compact			
	20	VABM-B10-20S-G14- ...	Connection size G1/4
	25	VABM-B10-25S-G38- ...	Connection size G3/8
	30	VABM-B10-30S-G12- ...	Connection size G1/2
Common supply manifold, for mounting on both sides			
	20	VABM-B10-20-G38- ... -P53	Connection size G3/8
	25	VABM-B10-25-G12- ... -P53	Connection size G1/2
	30	VABM-B10-30-G34- ... -P53	Connection size G3/4
Common supply manifold, for mounting on one side			
	20	VABM-B10-20-G38- ... -P53-E	Connection size G3/8
	25	VABM-B10-25-G12- ... -P53-E	Connection size G1/2
	30	VABM-B10-30-G34- ... -P53-E	Connection size G3/4

## Solenoid valves VUVS/valve manifold VTUS

Overview of valve functions

Valve	Order code for valves	Description	VUVS-LK			VUVS-LT			VUVS-L		
			Size			Size			Size		
			20	25	30	20	25	30	20	25	30
<b>3/2-way valve, normally closed, pneumatic spring</b>											
	M32C-A	Internal pilot air supply, not reversible	■	■	■	-	-	-	-	-	-
		Internal pilot air supply, not reversible	-	-	-	-	-	-	■	■	■
		External pilot air supply, reversible	-	-	-	-	-	-	■	■	■
<b>3/2-way valve, normally closed, pneumatical/mechanical spring</b>											
	M32C-M	• Internal pilot air supply, not reversible • Reset: mechanical spring, supported internally by pneumatic spring	-	-	-	-	-	-	■	-	-
		• External pilot air supply, reversible • Reset: mechanical spring, supported internally by pneumatic spring	-	-	-	-	-	-	■	-	-
<b>3/2-way valve, normally closed, mechanical spring</b>											
	M32C-M	Internal pilot air supply, not reversible	-	-	-	■	■	■	-	■	■
		External pilot air supply, not reversible	-	-	-	■	■	■	-	-	-
		External pilot air supply, reversible	-	-	-	-	-	-	-	■	■



**New**  
VUVS-LT20, VUVS-LT30

## Solenoid valves VUVS/valve manifold VTUS







Overview of valve functions

**FESTO**

Valve	Order code for valves	Description	VUVS-LK			VUVS-LT			VUVS-L		
			Size			Size			Size		
			20	25	30	20	25	30	20	25	30
3/2-way valve, normally open, pneumatic spring											
10	M32U-A	Internal pilot air supply, not reversible	-	-	-	-	-	-	■	■	■
10		External pilot air supply, reversible	-	-	-	-	-	-	■	■	■
3/2-way valve, normally open, pneumatical/mechanical spring											
10	M32U-M	• External pilot air supply, reversible • Reset: mechanical spring, supported internally by pneumatic spring	-	-	-	-	-	-	■	-	-
10		• External pilot air supply, reversible • Reset: mechanical spring, supported internally by pneumatic spring	-	-	-	-	-	-	■	-	-
3/2-way valve, normally open, mechanical spring											
10	M32U-M	Internal pilot air supply, not reversible	-	-	-	■	■	■	-	■	■
10		External pilot air supply, not reversible	-	-	-	■	■	■	-	-	-
10		External pilot air supply, reversible	-	-	-	-	-	-	■	■	

## Solenoid valves VUVS/valve manifold VTUS

Overview of valve functions

Valve	Order code for valves	Description	VUVS-LK			VUVS-LT			VUVS-L		
			Size			Size			Size		
			20	25	30	20	25	30	20	25	30
2x3/2-way valve, normally closed, mechanical spring											
	T32C	Internal pilot air supply, not reversible	-	-	-	■	■	■	-	-	-
	T32C	External pilot air supply, not reversible	-	-	-	■	■	■	-	-	-
2x3/2-way valve, normally open, mechanical spring											
	T32U	Internal pilot air supply, not reversible	-	-	-	■	■	■	-	-	-
	T32U	External pilot air supply, not reversible	-	-	-	■	■	■	-	-	-
2x 3/2-way valve, 1x normally open, 1x normally closed, mechanical spring											
	T32H	Internal pilot air supply, not reversible	-	-	-	■	■	■	-	-	-
	T32H	External pilot air supply, not reversible	-	-	-	■	■	■	-	-	-



**New**  
VUVS-LT20, VUVS-LT30

**FESTO**

## Solenoid valves VUVS/valve manifold VTUS

Overview of valve functions

Valve	Order code for valves	Description	VUVS-LK			VUVS-LT			VUVS-L		
			Size			Size			Size		
			20	25	30	20	25	30	20	25	30
5/2-way valve, single solenoid, pneumatic spring											
14	M52	Internal pilot air supply, not reversible	■	■	■	-	-	-	-	-	-
14		Internal pilot air supply, not reversible	-	-	-	-	-	-	■	■	■
14		External pilot air supply, reversible	-	-	-	-	-	-	■	■	■
5/2-way valve, single solenoid, mechanical spring											
14	M52	• Internal pilot air supply, not reversible • Reset: mechanical spring, supported internally by pneumatic spring	-	-	-	■	■	■	■	■	■
14		External pilot air supply, reversible	-	-	-	-	-	-	■	■	■
14		• External pilot air supply, not reversible • Reset: mechanical spring, supported internally by pneumatic spring	-	-	-	■	■	■	-	-	-
5/2-way valve, double solenoid											
14	B52	Internal pilot air supply, not reversible	■	■	■	-	-	-	-	-	-
14		• Internal pilot air supply, not reversible • Holding the switching position: via latch	-	-	-	-	■	-	-	-	-
14		Internal pilot air supply, not reversible	-	-	-	■	-	■	■	■	■
14		• External pilot air supply, not reversible • Holding the switching position: via latch	-	-	-	■	■	■	-	-	-
14		External pilot air supply, reversible	-	-	-	-	-	-	■	■	■

# Solenoid valves VUVS/valve manifold VTUS

FESTO

Overview of valve functions


Valve	Order code for valves	Description	VUVS-L		
			Size		
			20	25	30
5/3-way valve, mechanical spring, closed					
	P53C	Internal pilot air supply, not reversible	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
		External pilot air supply, reversible	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
5/3-way valve, mechanical spring, pressurised					
	P53U	Internal pilot air supply, not reversible	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
		External pilot air supply, reversible	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
5/3-way valve, mechanical spring, exhausted					
	P53E	Internal pilot air supply, not reversible	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
		External pilot air supply, reversible	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>

# Solenoid valves VUVS/valve manifold VTUS

Peripherals overview VUVS-LK

FESTO

Manifold block for 3/2-way valves



# Solenoid valves VUVS/valve manifold VTUS

FESTO

Peripherals overview VUVS-LK


Designation	Description	➔ Page/Internet
[1] H-rail	–	–
[2] H-rail mounting	For H-rail mounting	197
[3] Compact manifold block	For 3/2-way valves, no port for external pilot air supply	193
[6] Separator	For creating pressure zones in ports 1 and 3	197
[7] Blanking plug	For ports 1 and 3, supply and exhaust ports	197
[8] Push-in fitting	For ports 1 and 3, supply and exhaust ports	196
[9] Silencer	For port 3, exhaust	197
[12] Supply plate	For additional air supply and exhaust via a valve position	195
[13] Cover plate	For covering unused valve positions	195
[14] Solenoid valve	3/2-way valve, with solenoid coil	57
[15] Silencer	For port 3, exhaust	197
[16] Push-in fitting	For ports 1 and 3, supply and exhaust ports with supply plate, For port 2, working port, on the valve	196
[17] Illuminating seal	For indicating the switching status	66
[18] Plug socket with cable	For solenoid valves VUVS	66
[19] Plug socket	For solenoid valves VUVS	66

# Solenoid valves VUVS/valve manifold VTUS

Peripherals overview VUVS-LK

**FESTO**

## Manifold block for 5/2-way valves



Designation	Description	➔ Page/Internet
1 H-rail	-	-
2 H-rail mounting	For H-rail mounting	197
3 Compact manifold block	For 5/2-way valves, no port for external pilot air supply	193
8 Blanking plug	For ports 1, 3 and 5, supply and exhaust ports	197
9 Push-in fitting	For ports 1, 3 and 5, supply and exhaust ports	196
10 Silencer	For ports 3 and 5, exhaust	197
11 Separator	For creating pressure zones in ports 1, 3 and 5	197
12 Supply plate	For additional air supply and exhaust via a valve position	195

# Solenoid valves VUVS/valve manifold VTUS

FESTO

Peripherals overview VUVS-LK


Designation	Description	➔ Page/Internet
[13] Cover plate	For covering unused valve positions	195
[14] Solenoid valve	5/2-way double solenoid valve, with solenoid coil	57
[15] Solenoid valve	5/2-way valve, single solenoid, with solenoid coil	57
[16] Silencer	For ports 3 and 5, exhaust	197
[17] Push-in fitting	For ports 1, 3 and 5, supply and exhaust ports with supply plate For ports 2 and 4, working port, on the valve	196
[18] Illuminating seal	For indicating the switching status	66
[19] Plug socket with cable	For solenoid valves VUVS	66
[20] Plug socket	For solenoid valves VUVS	66

# Solenoid valves VUVS/valve manifold VTUS

Peripherals overview VUVS-LK

FESTO

## Common supply manifold for mounting on both sides




Designation	Description	➔ Page/Internet
[1] Common supply manifold	–	194
[2] Supply plate	For additional air supply via a valve position	195
[3] Push-in fitting	For connection 1	196
[4] Cover plate	For covering unused valve positions	195
[5] Solenoid valve	3/2-way valve, with solenoid coil	57
[6] Push-in fitting	For ports 2, 4, working port	196
[7] Illuminating seal	For indicating the switching status	66
[8] Plug socket with cable	For solenoid valves VUVS	66
[9] Plug socket	For solenoid valves VUVS	66
[10] Solenoid valve	5/2-way double solenoid valve, with solenoid coil	57
[11] Solenoid valve	5/2-way valve, single solenoid, with solenoid coil	57
[12] Silencer	For ports 3 and 5, exhaust, on the valve	197
[13] Push-in fitting	For ports 3 and 5, exhaust, on the valve	196
[14] Blanking plug	For port 1, supply port	197
[15] Separator	For creating pressure zones	197
[16] Push-in fitting	For port 1, supply port	196

# Solenoid valves VUVS/valve manifold VTUS

FESTO

Peripherals overview VUVS-LK

## Common supply manifold for mounting on one side




Designation	Description	➔ Page/Internet
[1] Common supply manifold	–	194
[2] Supply plate	For additional air supply via a valve position	195
[3] Push-in fitting	For port 1, supply port	196
[4] Cover plate	For covering unused valve positions	195
[5] Solenoid valve	3/2-way valve, with solenoid coil	65
[6] Push-in fitting	For ports 2 and 4, working port	196
[7] Illuminating seal	For indicating the switching status	66
[8] Plug socket with cable	For solenoid valves VUVS	66
[9] Plug socket	For solenoid valves VUVS	66
[10] Solenoid valve	5/2-way double solenoid valve, with solenoid coil	57
[11] Solenoid valve	5/2-way valve, single solenoid, with solenoid coil	57
[12] Silencer	For ports 3 and 5, exhaust, on the valve	197
[13] Push-in fitting	For ports 3 and 5, on the valve	196
[14] Blanking plug	For port 1, supply port	197
[15] Separator	For creating pressure zones	197
[16] Push-in fitting	For port 1, supply port	196

## Solenoid valves VUVS/valve manifold VTUS

Peripherals overview VUVS-LT, VUVS-L

**FESTO**

Manifold block for 3/2-way valves



Designation	Description	➔ Page/Internet
1 H-rail	–	–
2 H-rail mounting	For H-rail mounting	197
3 Compact manifold block	For 3/2-way valves, no port for external pilot air supply	193
4 standard manifold block	For 3/2-way valves, with port 10/12 for external pilot air supply	193
5 Extension module	For standard manifold block, with port 10/12 for external pilot air supply	193
6 Separator	For creating pressure zones in ports 1 and 3	197
7 Blanking plug	For ports 1 and 3, supply and exhaust ports	197
8 Push-in fitting	For ports 1 and 3, supply and exhaust ports	196
9 Silencer	For port 3, exhaust	197
10 Push-in fitting	For port 10/12, external pilot air supply, for standard manifold block only	196
11 Blanking plug	For port 10/12, external pilot air supply, for standard manifold block only	197
12 Supply plate	For additional air supply and exhaust via a valve position	195
13 Cover plate	For covering unused valve positions	195
14 Solenoid valve	3/2-way valve, with solenoid coil	57

## Solenoid valves VUVS/valve manifold VTUS


Peripherals overview VUVS-LT, VUVS-L

Designation	Description	➔ Page/Internet
[15] Solenoid valve	2x 3/2-way valve, with solenoid coil	57
[16] Silencer	For port 3, exhaust	197
[17] Push-in fitting	For ports 1 and 3, supply and exhaust ports with supply plate, For port 2, working port, on the valve	196
[18] Illuminating seal	For indicating the switching status	145
[19] Plug socket with cable	For solenoid valves VUVS	145
[20] Plug socket	For solenoid valves VUVS	145

## Solenoid valves VUVS/valve manifold VTUS

Peripherals overview VUVS-LT, VUVS-L

Manifold block for 5/2- and 5/3-way valves



Designation	Description	➔ Page/Internet
[1] H-rail	-	-
[2] H-rail mounting	For H-rail mounting	197
[3] Compact manifold block	For 5/2- and 5/3-way valves, no port for external pilot air supply	193
[4] standard manifold block	For 5/2- and 5/3-way valves, with ports 12 and 14 for external pilot air supply	193
[5] Extension module	For standard manifold block, with ports 12 and 14 for external pilot air supply	193
[6] Blanking plug	For ports 12 and 14, external pilot air supply, for standard manifold block only	197
[7] Push-in fitting	For ports 12 and 14, external pilot air supply, for standard manifold block only	196
[8] Blanking plug	For ports 1, 3 and 5, supply and exhaust ports	197
[9] Push-in fitting	For ports 1, 3 and 5, supply and exhaust ports	196
[10] Silencer	For ports 3 and 5, exhaust	197
[11] Separator	For creating pressure zones in ports 1, 3 and 5	197
[12] Supply plate	For additional air supply and exhaust via a valve position	195

## Solenoid valves VUVS/valve manifold VTUS

Peripherals overview VUVS-LT, VUVS-L


Designation	Description	➔ Page/Internet
[13] Cover plate	For covering unused valve positions	195
[14] Solenoid valve	5/3-way valve and 5/2-way valve, double solenoid, with solenoid coil	57
[15] Solenoid valve	5/2-way valve, single solenoid, with solenoid coil	57
[16] Silencer	For ports 3 and 5, exhaust	197
[17] Push-in fitting	For ports 1, 3 and 5, supply and exhaust ports with supply plate For ports 2 and 4, working port, on the valve	196
[18] Illuminating seal	For indicating the switching status	145
[19] Plug socket with cable	For solenoid valves VUVS	145
[20] Plug socket	For solenoid valves VUVS	145

## Solenoid valves VUVS/valve manifold VTUS

Peripherals overview VUVS-LT, VUVS-L

**FESTO**

### Supply manifold for mounting on both sides




Designation	Description	➔ Page/Internet
[1] Common supply manifold	–	194
[2] Supply plate	For additional air supply via a valve position	195
[3] Push-in fitting	For connection 1	196
[4] Cover plate	For covering unused valve positions	195
[5] Solenoid valve	3/2-way valve, with solenoid coil	57
[6] Push-in fitting	For ports 2, 4, working port	196
[7] Illuminating seal	For indicating the switching status	145
[8] Plug socket with cable	For solenoid valves VUVS	145
[9] Plug socket	For solenoid valves VUVS	145
[10] Solenoid valve	5/3-way valve and 5/2-way valve, double solenoid, with solenoid coil 2x 3/2-way valve with solenoid coil	57
[11] Solenoid valve	5/2-way valve, single solenoid, with solenoid coil	57
[12] Silencer	For ports 3 and 5, exhaust, on the valve	197
[13] Push-in fitting	For ports 3 and 5, exhaust, on the valve	196
[14] Blanking plug	For port 1, supply port	197
[15] Separator	For creating pressure zones	197
[16] Push-in fitting	For port 1, supply port	196

## Solenoid valves VUVS/valve manifold VTUS

Peripherals overview VUVS-LT, VUVS-L

### Common supply manifold for mounting on one side



Designation	Description	→ Page/Internet
[1] Common supply manifold	–	194
[2] Supply plate	For additional air supply via a valve position	195
[3] Push-in fitting	For port 1, supply port	196
[4] Cover plate	For covering unused valve positions	195
[5] Solenoid valve	3/2-way valve, with solenoid coil	57
[6] Push-in fitting	For ports 2 and 4, working port	196
[7] Illuminating seal	For indicating the switching status	145
[8] Plug socket with cable	For solenoid valves VUVS	145
[9] Plug socket	For solenoid valves VUVS	145
[10] Solenoid valve	5/3-way valve and 5/2-way valve, double solenoid, with solenoid coil 2x 3/2-way valve with solenoid coil	57
[11] Solenoid valve	5/2-way valve, single solenoid, with solenoid coil	57
[12] Silencer	For ports 3 and 5, exhaust, on the valve	197
[13] Push-in fitting	For ports 3 and 5, on the valve	196
[14] Blanking plug	For port 1, supply port	197
[15] Separator	For creating pressure zones	197
[16] Push-in fitting	For port 1, supply port	196

## Valve manifold VTUS

Technical data – Valve manifold

-  - Flow rate
- Size 20:  
up to 700 l/min
- Size 25:  
up to 1300 l/min
- Size 30:  
up to 2300 l/min



General technical data			
Size	20	25	30
Valve manifold configuration	Fixed grid		
Valve width [mm]	21	26.5	31
Valve design	VUVS-L VUVS-LT VUVS-LK		
Electrical actuation	Individual connection		
Reset method for valves	VUVS-L	Pneumatic or mechanical spring	
	VUVS-LT	Mechanical spring	
	VUVS-LK	Pneumatic spring	
Pilot air supply	Internal or external		
Flow direction	VUVS-L	Reversible with restrictions	
	VUVS-LT	Non-reversible	
	VUVS-LK	Non-reversible	
Suitable for vacuum	VUVS-L	Yes with external pilot air supply	
	VUVS-LT	Yes, with external pilot air supply (not for M52/B52 valves)	No
	VUVS-LK	No	
Overlap	VUVS-L	Positive overlap	
	VUVS-LT	Underlap	
	VUVS-LK	Positive overlap	
Sealing principle	Soft		
Max. number of valve positions	16 (a maximum of 18 valve positions with extension for standard manifold block)		
Max. no. of pressure zones	9		
Exhaust function	With flow control		
Type of actuation	Electrical		
Nominal operating voltage	[V DC]	12, 24	
	[V AC]	24, 110, 120, 230, 240	
Standard nominal flow rate qnN	[l/min]	500 ... 700	1000 ... 1300
Pilot air connection	Standard manifold block	12/14	G1/8
	Compact manifold block	12/14	On the valve
	Common supply manifold	12/14	On the valve
Pilot exhaust air port	82/84		
Mounting position	Optional		
Degree of protection	IP65, IP67 With plug socket, to IEC 60529		
Permissible voltage fluctuations	[%]	± 10	

# Valve manifold VTUS

Technical data – Valve manifold

Materials		
Seals	VUVS-L	HNBR, NBR
	VUVS-LT	HNBR, NBR, TPE-U(PU)
	VUVS-LK	HNBR, NBR
Note on materials	RoHS-compliant	

ATEX	
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T4 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T115°C X Dc
Explosion-proof ambient temperature rating [°C]	-10 °C <= Ta <= +60 °C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Operating and environmental conditions			
Valve design	Piston spool	Disc seat	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure			
With external pilot air [bar]	-0.9 ... +10	-0.9 ... +10 (M32, T32) +1.5 ... +10 (B52) +2.5 ... +10 (M52)	
With internal pilot air [bar]	+1.5 ... +10 +2.5 ... +10 (M32...-A, M32...-M, M52-A)	+1.5 ... +10 (B52) +2.5 ... +10 (M52, M32, T32)	
Pilot pressure [bar]	+1.5 ...+10 (B52) +2.5 ...+10	+1.5 ...+10 (B52) +2.5 ...+10 (M52, M32, T32)	
Ambient temperature [°C]	-10 ... +60	-5 ... +60 (M32, T32) -10 ... +60 (B52, M52)	
Temperature of medium [°C]	-10 ... +60	-5 ... +60 (M32, T32) -10 ... +60 (B52, M52)	
Approval	c UL us - Recognized (OL)		
Corrosion resistance class CRC <sup>1)</sup>	2		

- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070  
 Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.


## Valve manifold VTUS

Technical data – Valve manifold

### Dimensions – Valve manifold

With 3/2-way valves, standard manifold block

Download CAD data → [www.festo.com](http://www.festo.com)



## Valve manifold VTUS

Technical data – Valve manifold

Type	B2	B4	B5	B6	B7	B8	B9	B11	B12	B14	B15	B16
VTUS-20	110.7	75.5	53	66.5	63	50	24	12.5	75	11.5	25	5.5
VTUS-25	129.2	93	67.5	80.5	78	62	30	16	84.2	14	32	6
VTUS-30	144.9	108.2	79	93.2	94.7	75.7	36.2	19	91.2	17.2	38	6.5

Type	D1 Ø	D2	H1	H2	H3	H4	H5	H6	H7	H8	H9	L3	L4	L5	L6
VTUS-20	4.5	M4x6.5	77.4	61	37	23.5	8.5	18	5	91.4	32	6	25	22	1
VTUS-25	4.5	M4x9	95.5	71	45	25	9	22	5	123.4	39	6	29.8	27.5	1
VTUS-30	4.5	M5x11	118	91	61	35	9	28.5	6.5	170.1	54.5	7.5	34	32	-

Type	Valve positions	2	3	4	5	6	7	8	9	10
VTUS-20	L1	72	94	116	138	160	182	204	226	248
	L2	60	82	104	126	148	170	192	214	236
VTUS-25	L1	87	114.5	142	169.5	197	224.5	252	279.5	307
	L2	75	102.5	130	157.5	185	212.5	240	267.5	295
VTUS-30	L1	100	132	164	196	228	260	292	324	356
	L2	85	117	149	181	213	245	277	309	341


## Valve manifold VTUS

Technical data – Valve manifold

### Dimensions – Valve manifold

With 3/2-way valves, compact manifold block

Download CAD data → [www.festo.com](http://www.festo.com)



## Valve manifold VTUS

Technical data – Valve manifold

Type	B2	B4	B7	B8	B9	B11	B12	B14	B15
VTUS-20	110.7	56.1	53.1	47	22	10.5	75	11.5	25
VTUS-25	129.2	70.3	67.3	58.8	30	16	84	14	32
VTUS-30	144.9	83	80	69.4	36	19	91.2	17	38

Type	D1 Ø	D2	H1	H2	H3	H4	H6	H8	L3	L4	L5	L6
VTUS-20	4.5	M4x6.5	73.4	57	33	9.7	18	87.4	6	25	22	1
VTUS-25	5.5	M4x9	84.5	60	34	13.5	20	112.4	6	29.8	27.5	1
VTUS-30	6.3	M5x11	99.5	72.5	42.5	17.5	26	151.6	7.5	34	32	-

Type	Valve posi-tions	2	3	4	5	6	7	8	9	10
VTUS-20	L1	72	94	116	138	160	182	204	226	248
	L2	60	82	104	126	148	170	192	214	236
VTUS-25	L1	87	114.5	142	169.5	197	224.5	252	279.5	307
	L2	75	102.5	130	157.5	185	212.5	240	267.5	295
VTUS-30	L1	100	132	164	196	228	260	292	324	356
	L2	85	117	149	181	213	245	277	309	341


## Valve manifold VTUS

Technical data – Valve manifold

### Dimensions – Valve manifold

with 5/2-, 5/3-, and 2x 3/2-way valves, standard manifold block

Download CAD data → [www.festo.com](http://www.festo.com)



## Valve manifold VTUS

Technical data – Valve manifold

Type	B1	B2	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	B15
VTUS-20	174.9	141.2	110	100.5	97.5	73	81	55	29	12.5	75	75	42.5	25
VTUS-25	200.3	162.2	126	119	113.5	80	95	63	31	16	84.2	84.2	47	32
VTUS-30	220.3	180.7	144	137	129	104	111.5	72	32.5	19	91.2	91.2	38	25

Type	D1 Ø	D2	H1	H2	H3	H4	H5	H6	H7	H8	L3	L4	L5	L6
VTUS-20	4.5	M4x6.5	77.4	61	37	23.5	22	18	8.5	91.4	6	25	22	1
VTUS-25	5.5	M4x9	95.5	71	45	25	22	22	9	123.4	6	29.8	27.5	1
VTUS-30	6.3	M5x11	118	91	61	35	22	28.5	9	170.1	7.5	34	32	-

Type	Valve posi-tions	2	3	4	5	6	7	8	9	10
VTUS-20	L1	72	94	116	138	160	182	204	226	248
	L2	60	82	104	126	148	170	192	214	236
VTUS-25	L1	87	114.5	142	169.5	197	224.5	252	279.5	307
	L2	75	102.5	130	157.5	185	212.5	240	267.5	295
VTUS-30	L1	100	132	164	196	228	260	292	324	356
	L2	85	117	149	181	213	245	277	309	341




## Valve manifold VTUS

Technical data – Valve manifold

### Dimensions – Valve manifold

with 5/2-, 5/3-, and 2x 3/2-way valve, compact manifold block

Download CAD data → [www.festo.com](http://www.festo.com)



- [1] Ports 1, 3 and 5:  
G1/4 for VTUS-20  
G3/8 for VTUS-25  
G1/2 for VTUS-30

- [5] Ports 2 and 4:  
G1/8 for VTUS-20  
G1/4 for VTUS-25  
G3/8 for VTUS-30

- [7] H-rail mounting:  
VAME-T-M4 for VTUS-20  
VAME-T-M5 for VTUS-25  
VAME-T-M6 for VTUS-30

- [8] Blanking plate

- [9] Supply plate,  
port 1, 3 and 5:  
G1/8 for VTUS-20  
G1/4 for VTUS-25  
G3/8 for VTUS-30

- [10] 5/2-way valve, monostable  
[11] 5/2-way valve, bistable or  
5/3-way valve or 2x 3/2-way  
valve

## Valve manifold VTUS

Technical data – Valve manifold

Type	B1	B2	B4	B7	B8	B9	B10	B11	B12	B13	B14	B15
VTUS-20	174.9	141.2	64.2	47	55.1	32.1	9.1	12.5	75	75	19.6	25
VTUS-25	200.3	162.2	80.5	61.5	69	40.3	11.5	16	84.2	84.2	24.3	32
VTUS-30	220.3	180.7	94	77	80.4	47	13.6	19	91.2	91.2	28	38

Type	D1 Ø	D2	H1	H2	H3	H4	H6	H8	L3	L4	L5	L6
VTUS-20	4.5	M4x6.5	76.4	60	36	9.7	22.5	90.4	6	25	22	1
VTUS-25	5.5	M4x9	84.5	60	34	13.5	20	112.4	6	29.8	27.5	1
VTUS-30	6.3	M5x11	99.5	72.5	42.5	17.5	26	151.6	7.5	34	32	-

Type	Valve posi-tions	2	3	4	5	6	7	8	9	10
VTUS-20	L1	72	94	116	138	160	182	204	226	248
	L2	60	82	104	126	148	170	192	214	236
VTUS-25	L1	87	114.5	142	169.5	197	224.5	252	279.5	307
	L2	75	102.5	130	157.5	185	212.5	240	267.5	295
VTUS-30	L1	100	132	164	196	228	260	292	324	356
	L2	85	117	149	181	213	245	277	309	341



**New**  
VUVS-LT20, VUVS-LT30

## Valve manifold VTUS


Technical data – Valve manifold

**FESTO**

### Dimensions – Supply manifold

Mounting on both sides

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B17	H1	H2	H3	H10	H11	H12	L7
VTUS-20	23	55	80.4	59	40	11.5	6.3	2	21
VTUS-25	28.7	75	102.5	78	52	18	6.7	2	24
VTUS-30	34	85	122	95	65	17.5	6.7	2.5	26


## Valve manifold VTUS

Technical data – Valve manifold

### Dimensions – Supply manifold

Mounting on both sides

Download CAD data → [www.festo.com](http://www.festo.com)



- [1] Port 1 (at both sides):  
G3/8 for VTUS-20  
G1/2 for VTUS-25  
G3/4 for VTUS-30

- [5] Port 2 and 4:  
G1/8 for VTUS-20  
G1/4 for VTUS-25  
G3/8 for VTUS-30

 Note  
Mounting bracket can be adjusted through ±30°.



New

VUVS-LT20, VUVS-LT30

FESTO

## Valve manifold VTUS

Technical data – Valve manifold

Type	B1	B2	B3	B12	B13	B18	B19
VTUS-20	174.9	141.2	110.7	67.5	67.5	40	20
VTUS-25	200.3	162.2	129.2	70.2	70.2	60	35
VTUS-30	220.3	180.7	144.9	77.7	77.7	65	35

Type	D1 Ø	D2	D3 Ø	L3	L4	L5	W1
VTUS-20	4.5	M4x6.5	5.2	8	21	22	30°
VTUS-25	4.5	M4x9	6.6	8	29.8	27.5	30°
VTUS-30	5.5	M5x11	8.6	9	34	32	30°

Type	Valve positions	2	3	4	5	6	7	8	9	10
VTUS-20	L1	64	86	108	130	152	174	196	218	240
	L2	90	112	134	156	178	200	222	244	266
VTUS-25	L1	87	114.5	142	169.5	197	224.5	252	279.5	307
	L2	119	146.5	174	201.5	229	256.5	284	311.5	339
VTUS-30	L1	100	132	164	196	228	260	292	324	356
	L2	134	166	198	230	262	294	326	358	390


## Valve manifold VTUS

Technical data – Valve manifold

### Dimensions – Supply manifold

Mounting on one side

Download CAD data → [www.festo.com](http://www.festo.com)





New

VUVS-LT20, VUVS-LT30

## Valve manifold VTUS

Technical data – Valve manifold

FESTO

Type	B1	B2	B4	B17	B18	B19
VTUS-20	174.9	110.7	23	55	40	20
VTUS-25	200.3	129.2	28.7	80	60	35
VTUS-30	220.3	144.9	34	85	65	35

Type	D1 Ø	D3 Ø	H1	H3	H10	H11	H13	H14	H15	L7	L8
VTUS-20	4.5	5.2	80.4	40	33	6.3	106	90	8	50	2
VTUS-25	4.5	6.6	102.5	52	38	6.7	128	112	8	64	2
VTUS-30	5.5	8.6	122	65	38	6.7	146	128	9	74	2.5

Type	Valve positions	2	3	4
VTUS-20	L1	64	86	108
VTUS-25	L1	87	114.5	142
VTUS-30	L1	100	132	164

## Solenoid valves VUVS

Type code solenoid valves

VUVS	-	L		-		-							-	
Type of directional control valve														
In-line valve		L												
Design principle														
Piston spool with sealing cartridge			-											
Piston spool with sealing ring	K													
Poppet valve, soft seal	T													
Size														
Valve width	21 mm	20												
	26.5 mm	25												
	31 mm	30												
Valve functions														
3/2-way valve, normally closed		M32C												
3/2-way valve, normally open		M32U												
2x 3/2-way valve, normally closed		T32C												
2x 3/2-way valve, normally open		T32U												
2x 3/2-way valve,		T32H												
1x normally open, 1x normally closed														
5/2-way valve, single solenoid		M52												
5/2-way valve, double solenoid		B52												
5/3-way valve, mid-position closed		P53C												
5/3-way valve, mid-position pressurised		P53U												
5/3-way valve, mid-position exhausted		P53E												
Reset method														
Pneumatic spring for M52 and M32		A												
Mechanical spring for M52, M32 and P53		M												
For B52 and P53		-												
Pilot air supply														
Internal		-												
External		Z												
Manual override														
Non-detenting, detenting without accessories		D												
Covered		S												
Non-detenting		H												

Version	
-	Extended features
S	Core features
Electrical accessories, valve	
-	None
+G	Connector socket without LED
EU certification	
-	None
EX2	II 3GD
Degree of protection for electrics	
-	standard
S8	IP67
Electrical connection	
-	None
A1	Connection type A, to EN 175301
C1	Connection type C, to EN 175301
B2	Connection type B, industry standard
Nominal operating voltage	
-	None
1	24 V DC
1A	24 V AC
3W	230/240 V AC
5	12 V DC
16B	110/120 V AC
Valve pilot control interface	
F7	With 8 mm armature tube, short
F8	With 8 mm armature tube, standard
Exhaust port	
-	Without fitting
QN	With fitting
U1	Silencer with metal housing
U3	Silencer with polymer housing
U5	Silencer with sinter housing
Pneumatic connection	
G18	G1/8
G14	G <sup>1</sup> / <sub>2</sub>
G38	G3/8
Q4	Push-in connector 4 mm
Q6	Push-in connector 6 mm
Q8	Push-in connector 8 mm
Q10	Push-in connector 10 mm
Q12	Push-in connector 12 mm

# Solenoid valves VUVS-LK, size 20

Data sheet

**FESTO**

-  - Flow rate  
Up to 550 l/min

-  - Valve width  
21 mm

-  - Voltage  
24 V DC



General technical data			
Valve function	3/2-way valve	5/2-way valve	
Order code for valves	M32C	M52	B52
Valve width [mm]	21		
Nominal width [mm]	5.2		
Design	Piston spool		
Flow direction	Non-reversible		
Pilot air supply	Internal		
Type of control	Piloted		
Manual override	Non-detenting, detenting		
Overlap	Positive overlap		
Sealing principle	Soft		
Type of mounting	Optionally via through-hole or on manifold rail		
Standard nominal flow rate qN [l/min]	550	550	550
Type of actuation	Electrical		
Mounting position	Optional		
Exhaust function	With flow control		
Connection for venting hole	Not ducted		
b value	0.38		
c value [l/sbar]	2.66		
Pneumatic connection	1, 2, 3	G1/8	G1/8
	4, 5	-	G1/8
			G1/8

Technical data – 3/2-way valves			
Order code for valves	M32C		
Normal position	Closed		
Stable position	Monostable		
Reset method	Pneumatic spring		
Switching times in [ms]	On	16	
	Off	20	
	Change-over	-	
Product weight including solenoid coil	[g]	120	
Product weight including solenoid coil and plug socket	[g]	133	

# Solenoid valves VUVS-LK, size 20

**FESTO**

Data sheet

Technical data – 5/2-way valves		
Order code for valves	M52	B52
Normal position	–	–
Stable position	Monostable	Bistable
Reset method	Pneumatic spring	–
Switching times in [ms]	On Off Change-over	17 22 – 10
Product weight including solenoid coil	[g]	145 200
Product weight including solenoid coil and plug socket	[g]	158 226

Safety data		
Max. positive test pulse 0 signal	[μs]	2700
Max. negative test pulse 1 signal	[μs]	1100
Resistance to shocks	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6	

Operating and environmental conditions			
Order code for valves	M32C	M52	B52
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[bar]	1.5 ... 8	1.5 ... 8
Ambient temperature	[°C]	–5 ... +50	–5 ... +50
Temperature of medium	[°C]	–5 ... +50	–5 ... +50
Corrosion resistance class CRC <sup>1)</sup>	1		

- 1) Corrosion resistance class CRC 1 to Festo standard FN 940070  
 Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Electrical		
Electrical connection	Plug connector type C	
Operating voltage	[V DC]	24
Permissible voltage fluctuations	[%]	±10
Power	[W]	2.6
Duty cycle	[%]	100
Degree of protection to EN 60529	IP65 with plug socket	

Materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Piston spool	Wrought aluminium alloy
Note on materials	RoHS-compliant Contains paint-wetting impairment substances

# Solenoid valves VUVS-LK, size 20


Data sheet

**FESTO**

## Dimensions

3/2-way valves, with solenoid coil

Download CAD data → [www.festo.com](http://www.festo.com)



[1] Solenoid coil interface type C

[2] Location for inscription label

[7] For screw M3

Type	B1	B2	B4	B5	D1	H1	H2	H3	H4	H5
VUVS-LK20-M32C-AD-G18-1C1-S	21.2	16.1	2.5	0.2	G1/8	29.2	13.7	5	37.8	27.7

Type	L1	L6	L7	L8	L9	L14	L15	L16	L17	L19
VUVS-LK20-M32C-AD-G18-1C1-S	92.6	62.3	39.8	19.2	25.4	49.4	29.4	8	40.1	45.4

# Solenoid valves VUVS-LK, size 20




FESTO

Data sheet

## Dimensions

5/2-way single solenoid valves, with solenoid coil

Download CAD data ➔ [www.festo.com](http://www.festo.com)



[1] Solenoid coil interface type C

[2] Location for inscription label

[7] For screw M3

Type	B1	B2	B4	B5	D1	H1	H2	H3	H4	H5
VUVS-LK20-M52-AD-G18-1C1-S	21.2	16.1	2.5	0.2	G1/8	29.2	13.7	5	37.8	27.7

Type	L1	L6	L7	L8	L9	L13	L14	L15	L16	L17	L18	L19
VUVS-LK20-M52-AD-G18-1C1-S	115.7	85.3	39.8	19.2	25.4	69.4	49.4	29.4	8	40.1	18.6	45.4

# Solenoid valves VUVS-LK, size 20


Data sheet

**FESTO**

## Dimensions

5/2-way double solenoid valves, with solenoid coil

Download CAD data → [www.festo.com](http://www.festo.com)



[1] Solenoid coil interface type C

[2] Location for inscription label

[7] For screw M3

Type	B1	B2	B4	B5	D1	H1	H2	H3	H4	H5
VUVS-LK20-B52-D-G18-1C1-S	21.2	16.1	2.5	0.2	G1/8	29.2	13.7	5	37.8	27.7

Type	L1	L6	L7	L8	L9	L13
VUVS-LK20-B52-D-G18-1C1-S	159.6	98.8	39.8	19.2	25.4	69.4

Type	L14	L15	L16	L17	L18	L19
VUVS-LK20-B52-D-G18-1C1-S	49.4	29.4	8	40.1	18.6	45.4

# Solenoid valves VUVS-LK, size 20


FESTO

Accessories

## Dimensions

Foot mounting

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1	D2	D3	H1	H2	H3	H4
	Ø	Ø	Ø	Ø	Ø	Ø				
VAME-B10-20-A	VUVS-LK20-B52	20	13.1	10.6	3.2	4.2	5.2	112.5	106.5	77.5
	VUVS-LK20-M52									63.5
	VUVS-LK20-M32									

Type	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14
VAME-B10-20-A	VUVS-LK20-B52	44	39	19.2	10.5	2.5	176.7	–	176.7	176.7
	VUVS-LK20-M52							147.7	132.8	132.8
	VUVS-LK20-M32								109.8	109.8

Type	H15	L1	L2	L3	L4	L5	L6	L7	L8	L9
VAME-B10-20-A	VUVS-LK20-B52	87.7	55	41	29.4	19.2	40	20	19	174.9
	VUVS-LK20-M52									141.2
	VUVS-LK20-M32									110.7


# Solenoid valves VUVS-LK, size 20

Accessories

**FESTO**

## Dimensions

Wall mounting



Type		B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-LK20-B52	10	M3	M4	M5	35	20	10	11.5	9.7	8.7
	VUVS-LK20-M52										
	VUVS-LK20-M32										




Type		H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	VUVS-LK20-B52	13	16.5	50	40	20	79.8	79.8	49.4	49.4
	VUVS-LK20-M52									
	VUVS-LK20-M32									

# Solenoid valves VUVS-LK, size 20

**FESTO**

Accessories

## ★ Core product range

Ordering data		Code	Valve function	Part no.	Type
3/2-way valve with solenoid coil (24 V DC)					
		M32C-A	Monostable, normally closed, type C Pneumatic spring return, internal pilot air supply, direction of flow not reversible	★ 8043213	VUVS-LK20-M32C-AD-G18-1C1-S
5/2-way valve with solenoid coil (24 V DC)					
		M52-A	Monostable, type C Pneumatic spring return, internal pilot air supply, direction of flow not reversible	★ 8043214	VUVS-LK20-M52-AD-G18-1C1-S
		B52	Double solenoid, type C internal pilot air supply, direction of flow not reversible	★ 8043215	VUVS-LK20-B52-D-G18-1C1-S

Ordering data		Description	Part no.	Type
Cover cap				
		For manual override, non-detenting or covered	8049538	VAMC-B10-20-CH2-S
Plug socket				
		Connection pattern type C, to DIN EN 175301-803 3-pin, screw terminal 4-pin, insulation displacement connector	539712 ★ 151687 192745	MSSD-EB-M12 MSSD-EB MSSD-EB-S-M14

Festo core product range


★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LK, size 20

Accessories

**FESTO**

Ordering data		Description	Part no.	Type
<b>Plug socket with cable</b>				
	Connection pattern type C, to DIN EN 175301-803 Angled socket, 3-pin Cable, open end, 3-wire	24 V DC	LED	2,5 m <b>★ 151688 KMEB-1-24-2,5-LED</b> 5 m <b>151689 KMEB-1-24-5-LED</b> 10 m <b>193457 KMEB-1-24-10-LED</b>
<b>Illuminating seal</b>				
	Connection pattern type C, to DIN EN 175301-803	24 V DC		<b>151717 MEB-LD-12-24DC</b>
<b>Push-in fitting with internal hex</b>				
	Connecting thread G1/8 for tubing O.D.	4 mm	<b>★ 186106 QS-G1/8-4-I</b> <b>133008 QS-G1/8-4-I-100</b>	<b>10</b> <b>100</b>
		6 mm	<b>★ 186107 QS-G1/8-6-I</b> <b>133009 QS-G1/8-6-I-100</b>	<b>10</b> <b>100</b>
		8 mm	<b>★ 186109 QS-G1/8-8-I</b> <b>133010 QS-G1/8-8-I-100</b>	<b>10</b> <b>100</b>
<b>Angled push-in fitting with external hex</b>				
	Connecting thread G1/8 for tubing O.D.-	4 mm	<b>★ 186116 QSL-G1/8-4</b> <b>132048 QSL-G1/8-4-100</b>	<b>10</b> <b>100</b>
		6 mm	<b>★ 186117 QSL-G1/8-6</b> <b>132049 QSL-G1/8-6-100</b>	<b>10</b> <b>100</b>
		8 mm	<b>★ 186119 QSL-G1/8-8</b> <b>132050 QSL-G1/8-8-50</b>	<b>10</b> <b>50</b>
<b>Angled push-in fitting, long, with external hex</b>				
	Connecting thread G1/8 for tubing O.D.-	4 mm	<b>186127 QSLL-G1/8-4</b> <b>133015 QSLL-G1/8-4-100</b>	<b>10</b> <b>100</b>
		6 mm	<b>186128 QSLL-G1/8-6</b> <b>133016 QSLL-G1/8-6-100</b>	<b>10</b> <b>100</b>
		8 mm	<b>186130 QSLL-G1/8-8</b> <b>133017 QSLL-G1/8-8-100</b>	<b>10</b> <b>100</b>
<b>Silencer</b>				
	With connecting thread G, polymer design	G1/8	<b>★ 2307 U-1/8</b> <b>534222 U-1/8-50</b>	<b>1</b> <b>50</b>
	With connecting thread G, metal design	G1/8	<b>★ 6841 U-1/8-B</b>	<b>1</b>

1) Packaging unit quantity



Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LK, size 20

**FESTO**

Accessories

Ordering data		Description	Weight [g]	Part no.	Type
<b>Foot mounting</b>					
	With screw set for attaching the valve to the foot mounting	97		<b>576412</b>	<b>VAME-B10-20-A</b>
<b>Wall mounting</b>					
	With screw set for attaching the valve to the wall mounting	53		<b>576413</b>	<b>VAME-B10-20-W</b>
<b>Set of spare parts</b>					
	Set comprising seals and screws	10		<b>8026203</b>	<b>VAME-B10-20-MK</b>
<b>Screw set</b>					
	For mounting valves VUVS-LK on common supply manifolds, comprising 2 screws M3x30	4.5		<b>8069876</b>	<b>VAME-B10-20-S</b>
<b>Inscription label</b>					
	40 pieces in frame	-		<b>565306</b>	<b>ASLR-C-E4</b>

# Solenoid valves VUVS-LK, size 25

Data sheet

**FESTO**

-  - Flow rate  
Up to 1000 l/min

-  - Valve width  
26.5 mm

-  - Voltage  
24 V DC



General technical data			
Valve function	3/2-way valve	5/2-way valve	
Order code for valves	M32C	M52	B52
Valve width [mm]	26.5		
Nominal width [mm]	6.7		
Design	Piston spool		
Flow direction	Non-reversible		
Pilot air supply	Internal		
Type of control	Piloted		
Manual override	Non-detenting, detenting		
Overlap	Positive overlap		
Sealing principle	Soft		
Type of mounting	Optionally via through-hole or on manifold rail		
Standard nominal flow rate qN [l/min]	1000	1000	1000
Type of actuation	Electrical		
Mounting position	Optional		
Exhaust function	With flow control		
Connection for venting hole	Not ducted		
b value	0.45		
c value [l/sbar]	3.86		
Pneumatic connection	1, 2, 3	G1/4	G1/4
	4, 5	-	G1/4

Technical data – 3/2-way valves			
Order code for valves	M32C		
Normal position	Closed		
Stable position	Monostable		
Reset method	Pneumatic spring		
Switching times in [ms]	On	16	
	Off	20	
	Change-over	-	
Product weight including solenoid coil	[g]	200	
Product weight including solenoid coil and plug socket	[g]	224	

# Solenoid valves VUVS-LK, size 25

**FESTO**

Data sheet

Technical data – 5/2-way valves		
Order code for valves	M52	B52
Normal position	–	–
Stable position	Monostable	Bistable
Reset method	Pneumatic spring	–
Switching times in [ms]	On Off Change-over	20 22 – 12
Product weight including solenoid coil [g]	250	320
Product weight including solenoid coil and plug socket [g]	274	368

Safety data		
Max. positive test pulse [μs] 0 signal	2500	
Max. negative test pulse [μs] 1 signal	1100	
Resistance to shocks	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6	

Operating and environmental conditions			
Order code for valves	M32C	M52	B52
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure [bar]	1.5 ... 8	1.5 ... 8	1.5 ... 8
Ambient temperature [°C]	–5 ... +50		
Temperature of medium [°C]	–5 ... +50		
Corrosion resistance class CRC <sup>1)</sup>	1		

- 1) Corrosion resistance class CRC 1 to Festo standard FN 940070  
 Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Electrical		
Electrical connection	Plug connector type B	
Operating voltage [V DC]	24	
Permissible voltage fluctuations [%]	10	
Power [W]	3.3	
Duty cycle [%]	100	
Degree of protection to EN 60529	IP65 with plug socket	

Materials		
Housing	Wrought aluminium alloy	
Seals	HNBR, NBR	
Piston spool	Wrought aluminium alloy	
Note on materials	RoHS-compliant	
	Contains paint-wetting impairment substances	

# Solenoid valves VUVS-LK, size 25




Data sheet

**FESTO**

## Dimensions

3/2-way valves, with solenoid coil

Download CAD data → [www.festo.com](http://www.festo.com)



[1] Solenoid coil interface  
type B

[2] Location for inscription label

[7] For screw M4

Type	B1	B2	B4	B5	D1	H1	H2	H3	H4	H5
VUVS-LK25-M32C-AD-G14-1B2-S	26.5	20.2	1.9	1	G1/4	36.1	16.9	6	45.9	33.9

Type	L1	L6	L7	L8	L9	L14	L15	L16	L17	L19
VUVS-LK25-M32C-AD-G14-1B2-S	109.2	74.1	44.2	25	29	58	33.5	13	44.6	51.5

# Solenoid valves VUVS-LK, size 25


FESTO

Data sheet

## Dimensions

5/2-way single solenoid valves, with solenoid coil

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B1	B2	B4	B5	D1	H1	H2	H3	H4	H5
VUVS-LK25-M52-AD-G14-1B2-S	26.5	20.2	1.9	1	G1/4	36.1	16.9	6	45.9	33.9

Type	L1	L6	L7	L8	L9	L13	L14	L15	L16	L17	L18	L19
VUVS-LK25-M52-AD-G14-1B2-S	137.8	102.7	44.2	25	29	82.5	58	33.5	13	44.6	26.8	51.5

# Solenoid valves VUVS-LK, size 25


Data sheet

**FESTO**

## Dimensions

5/2-way double solenoid valves, with solenoid coil

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B4	B5	D1	H1	H2	H3	H4	H5
VUVS-LK25-B52-D-G14-1B2-S	26.5	20.2	1.9	1	G1/4	36.1	16.9	6	45.9	33.9

Type	L1	L6	L7	L8	L9	L13	L14	L15	L16	L17	L18	L19
VUVS-LK25-B52-D-G14-1B2-S	186.1	116	44.2	25	29	82.5	58	33.5	13	44.6	26.8	51.5

# Solenoid valves VUVS-LK, size 25


FESTO

Accessories

## Dimensions

Foot mounting

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1 ∅	D2 ∅	D3	H1	H2	H3	H4
VAME-B10-25-A	VUVS-LK25-B52	24	15.8	13.3	4.2	4.2	5.2	130	122.5	91
	VUVS-LK25-M52									80.5
	VUVS-LK25-M32									

Type	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14
VAME-B10-25-A	VUVS-LK25-B52	48.5	41.5	25	11	2.5	201.8	-	204.4	201.8
	VUVS-LK25-M52							170.3	156	156
	VUVS-LK25-M32								127.4	127.4

Type	H15	L1	L2	L3	L4	L5	L6	L7	L8	L9
VAME-B10-25-A	VUVS-LK25-B52	110.6	55	49.4	40.4	25	40	20	23.5	186.1
	VUVS-LK25-M52									137.8
	VUVS-LK25-M32									109.2


# Solenoid valves VUVS-LK, size 25

Accessories

**FESTO**

## Dimensions

Wall mounting



Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-LK25-B52	10	M3	M4	M5	35	20	10	11.5	9.7
	VUVS-LK25-M52									8.7
	VUVS-LK25-M32									




Type	H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	VUVS-LK25-B52	20.4	17.5	50	40	20	93.1	56.7	59.3
	VUVS-LK25-M52								-
	VUVS-LK25-M32								-

# Solenoid valves VUVS-LK, size 25

FESTO

Accessories

## ★ Core product range

Ordering data		Code	Valve function	Part no.	Type
3/2-way valve with solenoid coil (24 V DC)					
	Single solenoid, normally closed, type B	M32C-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	★ 8043217	VUVS-LK25-M32C-AD-G14-1B2-S
5/2-way valve with solenoid coil (24 V DC)					
	Single solenoid, type B	M52-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	★ 8043218	VUVS-LK25-M52-AD-G14-1B2-S
	Double solenoid, type B	B52	Internal pilot air supply, direction of flow not reversible	★ 8043219	VUVS-LK25-B52-D-G14-1B2-S

Festo core product range


★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LK, size 25

Accessories

**FESTO**

Ordering data		Description	Part no.	Type
<b>Cover cap</b>				
	For manual override, non-detenting or covered		8049539	VAMC-B10-25-CH2-S
<b>Plug socket</b>				
	Connection pattern type B, industry standard			
	3-pin, screw terminal	Cable fitting M16	0 ... 250 V AC/DC	IP65
		Cable fitting Pg9		
	3-pin, insulation displacement connector	-	0 ... 250 V AC/DC	IP67
<b>Plug socket with cable</b>				
	Connection pattern type B, industry standard			
	Angled socket, 3-pin	24 V DC	LED	2.5 m
	Cable, open end, 3-wire			★ 30935 KMF-1-24DC-2,5-LED
				5 m 30937 KMF-1-24DC-5-LED
				10 m 193458 KMF-1-24-10-LED
<b>Illuminating seal</b>				
	Connection pattern type B, industry standard	24 V DC	19143	MF-LD-12-24DC
<b>Push-in fitting with internal hex</b>				
	Connecting thread G1/4 for tubing O.D.-	6 mm	★ 186108 QS-G1/4-6-I	10
		8 mm	★ 186110 QS-G1/4-8-I	10
		10 mm	★ 186112 QS-G1/4-10-I	10
<b>Angled push-in fitting with external hex</b>				
	Connecting thread G1/4 for tubing O.D.-	6 mm	★ 186118 QSL-G1/4-6	10
			132051 QSL-G1/4-6-100	100
		8 mm	★ 186120 QSL-G1/4-8	10
			132052 QSL-G1/4-8-50	50
		10 mm	★ 186122 QSL-G1/4-10	10
			132053 QSL-G1/4-10-50	50
<b>Angled push-in fitting, long, with external hex</b>				
	Connecting thread G1/4 for tubing O.D.-	6 mm	186129 QSLL-G1/4-6	10
		8 mm	186131 QSLL-G1/4-8	10
		10 mm	186133 QSLL-G1/4-10	10
<b>Silencer</b>				
	With connecting thread G, polymer design	G1/4	★ 2316 U-1/4	1
			534223 U-1/4-20	20
	With connecting thread G, metal design	G1/4	★ 6842 U-1/4-B	1

1) Packaging unit quantity

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LK, size 25

**FESTO**

Accessories

Ordering data		Description	Weight [g]	Part no.	Type
<b>Foot mounting</b>					
	With screw set for attaching the valve to the foot mounting	130		<b>2293485</b>	<b>VAME-B10-25-A</b>
<b>Wall mounting</b>					
	With screw set for attaching the valve to the wall mounting	53		<b>576413</b>	<b>VAME-B10-20-W</b>
<b>Set of spare parts</b>					
	Set comprising seals and screws	12		<b>8035636</b>	<b>VAME-B10-25-MK</b>
<b>Screw set</b>					
	For mounting valves VUVS-LK on common supply manifolds, comprising 2 screws M4x40	9.6		<b>8068789</b>	<b>VAME-B10-25-S</b>
<b>Inscription label</b>					
	40 pieces in frame	-		<b>565306</b>	<b>ASLR-C-E4</b>

# Solenoid valves VUVS-LK, size 30

Data sheet

**FESTO**

-  - Flow rate  
Up to 1600 l/min

-  - Valve width  
31 mm

-  - Voltage  
24 V DC



General technical data			
Valve function	3/2-way valve	5/2-way valve	
Order code for valves	M32C	M52	B52
Valve width [mm]	31		
Nominal width [mm]	8.1		
Design	Piston spool		
Flow direction	Non-reversible		
Pilot air supply	Internal		
Type of control	Piloted		
Manual override	Non-detenting, detenting		
Overlap	Positive overlap		
Sealing principle	Soft		
Type of mounting	Optionally via through-hole or on manifold rail		
Standard nominal flow rate qN [l/min]	1600	1600	1600
Type of actuation	Electrical		
Mounting position	Optional		
Exhaust function	With flow control		
Connection for venting hole	Not ducted		
b value	0.37		
c value [l/sbar]	7.03		
Pneumatic connection	1, 2, 3	G3/8	G3/8
	4, 5	-	G3/8
			G3/8

Technical data – 3/2-way valves			
Order code for valves	M32C		
Normal position	Closed		
Stable position	Monostable		
Reset method	Pneumatic spring		
Switching times in [ms]	On	16	
	Off	20	
	Change-over	-	
Product weight including solenoid coil	[g]	250	
Product weight including solenoid coil and plug socket	[g]	274	

# Solenoid valves VUVS-LK, size 30

**FESTO**

Data sheet

Technical data – 5/2-way valves		
Order code for valves	M52	B52
Normal position	–	–
Stable position	Monostable	Bistable
Reset method	Pneumatic spring	–
Switching times in [ms]	On	16
	Off	21
	Change-over	–
Product weight including solenoid coil	[g]	315
Product weight including solenoid coil and plug socket	[g]	392
		416

Safety data		
Max. positive test pulse 0 signal	[μs]	2500
Max. negative test pulse 1 signal	[μs]	1100
Resistance to shocks	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6	

Operating and environmental conditions			
Order code for valves	M32C	M52	B52
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[bar]	1.5 ... 8	1.5 ... 8
Ambient temperature	[°C]	–5 ... +50	
Temperature of medium	[°C]	–5 ... +50	
Corrosion resistance class CRC <sup>1)</sup>		1	

- 1) Corrosion resistance class CRC 1 to Festo standard FN 940070  
Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Electrical		
Electrical connection	Plug connector type B	
Operating voltage	[V DC]	24
Permissible voltage fluctuations	[%]	10
Power	[W]	3.3
Duty cycle	[%]	100
Degree of protection to EN 60529	IP65 with plug socket	

Materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Piston spool	Wrought aluminium alloy
Note on materials	RoHS-compliant
	Contains paint-wetting impairment substances

# Solenoid valves VUVS-LK, size 30


Data sheet

FESTO

## Dimensions

3/2-way valves, with solenoid coil

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B4	D1	H1	H2	H3	H4	H5
VUVS-LK30-M32C-AD-G38-1B2-S	31	23.3	2.5	G3/8	39.1	19.9	8	48.9	36.9

Type	L1	L6	L7	L8	L9	L14	L15	L16	L17	L19
VUVS-LK30-M32C-AD-G38-1B2-S	122.1	87.1	50.6	31	29	66.1	36.1	17	44.8	57.6

# Solenoid valves VUVS-LK, size 30


FESTO

Data sheet

## Dimensions

5/2-way single solenoid valves, with solenoid coil

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B1	B2	B4	D1	H1	H2	H3	H4	H5
VUVS-LK30-M52-AD-G38-1B2-S	31	23.3	2.5	G3/8	39.1	19.9	8	48.9	36.9

Type	L1	L6	L7	L8	L9	L13	L14	L15	L16	L17	L18	L19
VUVS-LK30-M52-AD-G38-1B2-S	153.8	118.8	50.6	31	29	96.1	66.1	36.1	17	44.8	42.6	57.6

# Solenoid valves VUVS-LK, size 30


Data sheet

FESTO

## Dimensions

5/2-way double solenoid valves, with solenoid coil

Download CAD data → [www.festo.com](http://www.festo.com)



[1] Solenoid coil interface

form B

[2] Location for inscription label

[7] For screw M5

Type	B1	B2	B4	D1	H1	H2	H3	H4	H5
VUVS-LK30-B52-D-G38-1B2-S	31	23.3	2.5	G3/8	39.1	19.9	8	48.9	36.9

Type	L1	L6	L7	L8	L9	L13	L14	L15	L16	L17	L18	L19
VUVS-LK30-B52-D-G38-1B2-S	202.1	132.2	50.6	31	29	96.1	66.1	36.1	17	44.8	42.6	57.6

# Solenoid valves VUVS-LK, size 30


FESTO

Accessories

## Dimensions

Foot mounting

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1 Ø	D2 Ø	D3	D4	H1	H2	H3	
VAME-B10-30-A	VUVS-LK30-B52	26.8	18.5	15.5	5.2	4.2	5.2	5.2	146	136.5	102.5
	VUVS-LK30-M52										
	VUVS-LK30-M32										
Type	H4	H5	H7	H8	H9	H10	H11	H12	H13	H14	
VAME-B10-30-A	VUVS-LK30-B52	112	50.5	31	11.5	3	222	–	222.1	222.1	
	VUVS-LK30-M52										
	VUVS-LK30-M32										
Type	H15	L1	L3	L4	L5	L6	L7	L8	L9		
VAME-B10-30-A	VUVS-LK30-B52	143.1	57	45.6	31	40	20	32	202.1	4.1	
	VUVS-LK30-M52										
	VUVS-LK30-M32										

# Solenoid valves VUVS-LK, size 30


Accessories

**FESTO**

## Dimensions

Wall mounting

Download CAD data → [www.festo.com](http://www.festo.com)



[1] Mounting hole size 20

[2] Mounting hole size 25

[3] Mounting hole size 30

Type	B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-LK30-B52	10	M3	M4	M5	35	20	10	11.5	9.7
	VUVS-LK30-M52									
	VUVS-LK30-M32									

Type	H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	22.4	17.5	50	40	20	101.1	101.1	66.1	66.1

# Solenoid valves VUVS-LK, size 30

**FESTO**

Accessories

## ★ Core product range

### Ordering data

	Code	Valve function	Part no.	Type
3/2-way valve with solenoid coil (24 V DC)				
<b>M32C-A</b>	Single solenoid, normally closed, type B Pneumatic spring return, internal pilot air supply, direction of flow not reversible		★ 8049880	VUVS-LK30-M32C-AD-G38-1B2-S
5/2-way valve with solenoid coil (24 V DC)				
<b>M52-A</b>	Single solenoid, type B Pneumatic spring return, internal pilot air supply, direction of flow not reversible		★ 8049881	VUVS-LK30-M52-AD-G38-1B2-S
<b>B52</b>	Double solenoid, type B Internal pilot air supply, direction of flow not reversible		★ 8049882	VUVS-LK30-B52-D-G38-1B2-S

### Ordering data

	Description	Part no.	Type
Cover cap			
<b>8049539</b>	For manual override, non-detenting or covered	8049539	VAMC-B10-25-CH2-S
Plug socket			
<b>3-pin, screw terminal</b>	Connection pattern type B, industry standard Cable fitting M16	539710	MSSD-F-M16
	Cable fitting Pg9	★ 34431	MSSD-F
<b>3-pin, insulation displacement connector</b>	–	192746	MSSD-F-S-M16
Plug socket with cable			
<b>Angled socket, 3-pin</b>	Connection pattern type B, industry standard Cable, open end, 3-wire	24 V DC	LED
	2.5 m	★ 30935	KMF-1-24DC-2,5-LED
	5 m	30937	KMF-1-24DC-5-LED
	10 m	193458	KMF-1-24-10-LED
Illuminating seal			
<b>24 V DC</b>	Connection pattern type B, industry standard	19143	MF-LD-12-24DC

Festo core product range

★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LK, size 30

Accessories

**FESTO**

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Push-in fitting with internal hex</b>					
	Connecting thread for G3/8 for tubing O.D.-Ø	6 mm	<b>★ 186111</b>	QS-G3/8-8-I	<b>10</b>
		8 mm	<b>★ 186113</b>	QS-G3/8-10-I	<b>10</b>
		10 mm	<b>★ 186114</b>	QS-G3/8-12-I	<b>10</b>
<b>Angled push-in fitting with external hex</b>					
	Connecting thread for G3/8 for tubing O.D.-Ø	8 mm	<b>★ 186121</b>	QSL-G3/8-8	<b>10</b>
			<b>132055</b>	QSL-G3/8-8-50	<b>50</b>
		10 mm	<b>★ 186123</b>	QSL-G3/8-10	<b>10</b>
			<b>132056</b>	QSL-G3/8-10-20	<b>20</b>
<b>Angled push-in fitting, long, with external hex</b>					
	Connecting thread for G3/8 for tubing O.D.-Ø	8 mm	<b>186132</b>	QSLL-G3/8-8	<b>10</b>
		10 mm	<b>186134</b>	QSLL-G3/8-10	<b>10</b>
<b>Silencer</b>					
	With connecting thread G, metal design	G3/8	<b>★ 6843</b>	U-3/8-B	<b>1</b>

1) Packaging unit quantity

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LK, size 30

**FESTO**

Accessories

Ordering data		Description	Weight [g]	Part no.	Type
<b>Foot mounting</b>					
	With screw set for attaching the valve to the foot mounting	239		<b>8026337</b>	<b>VAME-B10-30-A</b>
<b>Wall mounting</b>					
	With screw set for attaching the valve to the wall mounting	53		<b>576413</b>	<b>VAME-B10-20-W</b>
<b>Set of spare parts</b>					
	Set comprising seals and screws	22		<b>8035637</b>	<b>VAME-B10-30-MK</b>
<b>Screw set</b>					
	For mounting valves VUVS-LK on common supply manifolds, comprising 2 screws M5x40	15.5		<b>8068790</b>	<b>VAME-B10-30-S</b>
<b>Inscription label</b>					
	40 pieces in frame	-		<b>565306</b>	<b>ASLR-C-E4</b>

## Solenoid valves VUVS-LT, size 20


Technical data

FESTO

-  - Flow rate  
Up to 600 l/min

-  - Valve width  
21 mm

-  - Voltage  
24 V DC



General technical data										
Valve function	3/2-way valve				5/2-way valve					
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52			
Valve width [mm]	21									
Nominal width [mm]	5.2	5.2	5.2	5.2	5.2	5	5			
Design	Disc seat									
Flow direction	Non-reversible									
Pilot air supply	Internal or external									
Type of control	Piloted									
Manual override	Non-detenting, detenting									
Overlap	Underlap									
Sealing principle	Soft									
Type of mounting	Optionally via through-hole or on manifold rail									
Standard nominal flow rate qN [l/min]	600				500					
Type of actuation	Electrical									
Mounting position	Optional									
Exhaust function	With flow control									
Connection for venting hole	Not ducted									
b value	0.39	0.29	0.39	0.29	0.34	0.31	0.27			
c value	2.3	2.3	2.3	2.3	2.3	2.1	2.1			
Pneumatic connection 1, 2, 3	G1/8	G1/8	G1/8	G1/8	G1/8	G1/8	G1/8			
4, 5	-	-	G1/8	G1/8	G1/8	G1/8	G1/8			
Pilot air port 12, 14	M5	M5	M5	M5	M5	M5	M5			
Pilot exhaust air port 82, 84	M5	M5	M5	M5	M5	M5	M5			
Corrosion resistance <sup>1)</sup>	2									

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

# Solenoid valves VUVS-LT, size 20

**FESTO**

Technical data

ATEX	
Type	VUVS-LT-...-EX2
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T4 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T115°C X Dc
Explosion-proof ambient temperature rating [°C]	-10 °C <= Ta <= +60 °C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Technical data		M32C	M32U	T32C	T32U	T32H	M52	B52
Normal position		Closed	Open	2x closed	2x normally open	1x normally open, 1x normally closed	-	-
Stable position		Monostable	Monostable	Monostable	Monostable	Monostable	Monostable	Bistable
Reset method		Mechanical spring		Mechanical spring			Mechanical spring	-
Switching times in [ms]	On	9	10	9	9	9	15	-
	Off	23	24	25	23	23	19	-
	Change-over	-	-	-	-	-	-	8
Product weight excluding solenoid coil	[g]	112	112	180	180	180	167	181
Product weight including solenoid coil	[g]	146	146	245	245	245	200	248

# Solenoid valves VUVS-LT, size 20

Technical data

**FESTO**

<b>Safety data</b>	
Max. positive test pulse 0 signal	[μs] 1900
Max. negative test pulse 1 signal	[μs] 2700
Resistance to shocks	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

<b>Operating and environmental conditions</b>							
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]						
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]						
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)						
Operating pressure with internal pilot air supply	[bar] 2.5 ... 10				3 ... 10	1.5 ... 10	
Operating pressure with external pilot air supply	[bar] -0.9 ... 10				2.5 ... 10	1.5 ... 10	
Pilot pressure	[bar] 2.5 ... 10				2.5 ... 10	1.5 ... 10	
Ambient temperature	[°C] -5 ... +60				-10 ... +60		
Temperature of medium	[°C] -5 ... +60				-10 ... +60		
Approval	c UL us - Recognized (OL)						

<b>Electrical</b>		
	With solenoid coil	Without solenoid coil
Electrical connection	Plug type C	Via solenoid coil
Operating voltage	[V DC] 24	→ Internet: vacf
Permissible voltage fluctuations	[%] 10	
Power	[W] 2.6	
Duty cycle	[%] 100	
Degree of protection to IEC 60529	IP65 with plug socket to IEC60529	

<b>Materials</b>	
Housing	Die-cast aluminium (painted)
Seals	HNBR, NBR, TPE-U(PU)
Screws	Galvanised steel
Note on materials	RoHS-compliant


# Solenoid valves VUVS-LT, size 20

FESTO

Technical data

## Dimensions

3/2-way valves, with solenoid coil




[1] Solenoid coil interface  
type C

[2] Location for inscription label

[4] Port 10/12 for pilot air supply

3/2-way valves, without solenoid coil



Download CAD data ➔ [www.festo.com](http://www.festo.com)

Type	B1	B2	B3	B4	B5	D1	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-LT20-M32...MD-G18...	21.1	16.1	-	2.5	2	G1/8	-	M5	8	40.4	20.9	6.2	46.7	36.4
VUVS-LT20-M32...MZD-G18...			2.6					M5						

Type	L2	L4	L6	L7	L8	L9	L11	L12	L13	L14	L15	L16	L17	L19
VUVS-LT20-M32...MD-G18...	100.4	98.8	69.8	47.3	19.2	30.6	29	-	60.9	56.9	36.9	8	45.6	52.9
VUVS-LT20-M32...MZD-G18...								19.5						


# Solenoid valves VUVS-LT, size 20

Technical data

**FESTO**


## Dimensions

5/2-way single solenoid valves, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way single solenoid valves, without solenoid coil



[1] Solenoid coil for interface type C

[2] Location for inscription label

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply  
(pneumatic spring)

[5] Port 84 for pilot exhaust air

[7] For screw M3

Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5 Ø	H1	H2	H3	H4	H5
VUVS-LT20-M52-...MD-G18-...	21.1	16.1	—	2.5	2	G1/8	—	—	M5	8	40.4	20.9	6.2	46.7	36.4
VUVS-LT20-M52-...MZD-G18-...			2.6				M5	M5							

Type	L2	L4	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-LT20-M52-...MD-G18-...	141.2	139.6	110.6	47.3	19.2	30.6	—	29	—	76.9	56.9	36.9	8	45.6	22.5	52.9
VUVS-LT20-M52-...MZD-G18-...							94.3		19.5							


# Solenoid valves VUVS-LT, size 20

FESTO

Technical data

## Dimensions

2x 3/2-way valves and 5/2-way valves, bistable, with solenoid coil




[1] Solenoid coil interface  
type C

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply

Download CAD data ➔ [www.festo.com](http://www.festo.com)

2x 3/2-way valve and 5/2-way valve, bistable, without solenoid coil



[2] Location for inscription label

[5] Port 84 for pilot exhaust air  
[6] Port 82 for pilot exhaust air

[7] For screw M3

Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5	H1
VUVS-LT20-B52-D-G18-...	21.1	16.1	-	2.5	2	G1/8	-	-	M5	8	40.4
VUVS-LT20-B52-ZD-G18-...			2.6				M5	M5			
VUVS-LT20-T32...-MD-G18-...			-				-	-			
VUVS-LT20-T32...-MZD-G18-...			2.6				M5	M5			

Type	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6	L7	L8
VUVS-LT20-B52-D-G18-...	20.9	6.2	46.7	36.4	174.9	144.3	171.7	142.7	139.1	113.7	47.3	19.2
VUVS-LT20-B52-ZD-G18-...												
VUVS-LT20-T32...-MD-G18-...												
VUVS-LT20-T32...-MZD-G18-...												

Type	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-LT20-B52-D-G18-...	30.6	-	29	-	76.9	56.9	36.9	8	45.6	22.5	52.9
VUVS-LT20-B52-ZD-G18-...		94.3		19.5							
VUVS-LT20-T32...-MD-G18-...		-		-							
VUVS-LT20-T32...-MZD-G18-...		94.3		19.5							

# Solenoid valves VUVS-LT, size 20


Accessories

**FESTO**

## Dimensions

Foot mounting

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1 ∅	D2 ∅	D3	H1	H2	H3	H4
VAME-B10-20-A	VUVS-LT20-B52/T32	20	13.1	10.6	3.2	4.2	5.2	112.5	106.5	77.5
	VUVS-LT20-M52									
	VUVS-LT20-M32									

Type	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14
VAME-B10-20-A	VUVS-LT20-B52/T32	44	39	19.2	10.5	2.5	184.4	184.4	184.4	184.4
	VUVS-LT20-M52									
	VUVS-LT20-M32									

Type	H15	L1	L2	L3	L4	L5	L6	L7	L8	L9
VAME-B10-20-A	VUVS-LT20-B52/T32	97.7	55	41	29.4	19.2	40	20	19	174.9 141.2 100.4
	VUVS-LT20-M52									
	VUVS-LT20-M32									


# Solenoid valves VUVS-LT, size 20

**FESTO**

Accessories

## Dimensions

Wall mounting



Download CAD data ➔ [www.festo.com](http://www.festo.com)




Type	B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-LT20-B52/T32	10	M3	M4	M5	35	20	10	11.5	9.7
	VUVS-LT20-M52									8.7
	VUVS-LT20-M32									

Type	H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	VUVS-LT20-B52/T32	22.7	17.7	50	40	20	87.5	87.5	56.9
	VUVS-LT20-M52							53.7	-
	VUVS-LT20-M32							12.9	

# Solenoid valves VUVS-LT, size 20

Accessories

**FESTO**

Ordering data		Code	Valve function	Part no.	Type
3/2-way valve without solenoid coil (24 V DC)					
	Single solenoid, normally closed	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	577490	VUVS-LT20-M32C-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow not reversible	577491	VUVS-LT20-M32C-MZD-G18-F7
	Monostable, normally open	M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	577492	VUVS-LT20-M32U-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow not reversible	577493	VUVS-LT20-M32U-MZD-G18-F7
3/2-way valve with solenoid coil (24 V DC)					
	Monostable, normally closed, type C	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	577511	VUVS-LT20-M32C-MD-G18-F7-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	577512	VUVS-LT20-M32C-MZD-G18-F7-1C1
	Monostable, normally open, type C	M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	577513	VUVS-LT20-M32U-MD-G18-F7-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	577514	VUVS-LT20-M32U-MZD-G18-F7-1C1
2x 3/2-way valve without solenoid coil (24 V DC)					
	Monostable, normally closed	T32C	Mechanical spring return, internal pilot air supply, direction of flow not reversible	577498	VUVS-LT20-T32C-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow not reversible	577499	VUVS-LT20-T32C-MZD-G18-F7
	Monostable, normally open	T32U	Mechanical spring return, internal pilot air supply, direction of flow not reversible	577500	VUVS-LT20-T32U-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow not reversible	577501	VUVS-LT20-T32U-MZD-G18-F7
Monostable, 1x normally open, 1x normally closed					
	Mechanical spring return, internal pilot air supply, direction of flow not reversible	T32H	577502	VUVS-LT20-T32H-MD-G18-F7	
	Mechanical spring return, external pilot air supply, direction of flow not reversible		577503	VUVS-LT20-T32H-MZD-G18-F7	

# Solenoid valves VUVS-LT, size 20

**FESTO**

Accessories


Ordering data		Code	Valve function	Part no.	Type
2x 3/2-way valve with solenoid coil (24 V DC)					
		T32C	Monostable, normally closed, type C Mechanical spring return, internal pilot air supply, direction of flow not reversible Mechanical spring return, external pilot air supply, direction of flow not reversible	577519 577520	VUVS-LT20-T32C-MD-G18-F7-1C1 VUVS-LT20-T32C-MZD-G18-F7-1C1
		T32U	Monostable, normally open, type C Mechanical spring return, internal pilot air supply, direction of flow not reversible Mechanical spring return, external pilot air supply, direction of flow not reversible	577521 577522	VUVS-LT20-T32U-MD-G18-F7-1C1 VUVS-LT20-T32U-MZD-G18-F7-1C1
		T32H	Monostable, 1x normally open, 1x normally closed, type C Mechanical spring return, internal pilot air supply, direction of flow not reversible Mechanical spring return, external pilot air supply, direction of flow not reversible	577523 577524	VUVS-LT20-T32H-MD-G18-F7-1C1 VUVS-LT20-T32H-MZD-G18-F7-1C1
5/2-way valve without solenoid coil (24 V DC)					
		M52-M	Monostable Mechanical spring return, internal pilot air supply, direction of flow not reversible Mechanical spring return, external pilot air supply, direction of flow not reversible	577494 577495	VUVS-LT20-M52-MD-G18-F7 VUVS-LT20-M52-MZD-G18-F7
		B52	Bistable Internal pilot air supply, direction of flow not reversible External pilot air supply, direction of flow not reversible	577496 577497	VUVS-LT20-B52-D-G18-F7 VUVS-LT20-B52-ZD-G18-F7
5/2-way valve with solenoid coil (24 V DC)					
		M52-M	Single solenoid, type C Mechanical spring return, internal pilot air supply, direction of flow not reversible Mechanical spring return, external pilot air supply, direction of flow not reversible	577515 577516	VUVS-LT20-M52-MD-G18-F7-1C1 VUVS-LT20-M52-MZD-G18-F7-1C1
		B52	Bistable Internal pilot air supply, direction of flow not reversible External pilot air supply, direction of flow not reversible	577517 577518	VUVS-LT20-B52-D-G18-F7-1C1 VUVS-LT20-B52-ZD-G18-F7-1C1

# Solenoid valves VUVS-LT, size 20

Accessories

**FESTO**

Ordering data		Description	Part no.	Type
Solenoid coils for valves				
	Connection pattern type C, to DIN EN 175301-803	12 V DC	<b>8025331</b>	VACS-C-C1-5
		24 V DC	<b>8025330</b>	VACS-C-C1-1
		48 V DC	<b>8025336</b>	VACS-C-C1-7
		24 V AC/50-60 Hz	<b>8025335</b>	VACS-C-C1-1A
		48 V AC/50-60 Hz	<b>8025337</b>	VACS-C-C1-7A
		110/120 V AC/50-60 Hz	<b>8025334</b>	VACS-C-C1-16B
		230/240 V AC/50-60 Hz	<b>8025338</b>	VACS-C-C1-3W
Seal set				
	For solenoid valves in order to guarantee protection class IP67			<b>2643771</b> VAMC-B10-C-B-S8
Cover cap				
	For manual override, non-detenting or covered			<b>8028240</b> VAMC-B10-20-CH2

Ordering data		Description	Part no.	Type
Plug socket				
	Connection pattern type C, to DIN EN 175301-803			
	3-pin, screw terminal	Cable fitting M12	0 ... 250 V AC/DC	IP65
		Cable fitting Pg7		
	4-pin, insulation displacement connector	Cable fitting M14	0 ... 250 V AC/DC	IP67
	3-pin, socket angled	Cable fitting M12	0 ... 24 V DC	IP65
Adapters				
	Socket, type C, to EN 175301-803	Plug connector M12x1, 2-pin, A-coded	12 ... 24 V AC/DC	IP65
Plug socket with cable				
	Connection pattern type C, to DIN EN 175301-803			
	Angled socket, 3-pin Cable, open end, 3-wire		24 V DC	LED
	5 m		<b>★ 151688</b> KMEB-1-24-2,5-LED	
	10 m		<b>151689</b> KMEB-1-24-5-LED	
	230 V AC	-	<b>193457</b> KMEB-1-24-10-LED	
	2.5 m		<b>151690</b> KMEB-1-230AC-2,5	
	5 m		<b>151691</b> KMEB-1-230AC-5	
Illuminating seal				
	Connection pattern type C, to DIN EN 175301-803		24 V DC	<b>151717</b> MEB-LD-12-24DC
		230 V AC	<b>151718</b> MEB-LD-230AC	

Festo core product range

★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LT, size 20

**FESTO**

Accessories

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Push-in fitting with internal hex</b>					
	Connecting thread M5 for tubing O.D.	4 mm	<b>★ 153315</b>	<b>QSM-M5-4-I</b>	<b>10</b>
	Connecting thread G1/8 for tubing O.D.	4 mm	<b>★ 186106</b>	<b>QS-G1/8-4-I</b>	<b>10</b>
			<b>133008</b>	<b>QS-G1/8-4-I-100</b>	<b>100</b>
		6 mm	<b>★ 186107</b>	<b>QS-G1/8-6-I</b>	<b>10</b>
			<b>133009</b>	<b>QS-G1/8-6-I-100</b>	<b>100</b>
		8 mm	<b>★ 186109</b>	<b>QS-G1/8-8-I</b>	<b>10</b>
			<b>133010</b>	<b>QS-G1/8-8-I-100</b>	<b>100</b>
<b>Angled push-in fitting with external hex</b>					
	Connecting thread G1/8 for tubing O.D.-	4 mm	<b>★ 186116</b>	<b>QLS-G1/8-4</b>	<b>10</b>
			<b>132048</b>	<b>QLS-G1/8-4-100</b>	<b>100</b>
		6 mm	<b>★ 186117</b>	<b>QLS-G1/8-6</b>	<b>10</b>
			<b>132049</b>	<b>QLS-G1/8-6-100</b>	<b>100</b>
		8 mm	<b>★ 186119</b>	<b>QLS-G1/8-8</b>	<b>10</b>
			<b>132050</b>	<b>QLS-G1/8-8-50</b>	<b>50</b>
<b>Angled push-in fitting, long, with external hex</b>					
	Connecting thread G1/8 for tubing O.D.-	4 mm	<b>186127</b>	<b>QSLL-G1/8-4</b>	<b>10</b>
			<b>133015</b>	<b>QSLL-G1/8-4-100</b>	<b>100</b>
		6 mm	<b>186128</b>	<b>QSLL-G1/8-6</b>	<b>10</b>
			<b>133016</b>	<b>QSLL-G1/8-6-100</b>	<b>100</b>
		8 mm	<b>186130</b>	<b>QSLL-G1/8-8</b>	<b>10</b>
			<b>133017</b>	<b>QSLL-G1/8-8-100</b>	<b>100</b>
<b>Silencer</b>					
	With connecting thread G, Polymer design	G1/8	<b>★ 2307</b>	<b>U-1/8</b>	<b>1</b>
			<b>534222</b>	<b>U-1/8-50</b>	<b>50</b>
	With connecting thread G, Metal version	G1/8	<b>★ 6841</b>	<b>U-1/8-B</b>	<b>1</b>
	With connecting thread G, Sinter design, long	G1/8	<b>★ 1205860</b>	<b>AMTE-M-LH-G18</b>	<b>20</b>

1) Packaging unit quantity

Festo core product range


**★** Generally ready for shipping ex works in 24 hours

**☆** Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LT, size 20

Accessories

FESTO

Ordering data		Description	Weight [g]	Part no.	Type
Foot mounting					
	With screw set for attaching the valve to the foot mounting	97		576412	VAME-B10-20-A
Wall mounting					
	With screw set for attaching the valve to the wall mounting	53		576413	VAME-B10-20-W
Set of spare parts					
	Set comprising seals and screws	10		8026203	VAME-B10-20-MK
Inscription label					
	40 pieces in frame	-		565306	ASLR-C-E4

# Solenoid valves VUVS-LT, size 25


**FESTO**

Data sheet

-  - Flow rate  
Up to 1000 l/min

-  - Valve width  
26.5 mm

-  - Voltage  
24 V DC



## General technical data

Valve function	3/2-way valve				5/2-way valve		
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52
Valve width [mm]	26.5						
Nominal width [mm]	6.9	6.6	6.9	6.6	6.9	6.6	6.6
Design	Disc seat						
Flow direction	Non-reversible						
Pilot air supply	Internal or external						
Type of control	Piloted						
Manual override	Non-detenting, detenting						
Overlap	Underlap						
Sealing principle	Soft						
Type of mounting	Optionally via through-hole or on manifold rail						
Standard nominal flow rate qnN [l/min]	1000						
Type of actuation	Electrical						
Mounting position	Optional						
Exhaust function	With flow control						
Connection for venting hole	Not ducted						
b value	0.4	0.3	0.4	0.3	0.4	0.3	0.2
c value [l/sbar]	4.4	4.2	4.5	4.4	4.4	4.5	4.6
Pneumatic connection 1, 2, 3	G1/4	G1/4	G1/4	G1/4	G1/4	G1/4	G1/4
4, 5	-	-	G1/4	G1/4	G1/4	G1/4	G1/4
Pilot air port 12, 14	M5	M5	M5	M5	M5	M5	M5
Pilot exhaust air port 82, 84	M5	M5	M5	M5	M5	M5	M5

## ATEX

Type	VUVS-LT-...-EX2
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T4 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T115°C X Dc
Explosion-proof ambient temperature rating	-10 °C <= Ta <= +60 °C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

# Solenoid valves VUVS-LT, size 25

Data sheet

**FESTO**

Technical data							
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52
Normal position	Closed	Open	2x closed	2x normally open	1x normally open, 1x normally closed	-	-
Stable position	Monostable	Monostable	Monostable	Monostable	Monostable	Monostable	Bistable
Reset method	Mechanical spring		Mechanical spring			Mechanical spring	-
Switching times in [ms]	On	10	10	10	10	13	-
	Off	23	27	25	25	22	-
	Change-over	-	-	-	-	-	10
Product weight excluding solenoid coil	[g]	208	208	312	312	299	310
Product weight including solenoid coil	[g]	260	260	415	415	351	415

Safety data	
Max. positive test pulse 0 signal	[μs] 2000 (valves with VACF-B....-1)
Max. negative test pulse 1 signal	[μs] 3600 (valves with VACF-B....-1)
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

Operating and environmental conditions									
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52		
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]								
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]								
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)								
Operating pressure with internal pilot air supply	[bar] 2.5 ... 10					2.5 ... 10	1.5 ... 10		
Operating pressure with external pilot air supply	[bar] -0.9 ... 10					2.5 ... 10	1.5 ... 10		
Pilot pressure	[bar] 2.5 ... 10					2.5 ... 10	1.5 ... 10		
Ambient temperature	[°C] -5 ... +60					-10 ... +60			
Temperature of medium	[°C] -5 ... +60					-10 ... +60			
Approval	c UL us - Recognized (OL)								
Corrosion resistance class CRC <sup>1)</sup>	2								

1) Corrosion resistance class CRC 2 to Festo standard FN 940070  
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

# Solenoid valves VUVS-LT, size 25

FESTO

Data sheet

Electrical		With solenoid coil	Without solenoid coil
Electrical connection		Plug connector type C, plug connector type B	Via solenoid coil ➔ Internet: vacf
Operating voltage [V DC]	24		
Permissible voltage fluctuations [%]	10		
Power [W]	3.3		
Duty cycle [%]	100		
Degree of protection to EN 60529	IP65 with plug socket		

Materials	
Housing	Die-cast aluminium (painted)
Seals	HNBR, NBR, TPE-U(PU)
Screws	Galvanised steel
Note on materials	RoHS-compliant


# Solenoid valves VUVS-LT, size 25

Data sheet

**FESTO**


## Dimensions

3/2-way valves, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

3/2-way valves, without solenoid coil



[1] Solenoid coil interface  
type B/type C

[4] Port 10/12 for pilot air supply

[6] Port 82 for pilot exhaust air

[7] For screw M4

[2] Location for inscription label

Type	B1	B2	B3	B4	B5	B6	D1	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-LT25-M32...D-G14...	26.5	20.2	—	1.9	1.9	22	G1/4	—	M5	8	50.5	28.2	8	57.2	45.2
VUVS-LT25-M32...ZD-G14...			4.5					M5							

Type	L2	L4	L5	L6	L7	L8	L9	L11	L12	L14	L15	L16	L17	L19
VUVS-LT25-M32...D-G14...	118.7	117.6	113.3	84.3	53.3	25	34.4	33.3	—	65.8	41.3	13	50.4	59.3
VUVS-LT25-M32...ZD-G14...									20.3					


# Solenoid valves VUVS-LT, size 25

FESTO

Data sheet

## Dimensions

5/2-way single solenoid valves, with solenoid coil



[1] Solenoid coil


[2] Location for inscription label

[3] Port 14 for pilot air supply

[4] Port 12 for pilot air supply

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way single solenoid valves, without solenoid coil



[5] Port 84 for pilot exhaust air

[7] For screw M4

Type	B1	B2	B3	B4	B5	B6	D1	D2	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-LT25-M52-...D-G14-...	26.5	20.2	-	1.9	1.9	22	G1/4	-	-	M5	8	50.5	28.2	8	57.2	45.2
VUVS-LT25-M52-...ZD-G14-...				4.5						M5						

Type	L2	L4	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-LT25-M52-...D-G14-...	162.2	161.1	156.8	127.8	53.3	25	34.4	-	33.3	-	90.3	65.8	41.3	13	50.4	30.8	59.3
VUVS-LT25-M52-...ZD-G14-...									111.3		20.3						




# Solenoid valves VUVS-LT, size 25

Data sheet

**FESTO**

## Dimensions

2x 3/2-way valves and 5/2-way valves, bistable, with solenoid coil



[1] Solenoid coil


[2] Location for inscription label

[3] Port 14 for pilot air supply

[4] Port 12 for pilot air supply

Download CAD data → [www.festo.com](http://www.festo.com)

2x 3/2-way valve and 5/2-way valve, bistable, without solenoid coil



Type	B1	B2	B3	B4	B5	B6	D1	D2	D3	D4	D5	H1
VUVS-LT25-B52-D-G14-...	26.5	20.2	—	1.9	1.9	22	G1/4	—	—	M5	8	50.5
VUVS-LT25-B52-ZD-G14-...			4.5					M5	M5			
VUVS-LT25-T32-MD-G14-...			—					—	—			
VUVS-LT25-T32-MZD-G14-...			4.5					M5	M5			

Type	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6	L7	L8
VUVS-LT25-B52-D-G14-...	28.2	8	57.2	45.2	200.3	166	198.2	164.9	160.6	131.6	53.3	25
VUVS-LT25-B52-ZD-G14-...												
VUVS-LT25-T32-MD-G14-...												
VUVS-LT25-T32-MZD-G14-...												

Type	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-LT25-B52-D-G14-...	33.3	—	33.3	—	90.3	65.8	41.3	13	50.4	30.8	59.3
VUVS-LT25-B52-ZD-G14-...		111.3		20.3							
VUVS-LT25-T32-MD-G14-...		—		—							
VUVS-LT25-T32-MZD-G14-...		111.3		20.3							

# Solenoid valves VUVS-LT, size 25


FESTO

Accessories

## Dimensions

Foot mounting

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1	D2	D3	H1	H2	H3	H4	
VAME-B10-25-A	VUVS-LT25-B52/T32	24	15.8	13.3	4.2	4.2	5.2	130	122.5	91	80.5
	VUVS-LT25-M52										
	VUVS-LT25-M32										
Type	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14	
VAME-B10-25-A	VUVS-LT25-B52/T32	48.5	41.5	25	11	2.5	210.2	–	210.2	210.2	
	VUVS-LT25-M52							178.7	172	172	
	VUVS-LT25-M32								138.9	138.9	
Type	H15	L1	L2	L3	L4	L5	L6	L7	L8	L9	
VAME-B10-25-A	VUVS-LT25-B52/T32	123	55	49.4	40.4	25	40	20	23.5	200.3	
	VUVS-LT25-M52									162.2	
	VUVS-LT25-M32									118.7	


# Solenoid valves VUVS-LT, size 25

Accessories

FESTO

## Dimensions

Wall mounting



[1] Mounting hole for size 20

[2] Mounting hole size 25

[3] Mounting hole for size 30



Type		B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-LT25-B52/T32	10	M3	M4	M5	35	20	10	11.5	9.7	8.7
	VUVS-LT25-M52										
	VUVS-LT25-M32										

Type		H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	VUVS-LT25-B52/T32	32.8	17.7	50	40	20	100.2	100.2	65.8	65.8
	VUVS-LT25-M52									
	VUVS-LT25-M32									

# Solenoid valves VUVS-LT, size 25

**FESTO**




Accessories

Ordering data		Code	Valve function	Part no.	Type
3/2-way valve without solenoid coil					
	Single solenoid, normally closed	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035167	VUVS-LT25-M32C-MD-G14-F8
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035168	VUVS-LT25-M32C-MZD-G14-F8
	Monostable, normally open	M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035174	VUVS-LT25-M32U-MD-G14-F8
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035175	VUVS-LT25-M32U-MZD-G14-F8
3/2-way valve with solenoid coil (24 V DC)					
	Monostable, normally closed, type C	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035169	VUVS-LT25-M32C-MD-G14-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035170	VUVS-LT25-M32C-MZD-G14-F8-1C1
	Single solenoid, normally closed, type B	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035171	VUVS-LT25-M32C-MD-G14-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035172	VUVS-LT25-M32C-MZD-G14-F8-1B2
	Monostable, normally open, type C	M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035176	VUVS-LT25-M32U-MD-G14-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035177	VUVS-LT25-M32U-MZD-G14-F8-1C1
	Monostable, normally open, type B	M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035178	VUVS-LT25-M32U-MD-G14-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035179	VUVS-LT25-M32U-MZD-G14-F8-1B2

# Solenoid valves VUVS-LT, size 25

Accessories

**FESTO**

Ordering data		Code	Valve function	Part no.	Type
2x 3/2-way valve without solenoid coil					
	Monostable, normally closed	T32C	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035195	VUVS-LT25-T32C-MD-G14-F8
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035196	VUVS-LT25-T32C-MZD-G14-F8
Monostable, normally open					
	T32U	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035202	VUVS-LT25-T32U-MD-G14-F8	
		Mechanical spring return, external pilot air supply, direction of flow not reversible	8035203	VUVS-LT25-T32U-MZD-G14-F8	
Monostable, 1x normally open, 1x normally closed					
	T32H	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035209	VUVS-LT25-T32H-MD-G14-F8	
		Mechanical spring return, external pilot air supply, direction of flow not reversible	8035210	VUVS-LT25-T32H-MZD-G14-F8	

# Solenoid valves VUVS-LT, size 25

**FESTO**





Accessories

Ordering data		Code	Valve function	Part no.	Type
2x 3/2-way valve with solenoid coil (24 V DC)					
			Monostable, normally closed, type C		
	T32C		Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035197	VUVS-LT25-T32C-MD-G14-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035198	VUVS-LT25-T32C-MZD-G14-F8-1C1
			Single solenoid, normally closed, type B		
	T32C		Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035199	VUVS-LT25-T32C-MD-G14-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035200	VUVS-LT25-T32C-MZD-G14-F8-1B2
			Monostable, normally open, type C		
	T32U		Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035204	VUVS-LT25-T32U-MD-G14-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035205	VUVS-LT25-T32U-MZD-G14-F8-1C1
			Monostable, normally open, type B		
	T32U		Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035206	VUVS-LT25-T32U-MD-G14-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035207	VUVS-LT25-T32U-MZD-G14-F8-1B2
			Monostable, 1x normally open, 1x normally closed, type C		
	T32H		Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035211	VUVS-LT25-T32H-MD-G14-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035212	VUVS-LT25-T32H-MZD-G14-F8-1C1
			Monostable, 1x normally open, 1x normally closed, type B		
	T32H		Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035213	VUVS-LT25-T32H-MD-G14-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035214	VUVS-LT25-T32H-MZD-G14-F8-1B2

# Solenoid valves VUVS-LT, size 25

Accessories

**FESTO**

Ordering data		Code	Valve function	Part no.	Type
5/2-way valve without solenoid coil					
	Monostable	M52	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035181	VUVS-LT25-M52-MD-G14-F8
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035182	VUVS-LT25-M52-MZD-G14-F8
5/2-way valve with solenoid coil (24 V DC)					
	Bistable	B52	Internal pilot air supply, direction of flow not reversible	8035188	VUVS-LT25-B52-D-G14-F8
			External pilot air supply, direction of flow not reversible	8035189	VUVS-LT25-B52-ZD-G14-F8
		M52-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035183	VUVS-LT25-M52-MD-G14-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035184	VUVS-LT25-M52-MZD-G14-F8-1C1
	Single solenoid, type C	M52-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8035185	VUVS-LT25-M52-MD-G14-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8035186	VUVS-LT25-M52-MZD-G14-F8-1B2
		B52	Double solenoid, type C	8035190	VUVS-LT25-B52-D-G14-F8-1C1
			Internal pilot air supply, direction of flow not reversible	8035191	VUVS-LT25-B52-ZD-G14-F8-1C1
	Double solenoid, type B	B52	Double solenoid, type B	8035192	VUVS-LT25-B52-D-G14-F8-1B2
			Internal pilot air supply, direction of flow not reversible	8035193	VUVS-LT25-B52-ZD-G14-F8-1B2

# Solenoid valves VUVS-LT, size 25

**FESTO**


Accessories

Ordering data		Description	Part no.	Type
Solenoid coils for valves				
	Connection pattern type C, to DIN EN 175301-803	12 V DC	<b>8030810</b>	VACF-B-C1-5
		24 V DC	<b>8030811</b>	VACF-B-C1-1
		48 V DC	<b>8030812</b>	VACF-B-C1-7
		24 V AC/50-60 Hz	<b>8030813</b>	VACF-B-C1-1A
		48 V AC/50-60 Hz	<b>8030814</b>	VACF-B-C1-7A
		110/120 V AC/50-60 Hz	<b>8030815</b>	VACF-B-C1-16B
		230/240 V AC/50-60 Hz	<b>8030817</b>	VACF-B-C1-3W
	Connection pattern type B, industry standard	12 V DC	<b>8030801</b>	VACF-B-B2-5
		24 V DC	<b>8030802</b>	VACF-B-B2-1
		48 V DC	<b>8030803</b>	VACF-B-B2-7
		24 V AC/50-60 Hz	<b>8030804</b>	VACF-B-B2-1A
		48 V AC/50-60 Hz	<b>8030805</b>	VACF-B-B2-7A
		110/120 V AC/50-60 Hz	<b>8030806</b>	VACF-B-B2-16B
		230/240 V AC/50-60 Hz	<b>8030808</b>	VACF-B-B2-3W
Seal-SET for solenoid coil				
	Connection pattern type C to guarantee protection class IP67		<b>2643771</b>	VAMC-B10-C-B-S8
	Connection pattern type B to guarantee protection class IP67		<b>8034609</b>	VAMC-B10-B-B-S8
Cover cap				
	For manual override, non-detenting or covered		<b>8028240</b>	VAMC-B10-20-CH2

# Solenoid valves VUVS-LT, size 25

Accessories

FESTO

Ordering data		Description	Part no.	Type		
<b>Plug socket</b>						
	Connection pattern type C, to DIN EN 175301-803					
	3-pin, screw terminal	Cable fitting M12	0 ... 250 V AC/DC	IP65	539712 MSSD-EB-M12	
		Cable fitting Pg7			★ 151687 MSSD-EB	
	4-pin, insulation displacement connector	Cable fitting M14	0 ... 250 V AC/DC	IP67	192745 MSSD-EB-S-M14	
	3-pin, socket angled	Cable fitting M12	0 ... 24 V DC	IP65	570367 MSSD-EB-M12-24VDC-SD-EX	
	Connection pattern type B, industry standard					
	3-pin, screw terminal	Cable fitting M16	0 ... 250 V AC/DC	IP65	539710 MSSD-F-M16	
		Cable fitting Pg9			★ 34431 MSSD-F	
3-pin, insulation displacement connector	-	0 ... 250 V AC/DC	IP67	192746 MSSD-F-S-M16		
<b>Adapters</b>						
	Socket, type C, to EN 175301-803	Plug connector M12x1, 2-pin, A-coded	12 ... 24 V AC/DC	IP65	188024 MSSD-EB-M12-MONO	
<b>Plug socket with cable</b>						
	Connection pattern type C, to DIN EN 175301-803					
	Angled socket, 3-pin	Cable, open end, 3-wire	24 V DC	LED	2.5 m	★ 151688 KMEB-1-24-2,5-LED
	Cable, open end, 3-wire		5 m		151689 KMEB-1-24-5-LED	
			10 m	193457 KMEB-1-24-10-LED		
	230 V AC		-	2.5 m	151690 KMEB-1-230AC-2,5	
		5 m		151691 KMEB-1-230AC-5		
	Connection pattern type B, industry standard					
	Angled socket, 3-pin	Cable, open end, 3-wire	24 V DC	LED	2.5 m	★ 30935 KMF-1-24DC-2,5-LED
	Cable, open end, 3-wire		5 m		30937 KMF-1-24DC-5-LED	
			10 m	193458 KMF-1-24-10-LED		
230 V AC	-		2.5 m	30936 KMF-1-230AC-2,5		
			5 m	30938 KMF-1-230AC-5		
<b>Illuminating seal</b>						
	Connection pattern type C, to DIN EN 175301-803	24 V DC		151717 MEB-LD-12-24DC		
		230 V AC		151718 MEB-LD-230AC		
	Connection pattern type B, industry standard	24 V DC		19143 MF-LD-12-24DC		
		230 V AC		19144 MF-LD-230AC		

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LT, size 25

**FESTO**

Accessories

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
Push-in fitting with internal hex					
	Connecting thread M5 for tubing O.D.	4 mm	★ 153315	QSM-M5-4-I	10
	Connecting thread G1/4 for tubing O.D.	6 mm	★ 186108	QS-G1/4-6-I	10
		8 mm	★ 186110	QS-G1/4-8-I	10
		10 mm	★ 186112	QS-G1/4-10-I	10
Angled push-in fitting with external hex					
	Connecting thread G1/4 for tubing O.D.	6 mm	★ 186118	QSL-G1/4-6	10
			132051	QSL-G1/4-6-100	100
		8 mm	★ 186120	QSL-G1/4-8	10
			132052	QSL-G1/4-8-50	50
		10 mm	★ 186122	QSL-G1/4-10	10
			132053	QSL-G1/4-10-50	50
Angled push-in fitting, long, with external hex					
	Connecting thread G1/4 for tubing O.D.	6 mm	186129	QSLL-G1/4-6	10
		8 mm	186131	QSLL-G1/4-8	10
		10 mm	186133	QSLL-G1/4-10	10
Silencer					
	With connecting thread G, polymer design	G1/4	★ 2316	U-1/4	1
			534223	U-1/4-20	20
	With connecting thread G, metal design	G1/4	★ 6842	U-1/4-B	1
	With connecting thread G, sinter design, long	G1/4	★ 1205861	AMTE-M-LH-G14	20

1) Packaging unit quantity

Festo core product range


★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-LT, size 25

Accessories

FESTO

Ordering data		Description	Weight [g]	Part no.	Type
Foot mounting					
	With screw set for attaching the valve to the foot mounting	130		2293485	VAME-B10-25-A
Wall mounting					
	With screw set for mounting the valve on the wall mounting	53		576413	VAME-B10-20-W
Set of spare parts					
	Set comprising seals and screws	12		8035636	VAME-B10-25-MK
Inscription label					
	40 pieces in frame	-		565306	ASLR-C-E4


**Solenoid valves VUVS-LT, size 30**

Technical data

-  - Flow rate  
Up to 1800 l/min

-  - Valve width  
31 mm

-  - Voltage  
24 V DC

**General technical data**

Valve function	3/2-way valve					5/2-way valve			
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52		
Valve width [mm]	31								
Nominal width [mm]	7.9	7.9	7.9	7.8	7.8	8.1	8.7		
Design	Disc seat								
Flow direction	Non-reversible								
Pilot air supply	Internal or external								
Type of control	Piloted								
Manual override	Non-detenting, detenting								
Overlap	Underlap								
Sealing principle	Soft								
Type of mounting	Optionally via through-hole or on manifold rail								
Standard nominal flow rate qnN [l/min]	1600					1800			
Type of actuation	Electrical								
Mounting position	Optional								
Exhaust function	With flow control								
Connection for venting hole	Not ducted								
b value	0.4	0.2	0.4	0.3	0.3	0.3	0.3		
c value [l/sbar]	6.0	7.0	6.0	6.7	6.7	9.9	9.9		
Pneumatic connection 1, 2, 3	G3/8	G3/8	G3/8	G3/8	G3/8	G3/8	G3/8		
4, 5	-	-	G3/8	G3/8	G3/8	G3/8	G3/8		
Pilot air port 12, 14	G1/8	G1/8	G1/8	G1/8	G1/8	G1/8	G1/8		
Pilot exhaust air port 82, 84	M5	M5	M5	M5	M5	M5	M5		

**ATEX**

Type	VUVS-LT-...-EX2
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T4 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T115°C X Dc
Explosion-proof ambient temperature rating	-10 °C <= Ta <= +60 °C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

## Solenoid valves VUVS-LT, size 30

Technical data

**FESTO**

Technical data							
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52
Normal position	Closed	Open	2x closed	2x normally open	1x normally open, 1x normally closed	-	-
Stable position	Monostable	Monostable	Monostable	Monostable	Monostable	Monostable	Bistable
Reset method	Mechanical spring		Mechanical spring			Mechanical spring	-
Switching times in [ms]	On	13	14	13	14	13	17
	Off	32	36	33	35	37	26
	Change-over	-	-	-	-	-	13
Product weight excluding solenoid coil	[g]	305	305	442	442	442	432
Product weight including solenoid coil	[g]	359	359	543	543	543	486
							542

Safety data	
Max. positive test pulse 0 signal	[μs] 2000 (valves with VACF-B....-1)
Max. negative test pulse 1 signal	[μs] 3600 (valves with VACF-B....-1)
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

Operating and environmental conditions									
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52		
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]								
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]								
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)								
Operating pressure with internal pilot air supply	[bar] 2.5 ... 10				2.5 ... 10	1.5 ... 10			
Operating pressure with external pilot air supply	[bar] 1.0 ... 10				2.5 ... 10	1.5 ... 10			
Pilot pressure	[bar] 2.5 ... 10				2.5 ... 10	1.5 ... 10			
Ambient temperature	[°C] -10 ... +60				2.5 ... 10	1.5 ... 10			
Temperature of medium	[°C] -10 ... +60				2.5 ... 10	1.5 ... 10			
Approval	c UL us - Recognized (OL)								
Corrosion resistance class CRC <sup>1)</sup>	2								

1) Corrosion resistance class CRC 2 to Festo standard FN 940070  
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

## Solenoid valves VUVS-LT, size 30

Technical data

Electrical		With solenoid coil	Without solenoid coil
Electrical connection		Plug connector type C, plug connector type B	Via solenoid coil ➔ Internet: vacf
Operating voltage [V DC]	24		
Permissible voltage fluctuations [%]	10		
Power [W]	3.3		
Duty cycle [%]	100		
Degree of protection to EN 60529	IP65 with plug socket		

Materials							
Order code for valves	M32C	M32U	T32C	T32U	T32H	M52	B52
Housing	Die-cast aluminium (painted)						
Seals	HNBR, NBR, TPE-U(PU)						
Piston spool	Wrought aluminium alloy				POM	POM	
Screws	Galvanised steel						
Note on materials	RoHS-compliant						


## Solenoid valves VUVS-LT, size 30

Technical data

FESTO


### Dimensions

3/2-way valves, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

3/2-way valves, without solenoid coil



[1] Solenoid coil

[4] Port 10/12 for pilot air supply

[6] Port 82 for pilot exhaust air

[7] For screw M5

[2] Location for inscription label

Type	B1	B2	B3	B4	B5	D1	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-LT30-M32...-...D-G38...	31	23.3	—	2.5	2.5	G3/8	—	M5	8	57	31.8	9	64.7	52.6
VUVS-LT30-M32...-...ZD-G38...			4.6				G1/8							




Type	L2	L4	L5	L6	L7	L8	L9	L11	L12	L14	L15	L16	L17	L19
VUVS-LT30-M32...-...D-G38...	133.2	131.1	127.8	97.8	59.3	31	35.4	33.3	—	74.8	44.8	17	56	66.3
VUVS-LT30-M32...-...ZD-G38...									20.8					

# Solenoid valves VUVS-LT, size 30

Technical data

## Dimensions

5/2-way single solenoid valves, with solenoid coil




[1] Solenoid coil interface  
type B/type C

[2] Location for inscription label

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way single solenoid valves, without solenoid coil



[5] Port 84 for pilot exhaust air

[7] For screw M5

Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-LT30-M52-...D-G38-...	31	23.3	—	2.5	2.5	G3/8	—	—	M5	8	57	31.8	9	64.7	52.6
VUVS-LT30-M52-...ZD-G38-...			4.6				G1/8	G1/8							

Type	L2	L4	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-LT30-M52-...D-G38-...	180.7	178.6	179.6	145.3	59.3	31	35.4	—	33.3	—	104.8	74.8	44.8	17	56	37.6	66.3
VUVS-LT30-M52-...ZD-G38-...								128.8		20.8							


## Solenoid valves VUVS-LT, size 30

Technical data

FESTO


### Dimensions

2x 3/2-way valves and 5/2-way valves, bistable, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

2x 3/2-way valve and 5/2-way valve, bistable, without solenoid coil



[1] Solenoid coil interface  
type B/type C

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply

[5] Port 84 for pilot exhaust air  
[6] Port 82 for pilot exhaust air

[7] For screw M5

[2] Location for inscription label

Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-LT30-T32...-MD-G38-...	31	23.3	—	2.5	2.5	G3/8	—	—	M5	8	57	31.8	9	64.7	52.6
VUVS-LT30-T32...-MZD-G38-...			4.6				G1/8	G1/8							
VUVS-LT30-B52-D-G38-...			—				—	—							
VUVS-LT30-B52-ZD-G38-...			4.6				G1/8	G1/8							

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VUVS-LT30-T32...-MD-G38-...	220.3	185	216.2	182.9	179.6	149.6	59.3	31	35.4	—
VUVS-LT30-T32...-MZD-G38-...										128.8
VUVS-LT30-B52-D-G38-...										—
VUVS-LT30-B52-ZD-G38-...										128.8

Type	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-LT30-T32...-MD-G38-...	33.3	—	104.8	74.8	44.8	17	56	37.6	66.3
VUVS-LT30-T32...-MZD-G38-...		20.8							
VUVS-LT30-B52-D-G38-...		—							
VUVS-LT30-B52-ZD-G38-...		20.8							


# Solenoid valves VUVS-LT, size 30

**FESTO**

Accessories

**Dimensions**

Foot mounting

[Download CAD data ➔ www.festo.com](#)


Type		B1	B2	B3	D1 ∅	D2 ∅	D3	D4	H1	H2	H3
VAME-B10-30-A	VUVS-LT30-B52/T32	26.8	18.5	15.5	5.2	4.2	5.2	5.2	146	136.5	102.5
	VUVS-LT30-M52										
	VUVS-LT30-M32										

Type		H4	H5	H7	H8	H9	H10	H11	H12	H13	H14
VAME-B10-30-A	VUVS-LT30-B52/T32	112	50.5	31	11.5	3	231.2	—	231.2	231.2	231.2
	VUVS-LT30-M52										
	VUVS-LT30-M32							197.2	191.5	191.5	144

Type		H15	L1	L3	L4	L5	L6	L7	L8	L9
VAME-B10-30-A	VUVS-LT30-B52/T32	160	57	45.6	31	40	20	32	220.3	4.1
	VUVS-LT30-M52									
	VUVS-LT30-M32								180.7	
									133.2	


## Solenoid valves VUVS-LT, size 30

Accessories

**FESTO**

### Dimensions

Wall mounting





Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-LT30-B52/T32	10	M3	M4	M5	35	20	10	11.5	9.7
	VUVS-LT30-M52									8.7
	VUVS-LT30-M32									

Type	H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	39.3	17.7	50	40	20	110.2	110.2	74.8	74.8
	VUVS-LT30-B52/T32							70.5	
	VUVS-LT30-M52							23	-
VUVS-LT30-M32									

## Solenoid valves VUVS-LT, size 30


Accessories

Ordering data		Code	Valve function	Part no.	Type
3/2-way valve without solenoid coil					
	Single solenoid, normally closed	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036672	VUVS-LT30-M32C-MD-G38-F8
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036673	VUVS-LT30-M32C-MZD-G38-F8
	Monostable, normally open	M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036679	VUVS-LT30-M32U-MD-G38-F8
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036680	VUVS-LT30-M32U-MZD-G38-F8
3/2-way valve with solenoid coil (24 V DC)					
	Monostable, normally closed, type C	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036674	VUVS-LT30-M32C-MD-G38-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036675	VUVS-LT30-M32C-MZD-G38-F8-1C1
	Single solenoid, normally closed, type B	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036676	VUVS-LT30-M32C-MD-G38-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036677	VUVS-LT30-M32C-MZD-G38-F8-1B2
	Monostable, normally open, type C	M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036681	VUVS-LT30-M32U-MD-G38-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036682	VUVS-LT30-M32U-MZD-G38-F8-1C1
	Monostable, normally open, type B	M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036683	VUVS-LT30-M32U-MD-G38-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036684	VUVS-LT30-M32U-MZD-G38-F8-1B2

## Solenoid valves VUVS-LT, size 30


Accessories

**FESTO**

Ordering data		Code	Valve function	Part no.	Type
2x 3/2-way valve without solenoid coil					
	Monostable, normally closed	T32C	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036700	VUVS-LT30-T32C-MD-G38-F8
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036701	VUVS-LT30-T32C-MZD-G38-F8
Monostable, normally open					
	T32U	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036707	VUVS-LT30-T32U-MD-G38-F8	
		Mechanical spring return, external pilot air supply, direction of flow not reversible	8036708	VUVS-LT30-T32U-MZD-G38-F8	
Monostable, 1x normally open, 1x normally closed					
	T32H	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036714	VUVS-LT30-T32H-MD-G38-F8	
		Mechanical spring return, external pilot air supply, direction of flow not reversible	8036715	VUVS-LT30-T32H-MZD-G38-F8	

**Solenoid valves VUVS-LT, size 30**





Accessories

Ordering data		Code	Valve function	Part no.	Type
2x 3/2-way valve with solenoid coil (24 V DC)					
	T32C	Monostable, normally closed, type C			
		Mechanical spring return, internal pilot air supply, direction of flow not reversible		8036702	VUVS-LT30-T32C-MD-G38-F8-1C1
	T32C	Mechanical spring return, external pilot air supply, direction of flow not reversible		8036703	VUVS-LT30-T32C-MZD-G38-F8-1C1
		Single solenoid, normally closed, type B			
	T32C	Mechanical spring return, internal pilot air supply, direction of flow not reversible		8036704	VUVS-LT30-T32C-MD-G38-F8-1B2
		Mechanical spring return, external pilot air supply, direction of flow not reversible		8036705	VUVS-LT30-T32C-MZD-G38-F8-1B2
Monostable, normally open, type C					
	T32U	Mechanical spring return, internal pilot air supply, direction of flow not reversible		8036709	VUVS-LT30-T32U-MD-G38-F8-1C1
		Mechanical spring return, external pilot air supply, direction of flow not reversible		8036710	VUVS-LT30-T32U-MZD-G38-F8-1C1
Monostable, normally open, type B					
	T32U	Mechanical spring return, internal pilot air supply, direction of flow not reversible		8036711	VUVS-LT30-T32U-MD-G38-F8-1B2
		Mechanical spring return, external pilot air supply, direction of flow not reversible		8036712	VUVS-LT30-T32U-MZD-G38-F8-1B2
Monostable, 1x normally open, 1x normally closed, type C					
	T32H	Mechanical spring return, internal pilot air supply, direction of flow not reversible		8036716	VUVS-LT30-T32H-MD-G38-F8-1C1
		Mechanical spring return, external pilot air supply, direction of flow not reversible		8036717	VUVS-LT30-T32H-MZD-G38-F8-1C1
Monostable, 1x normally open, 1x normally closed, type B					
	T32H	Mechanical spring return, internal pilot air supply, direction of flow not reversible		8036718	VUVS-LT30-T32H-MD-G38-F8-1B2
		Mechanical spring return, external pilot air supply, direction of flow not reversible		8036719	VUVS-LT30-T32H-MZD-G38-F8-1B2

## Solenoid valves VUVS-LT, size 30

Accessories

**FESTO**

Ordering data		Code	Valve function	Part no.	Type
5/2-way valve without solenoid coil					
	Monostable	M52	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036686	VUVS-LT30-M52-MD-G38-F8
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036687	VUVS-LT30-M52-MZD-G38-F8
5/2-way valve with solenoid coil (24 V DC)					
	Bistable	B52	Internal pilot air supply, direction of flow not reversible	8036693	VUVS-LT30-B52-D-G38-F8
			External pilot air supply, direction of flow not reversible	8036694	VUVS-LT30-B52-ZD-G38-F8
		M52-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036688	VUVS-LT30-M52-MD-G38-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036689	VUVS-LT30-M52-MZD-G38-F8-1C1
	Single solenoid, type C	M52-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	8036690	VUVS-LT30-M52-MD-G38-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow not reversible	8036691	VUVS-LT30-M52-MZD-G38-F8-1B2
		B52	Double solenoid, type C	8036695	VUVS-LT30-B52-D-G38-F8-1C1
			Internal pilot air supply, direction of flow not reversible	8036696	VUVS-LT30-B52-ZD-G38-F8-1C1
	Double solenoid, type B	B52	Double solenoid, type B	8036697	VUVS-LT30-B52-D-G38-F8-1B2
			Internal pilot air supply, direction of flow not reversible	8036698	VUVS-LT30-B52-ZD-G38-F8-1B2

**Solenoid valves VUVS-LT, size 30**

Accessories

Ordering data		Description	Part no.	Type		
Solenoid coils for valves						
	Connection pattern type C, to EN 175301-803	12 V DC	<b>8030810</b>	VACF-B-C1-5		
		24 V DC	<b>8030811</b>	VACF-B-C1-1		
		48 V DC	<b>8030812</b>	VACF-B-C1-7		
		24 V AC/50-60 Hz	<b>8030813</b>	VACF-B-C1-1A		
		48 V AC/50-60 Hz	<b>8030814</b>	VACF-B-C1-7A		
		110/120 V AC/50-60 Hz	<b>8030815</b>	VACF-B-C1-16B		
		230/240 V AC/50-60 Hz	<b>8030817</b>	VACF-B-C1-3W		
	Connection pattern type B, industry standard	12 V DC	<b>8030801</b>	VACF-B-B2-5		
		24 V DC	<b>8030802</b>	VACF-B-B2-1		
		48 V DC	<b>8030803</b>	VACF-B-B2-7		
		24 V AC/50-60 Hz	<b>8030804</b>	VACF-B-B2-1A		
		48 V AC/50-60 Hz	<b>8030805</b>	VACF-B-B2-7A		
		110/120 V AC/50-60 Hz	<b>8030806</b>	VACF-B-B2-16B		
		230/240 V AC/50-60 Hz	<b>8030808</b>	VACF-B-B2-3W		
	Connection pattern type A, to EN 175301-803	12 V DC	<b>8030821</b>	VACF-A-A1-5		
		24 V DC	<b>8030822</b>	VACF-A-A1-1		
		48 V DC	<b>8030823</b>	VACF-A-A1-7		
		24 V AC/50-60 Hz	<b>8030824</b>	VACF-A-A1-1A		
		48 V AC/50-60 Hz	<b>8030825</b>	VACF-A-A1-7A		
		110/120 V AC, 50/60 Hz	<b>8030826</b>	VACF-A-A1-16B		
		230/240 V AC, 50/60 Hz	<b>8030828</b>	VACF-A-A1-3W		
Seal-SET for solenoid coil						
	Connection pattern type C to guarantee protection class IP67		<b>2643771</b>	VAMC-B10-C-B-S8		
	Connection pattern type B to guarantee protection class IP67		<b>8034609</b>	VAMC-B10-B-B-S8		
	Connection pattern type B to guarantee protection class IP67		<b>8034611</b>	VAMC-B10-A-B-S8		
Cover cap						
	For manual override, non-detenting or covered			<b>8028240</b> VAMC-B10-20-CH2		
Plug socket						
	Connection pattern type C, to EN 175301-803					
	3-pin, screw terminal	Cable fitting M12	0 ... 250 V AC/DC	IP65	<b>539712</b>	MSSD-EB-M12
		Cable fitting Pg7			<b>★ 151687</b>	MSSD-EB
	4-pin, insulation displacement connector	Cable fitting M14	0 ... 250 V AC/DC	IP67	<b>192745</b>	MSSD-EB-S-M14
	3-pin, socket angled	Cable fitting M12	0 ... 24 V DC	IP65	<b>570367</b>	MSSD-EB-M12-24VDC-SD-EX
	Connection pattern type B, industry standard					
	3-pin, screw terminal	Cable fitting M16	0 ... 250 V AC/DC	IP65	<b>539710</b>	MSSD-F-M16
		Cable fitting Pg9			<b>★ 34431</b>	MSSD-F
	3-pin, insulation displacement connector	-	0 ... 250 V AC/DC	IP67	<b>192746</b>	MSSD-F-S-M16

Festo core product range


★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

## Solenoid valves VUVS-LT, size 30

Accessories

**FESTO**

Ordering data		Description	Part no.	Type
<b>Plug socket</b>				
	Connection pattern type A, to EN 175301-803			
	3-pin, socket angled	Cable fitting Pg9	0 ... 250 V AC/DC	IP65
	3-pin, socket angled	Cable fitting M16	0 ... 250 V AC/DC	IP65
	4-pin, socket angled	Cable connection, insulation displacement	0 ... 250 V AC/DC	IP67
<b>Adapters</b>				
	Socket, type C, to EN 175301-803	Plug connector M12x1, 2-pin, A-coded	12 ... 24 V AC/DC	IP65
<b>Plug socket with cable</b>				
	Connection pattern type C, to DIN EN 175301-803			
	Angled socket, 3-pin Cable, open end, 3-wire	24 V DC	LED	2.5 m
				5 m
				10 m
		230 V AC	-	2.5 m
				5 m
	Connection pattern type B, industry standard			
	Angled socket, 3-pin Cable, open end, 3-wire	24 V DC	LED	2.5 m
				5 m
		230 V AC	-	10 m
				2.5 m
	Connection pattern type A, to EN 175301-803			
	Angled socket, 3-pin Cable, open end, 3-wire	24 V DC	LED	2.5 m
				5 m
	24 V DC	LED	10 m	193459 KMC-1-24-10-LED
			2.5 m	
	230 V AC	-	2.5 m	30936 KMF-1-230AC-2,5
			5 m	30938 KMF-1-230AC-5
	<b>Illuminating seal</b>			
	Connection pattern type C, to DIN EN 175301-803	24 V DC		151717 MEB-LD-12-24DC
		230 V AC		151718 MEB-LD-230AC
	Connection pattern type B, industry standard	24 V DC		19143 MF-LD-12-24DC
		230 V AC		19144 MF-LD-230AC

Festo core product range

 Generally ready for shipping ex works in 24 hours

 Generally ready for shipping ex works in 5 days

## Solenoid valves VUVS-LT, size 30

Accessories


Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Push-in fitting with internal hex</b>					
	Connecting thread G1/8 for tubing O.D.	4 mm	★ 186106	QS-G1/8-4-I	10
			133008	QS-G1/8-4-I-100	100
	Connecting thread for G3/8 for tubing O.D.	8 mm	★ 186111	QS-G3/8-8-I	10
		10 mm	★ 186113	QS-G3/8-10-I	10
		12 mm	★ 186114	QS-G3/8-12-I	10
<b>Angled push-in fitting with external hex</b>					
	Connecting thread for G3/8 for tubing O.D.	8 mm	★ 186121	QSL-G3/8-8	10
			132055	QSL-G3/8-8-50	50
		10 mm	★ 186123	QSL-G3/8-10	10
			132056	QSL-G3/8-10-20	20
		12 mm	★ 186124	QSL-G3/8-12	10
			132057	QSL-G3/8-12-20	20
<b>Angled push-in fitting, long, with external hex</b>					
	Connecting thread for G3/8 for tubing O.D.	8 mm	186132	QSLL-G3/8-8	10
		10 mm	186134	QSLL-G3/8-10	10
		12 mm	186135	QSLL-G3/8-12	10
<b>Silencer</b>					
	With connecting thread G, metal design	G3/8	★ 6843	U-3/8-B	1
	With connecting thread G, sinter design, long	G3/8	★ 1205862	AMTE-M-LH-G38	10

1) Packaging unit quantity

## Solenoid valves VUVS-LT, size 30

Accessories

**FESTO**

Ordering data		Description	Weight [g]	Part no.	Type
<b>Foot mounting</b>					
	With screw set for attaching the valve to the foot mounting	239		<b>8026337</b>	<b>VAME-B10-30-A</b>
<b>Wall mounting</b>					
	With screw set for mounting the valve on the wall mounting	53		<b>576413</b>	<b>VAME-B10-20-W</b>
<b>Set of spare parts</b>					
	Set comprising seals and screws	22		<b>8035637</b>	<b>VAME-B10-30-MK</b>
<b>Inscription label</b>					
	40 pieces in frame	–		<b>565306</b>	<b>ASLR-C-E4</b>

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 20


**FESTO**

Data sheet –

-  - Flow rate  
Up to 700 l/min

-  - Valve width  
21 mm

-  - Voltage  
12, 24 V DC  
24, 110, 120, 230, 240 V AC



## General technical data

Valve function	3/2-way valve		5/2-way valve		5/3-way valve		
Order code for valves	M32C	M32U	M52	B52	P53C	P53U	P53E
Valve width [mm]	21						
Nominal width [mm]	5.7			5	4.8	4.5	
Design	Piston spool						
Flow direction	Reversible with external pilot air supply						
Pilot air supply	Internal or external						
Type of control	Piloted						
Manual override	Non-detenting, detenting						
Overlap	Positive overlap						
Sealing principle	Soft						
Type of mounting	Optionally via through-hole or on manifold rail						
Standard nominal flow rate qnN [l/min]	700	700	700	700	600		
Type of actuation	Electrical						
Mounting position	Optional						
Exhaust function	With flow control						
Pneumatic port 1, 2, 3	G1/8	G1/8	G1/8	G1/8	G1/8	G1/8	G1/8
4, 5	–	–	G1/8	G1/8	G1/8	G1/8	G1/8
Pilot air port 12/14	M5						
Pilot exhaust air port 82/84	M5						

## ATEX

Type	VUVS-L...-EX2
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T4 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T115°C X Dc
Explosion-proof ambient temperature rating [°C]	10°C <= Ta <= +60°C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

# Solenoid valves VUVS-L, size 20

Data sheet

**FESTO**

## Technical data – 3/2-way valves

Order code for valves	M32C		M32U	
Normal position	Closed		Open	
Stable position	Monostable		Monostable	
Reset method	Pneumatic spring	Mechanical spring	Pneumatic spring	Mechanical spring
Switching times in [ms]	On	14	14	14
	Off	21	32	21
	Change-over	–	–	–
Product weight excluding solenoid coil [g]	138	136	138	136
Product weight including solenoid coil [g]	172	170	172	170
Product weight including solenoid coil and plug socket [g]	182	180	182	180

## Technical data – 5/2-way valves

Order code for valves	M52		B52
Normal position	–		–
Stable position	Monostable		Bistable
Reset method	Pneumatic spring	Mechanical spring	–
Switching times in [ms]	On	20	12
	Off	29	44
	Change-over	–	10
Product weight excluding solenoid coil [g]	188	183	225
Product weight including solenoid coil [g]	222	217	259
Product weight including solenoid coil and plug socket [g]	232	227	279

## Technical data – 5/3-way valves

Order code for valves	P53C	P53U	P53E
Normal position/mid-position	Closed	Pressurised	Exhausted
Stable position	Monostable		
Reset method	Mechanical spring		
Switching times in [ms]	On	13	13
	Off	42	44
	Change-over	24	21
Product weight excluding solenoid coil [g]	229	229	229
Product weight including solenoid coil [g]	263	263	263
Product weight including solenoid coil and plug socket [g]	283	283	283

# Solenoid valves VUVS-L, size 20

**FESTO**

Data sheet

<b>Safety data</b>	
Max. positive test pulse 0 signal	[μs] 1900 (valves with VACS-C-C1-1)
Max. negative test pulse 1 signal	[μs] 2700 (valves with VACS-C-C1-1)
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

<b>Operating and environmental conditions</b>				
Order code for valves	M32	M52	B52	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure with internal pilot air supply [bar]	2.5 ... 10		1.5 ... 10	2.5 ... 10
Operating pressure with external pilot air supply [bar]	-0.9 ... +10			
Pilot pressure [bar]	2.5 ... 10		1.5 ... 10	2.5 ... 10
Ambient temperature [°C]	-10 ... +60			
Temperature of medium [°C]	-10 ... +60			
Approval	c UL us - Recognized (OL)			
Corrosion resistance class CRC <sup>1)</sup>	2			

- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

<b>Electrical</b>		
	With solenoid coil	Without solenoid coil
Electrical connection	Plug type C	Via solenoid coil
Operating voltage [V DC]	12, und 24 ±10%	→ Internet: vacs
[V AC]	24, 110, 120, 230, 240 ±10%	
Permissible voltage fluctuations [%]	±10	
Power [W]	2.6	
Duty cycle [%]	100	
Degree of protection to EN 60529	IP65 with plug socket	

<b>Materials</b>	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Piston spool	Wrought aluminium alloy (P53 types: high-alloy stainless steel)
Screws	Galvanised steel
Note on materials	RoHS-compliant


# Solenoid valves VUVS-L, size 20

Data sheet

FESTO


## Dimensions

3/2-way valves, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

3/2-way valves, without solenoid coil



[1] Solenoid coil interface

type C

[2] Location for inscription label

[4] Port 10/12 for pilot air supply

[6] Port 82 for pilot exhaust air

[7] For screw M3

Type	B1	B2	B3	B4	B5	D1	D3	D4	D5 Ø	H1	H2	H3	H4	H5
VUVS-L20-M32...-D-G18...	21.1	16.1	-	2.5	2	G1/8	-	M5	8	40	20.9	6.2	46.7	36.4
VUVS-L20-M32...-ZD-G18...			2.6				M5							

Type	L2	L4	L6	L7	L8	L9	L11	L12	L13	L14	L15	L16	L17	L19
VUVS-L20-M32...-D-G18...	110.7	109.1	80.1	47.3	19.2	30.6	29	-	60.9	56.9	36.9	8	45.6	52.9
VUVS-L20-M32...-ZD-G18...								19.5						


# Solenoid valves VUVS-L, size 20

FESTO

Data sheet

## Dimensions

5/2-way single solenoid valves, with solenoid coil




[1] Solenoid coil interface  
type C

[2] Location for inscription label

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply

5/2-way single solenoid valves, without solenoid coil



[5] Port 84 for pilot exhaust air

[7] For screw M3

Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5 Ø	H1	H2	H3	H4	H5
VUVS-L20-M52-...D-G18-...	21.1	16.1	—	2.5	2	G1/8	—	—	M5	8	40.4	20.9	6.2	46.7	36.4
VUVS-L20-M52-...ZD-G18-...			2.6				M5	M5							

Type	L2	L4	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-L20-M52-...D-G18-...	141.2	139.6	110.6	47.3	19.2	30.6	—	29	—	76.9	56.9	36.9	8	45.6	22.5	52.9
VUVS-L20-M52-...ZD-G18-...							94.3		19.5							


# Solenoid valves VUVS-L, size 20

Data sheet

FESTO


## Dimensions

5/3-way valves and 5/2-way valves, double solenoid, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

5/3-way valves and 5/2-way valves, double solenoid, without solenoid coil



**[1]** Solenoid coil interface  
type C

**[2]** Location for inscription label

**[3]** Port 14 for pilot air supply  
**[4]** Port 12 for pilot air supply

**[5]** Port 84 for pilot exhaust air  
**[6]** Port 82 for pilot exhaust air

**[7]** For screw M3

Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5 Ø	H1	H2	H3	H4	H5
VUVS-L20-P53...-MD-G18...	21.1	16.1	—	2.5	2	G1/8	—	—	M5	8	40.4	20.9	6.2	46.7	36.4
VUVS-L20-P53...-MZD-G18...			2.6				M5	M5							
VUVS-L20-B52-D-G18...			—				—	—							
VUVS-L20-B52-ZD-G18...			2.6				M5	M5							

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11
VUVS-L20-P53...-MD-G18...	174.9	144.3	171.7	142.7	139.1	113.7	47.3	19.2	30.6	—	29
VUVS-L20-P53...-MZD-G18...										94.3	
VUVS-L20-B52-D-G18...										—	
VUVS-L20-B52-ZD-G18...										94.3	

Type	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-L20-P53...-MD-G18...	—	76.9	56.9	36.9	8	45.6	22.5	52.9
VUVS-L20-P53...-MZD-G18...	19.5							
VUVS-L20-B52-D-G18...	—							
VUVS-L20-B52-ZD-G18...	19.5							

# Solenoid valves VUVS-L, size 20


FESTO

Accessories

## Dimensions

Foot mounting

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1 ∅	D2 ∅	D3	H1	H2	H3	H4
VAME-B10-20-A	VUVS-L20-B52/P53	20	13.1	10.6	3.2	4.2	5.2	112.5	106.5	77.5
	VUVS-L20-M52									
	VUVS-L20-M32									

Type	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14
VAME-B10-20-A	44	39	19.2	10.5	2.5	184.4	-	184.4	184.4	184.4

Type	H15	L1	L2	L3	L4	L5	L6	L7	L8	L9
VAME-B10-20-A	97.7	55	41	29.4	19.2	40	20	19	174.9	4.1


# Solenoid valves VUVS-L, size 20

Data sheet

**FESTO**

## Dimensions

Wall mounting



Type		B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-L20-B52/P53	10	M3	M4	M5	35	20	10	11.5	9.7	8.7
	VUVS-L20-M52										
	VUVS-L20-M32										

Type		H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	VUVS-L20-B52/P53	22.7	17.7	50	40	20	87.5	87.5	56.9	56.9
	VUVS-L20-M52							53.7		-
	VUVS-L20-M32							23.3		





# Solenoid valves VUVS-L, size 20

**FESTO**

Accessories

## ★ Core product range

### Ordering data

	Code	Valve function	Part no.	Type
3/2-way valve with solenoid coil (24 V DC)				
		Monostable, normally closed, type C		
M32C-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible		★ 575269	VUVS-L20-M32C-AD-G18-F7-1C1
M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible		★ 575274	VUVS-L20-M32C-MD-G18-F7-1C1
5/2-way valve with solenoid coil (24 V DC)				
		Single solenoid, type C		
M52-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible		★ 575263	VUVS-L20-M52-AD-G18-F7-1C1
M52-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible		★ 575264	VUVS-L20-M52-MD-G18-F7-1C1
		Bistable, type C		
B52	Internal pilot air supply, direction of flow not reversible		★ 575265	VUVS-L20-B52-D-G18-F7-1C1
5/3-way valve with solenoid coil (24 V DC)				
		Mid-position closed, type C		
P53C	Mechanical spring return, internal pilot air supply, direction of flow not reversible		★ 575268	VUVS-L20-P53C-MD-G18-F7-1C1

Festo core product range



★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 20

Accessories





**FESTO**

Ordering data		Code	Valve function	Part no.	Type
3/2-way valve without solenoid coil					
	Monostable, normally closed	M32C-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575255	VUVS-L20-M32C-AD-G18-F7
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575257	VUVS-L20-M32C-AZD-G18-F7
	M32C-M		Mechanical spring return, internal pilot air supply, direction of flow not reversible	575260	VUVS-L20-M32C-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow reversible	575259	VUVS-L20-M32C-MZD-G18-F7
Monostable, normally open					
	M32U-A		Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575256	VUVS-L20-M32U-AD-G18-F7
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575258	VUVS-L20-M32U-AZD-G18-F7
	M32U-M		Mechanical spring return, internal pilot air supply, direction of flow not reversible	575262	VUVS-L20-M32U-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow reversible	575261	VUVS-L20-M32U-MZD-G18-F7
3/2-way valve with solenoid coil (24 V DC)					
	Monostable, normally closed, type C	M32C-A	Pneumatic spring return, external pilot air supply, direction of flow reversible	575271	VUVS-L20-M32C-AZD-G18-F7-1C1
	M32C-M		Mechanical spring return, external pilot air supply, direction of flow reversible	575273	VUVS-L20-M32C-MZD-G18-F7-1C1
Monostable, normally open, type C					
	M32U-A		Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575270	VUVS-L20-M32U-AD-G18-F7-1C1
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575272	VUVS-L20-M32U-AZD-G18-F7-1C1
	M32U-M		Mechanical spring return, internal pilot air supply, direction of flow not reversible	575276	VUVS-L20-M32U-MD-G18-F7-1C1
			Mechanical spring return, external pilot air supply, direction of flow reversible	575275	VUVS-L20-M32U-MZD-G18-F7-1C1

# Solenoid valves VUVS-L, size 20

**FESTO**



Accessories

Ordering data		Code	Valve function	Part no.	Type
<b>5/2-way valve without solenoid coil</b>					
	Monostable	M52-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575249	VUVS-L20-M52-AD-G18-F7
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575675	VUVS-L20-M52-AZD-G18-F7
		M52-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575250	VUVS-L20-M52-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow reversible	575679	VUVS-L20-M52-MZD-G18-F7
	Bistable	B52	Internal pilot air supply, direction of flow not reversible	575251	VUVS-L20-B52-D-G18-F7
			External pilot air supply, direction of flow reversible	575682	VUVS-L20-B52-ZD-G18-F7
<b>5/2-way valve with solenoid coil (24 V DC)</b>					
	Single solenoid, type C	M52-A	Pneumatic spring return, external pilot air supply, direction of flow reversible	575676	VUVS-L20-M52-AZD-G18-F7-1C1
		M52-M	Mechanical spring return, external pilot air supply, direction of flow reversible	575680	VUVS-L20-M52-MZD-G18-F7-1C1
	Bistable, type C	B52	External pilot air supply, direction of flow reversible	575683	VUVS-L20-B52-ZD-G18-F7-1C1

# Solenoid valves VUVS-L, size 20

Accessories

**FESTO**

Ordering data		Code	Valve function	Part no.	Type
5/3-way valve without solenoid coil					
	Mid-position closed	P53C	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575254	VUVS-L20-P53C-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow reversible	575685	VUVS-L20-P53C-MZD-G18-F7
	Mid-position exhausted	P53E	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575252	VUVS-L20-P53E-MD-G18-F7
			Mechanical spring return, external pilot air supply, direction of flow reversible	575691	VUVS-L20-P53E-MZD-G18-F7
Mid-position pressurised					
	P53U	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575253	VUVS-L20-P53U-MD-G18-F7	
			Mechanical spring return, external pilot air supply, direction of flow reversible	575688	VUVS-L20-P53U-MZD-G18-F7
5/3-way valve with solenoid coil (24 V DC)					
Mid-position closed, type C	P53C	Mechanical spring return, external pilot air supply, direction of flow reversible	575686	VUVS-L20-P53C-MZD-G18-F7-1C1	
Mid-position exhausted, type C					
P53E	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575266	VUVS-L20-P53E-MD-G18-F7-1C1		
		Mechanical spring return, external pilot air supply, direction of flow reversible	575692	VUVS-L20-P53E-MZD-G18-F7-1C1	
Mid-position pressurised, type C					
	P53U	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575267	VUVS-L20-P53U-MD-G18-F7-1C1	
			Mechanical spring return, external pilot air supply, direction of flow reversible	575689	VUVS-L20-P53U-MZD-G18-F7-1C1

# Solenoid valves VUVS-L, size 20

**FESTO**

Accessories

Ordering data		Description	Part no.	Type
<b>Solenoid coils for valves</b>				
	Plug pattern type C, to DIN EN 175301-803	12 V DC	<b>8025331</b>	VACS-C-C1-5
		24 V DC	<b>8025330</b>	VACS-C-C1-1
		48 V DC	<b>8025336</b>	VACS-C-C1-7
		24 V AC/50-60 Hz	<b>8025335</b>	VACS-C-C1-1A
		48 V AC/50-60 Hz	<b>8025337</b>	VACS-C-C1-7A
		110/120 V AC/50-60 Hz	<b>8025334</b>	VACS-C-C1-16B
		230/240 V AC/50-60 Hz	<b>8025338</b>	VACS-C-C1-3W
<b>Seal set</b>				
	For valves in order to guarantee protection class IP67		<b>2643771</b>	VAMC-B10-C-B-S8
<b>Cover cap</b>				
	For manual override, non-detenting or covered		<b>8028240</b>	VAMC-B10-20-CH2
<b>Plug socket</b>				
	Connection pattern type C, to DIN EN 175301-803			
	3-pin, screw terminal	Cable fitting M12 Kabelverschraubung Pg7	0 ... 250 V AC/DC IP65	<b>539712</b> MSSD-EB-M12 <b>★ 151687</b> MSSD-EB
	4-pin, insulation displacement connector	Kabelverschraubung M14	0 ... 250 V AC/DC IP67	<b>192745</b> MSSD-EB-S-M14
	3-pin, socket angled	Cable fitting M12	0 ... 24 V DC IP65	<b>570367</b> MSSD-EB-M12-24VDC-SD-EX
<b>Adapters</b>				
	Socket, type C, to EN 175301-803	Plug connector M12x1, 2-pin, A-coded	12 ... 24 V AC/DC IP65	<b>188024</b> MSSD-EB-M12-MONO
<b>Plug socket with cable</b>				
	Connection pattern type C, to DIN EN 175301-803			
	Angled socket, 3-pin Cable, open end, 3-wire	24 V DC	LED 2,5 m	<b>★ 151688</b> KMEB-1-24-2,5-LED
			5 m	<b>151689</b> KMEB-1-24-5-LED
			10 m	<b>193457</b> KMEB-1-24-10-LED
		230 V AC	- 2,5 m	<b>151690</b> KMEB-1-230AC-2,5
				<b>151691</b> KMEB-1-230AC-5
<b>Illuminating seal</b>				
	Connection pattern type C, to DIN EN 175301-803	24 V DC	<b>151717</b>	MEB-LD-12-24DC
		230 V AC	<b>151718</b>	MEB-LD-230AC

Festo core product range

**★** Generally ready for shipping ex works in 24 hours

**★** Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 20

Accessories

**FESTO**

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Push-in fitting with internal hex</b>					
	Connecting thread M5 for tubing O.D.	4 mm	<b>★ 153315</b>	QSM-M5-4-I	<b>10</b>
	Connecting thread G1/8 for tubing O.D.	4 mm	<b>★ 186106</b>	QS-G1/8-4-I	<b>10</b>
			<b>133008</b>	QS-G1/8-4-I-100	<b>100</b>
		6 mm	<b>★ 186107</b>	QS-G1/8-6-I	<b>10</b>
			<b>133009</b>	QS-G1/8-6-I-100	<b>100</b>
		8 mm	<b>★ 186109</b>	QS-G1/8-8-I	<b>10</b>
			<b>133010</b>	QS-G1/8-8-I-100	<b>100</b>
<b>Angled push-in fitting with external hex</b>					
	Connecting thread G1/8 for tubing O.D.	4 mm	<b>★ 186116</b>	QSL-G1/8-4	<b>10</b>
			<b>132048</b>	QSL-G1/8-4-100	<b>100</b>
		6 mm	<b>★ 186117</b>	QSL-G1/8-6	<b>10</b>
			<b>132049</b>	QSL-G1/8-6-100	<b>100</b>
		8 mm	<b>★ 186119</b>	QSL-G1/8-8	<b>10</b>
			<b>132050</b>	QSL-G1/8-8-50	<b>50</b>
<b>Angled push-in fitting, long, with external hex</b>					
	Connecting thread G1/8 for tubing O.D.	4 mm	<b>186127</b>	QSLL-G1/8-4	<b>10</b>
			<b>133015</b>	QSLL-G1/8-4-100	<b>100</b>
		6 mm	<b>186128</b>	QSLL-G1/8-6	<b>10</b>
			<b>133016</b>	QSLL-G1/8-6-100	<b>100</b>
		8 mm	<b>186130</b>	QSLL-G1/8-8	<b>10</b>
			<b>133017</b>	QSLL-G1/8-8-100	<b>100</b>
<b>Silencer</b>					
	With connecting thread G, polymer design	G1/8	<b>★ 2307</b>	U-1/8	<b>1</b>
			<b>534222</b>	U-1/8-50	<b>50</b>
	With connecting thread G, metal design	G1/8	<b>★ 6841</b>	U-1/8-B	<b>1</b>
	With connecting thread G, sinter design, long	G1/8	<b>★ 1205860</b>	AMTE-M-LH-G18	<b>20</b>

1) Packaging unit quantity

Festo core product range


**★** Generally ready for shipping ex works in 24 hours

**☆** Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 20

FESTO

Accessories

Ordering data		Description	Weight [g]	Part no.	Type
<b>Foot mounting</b>					
	With screw set for attaching the valve to the foot mounting	97		<b>576412</b>	<b>VAME-B10-20-A</b>
<b>Wall mounting</b>					
	With screw set for mounting the valve on the wall mounting	53		<b>576413</b>	<b>VAME-B10-20-W</b>
<b>Set of spare parts</b>					
	Set comprising seals and screws	10		<b>8026203</b>	<b>VAME-B10-20-MK</b>
<b>Inscription label</b>					
	40 pieces in frame	-		<b>565306</b>	<b>ASLR-C-E4</b>

# Solenoid valves VUVS-L, size 25


Data sheet

FESTO

-  Flow rate  
Up to 1300 l/min

-  Valve width  
26.5 mm

-  Voltage  
12, 24 V DC  
24, 110, 120, 230, 240 V AC



## General technical data

Valve function	3/2-way valve		5/2-way valve		5/3-way valve		
Order code for valves	M32C	M32U	M52	B52	P53C	P53U	P53E
Valve width [mm]	26.5						
Nominal width [mm]	6.3		6.9		6.5		6.3
Design	Piston spool						
Flow direction	Reversible with external pilot air supply						
Pilot air supply	Internal or external						
Type of control	Piloted						
Manual override	Non-detenting, detenting						
Overlap	Positive overlap						
Sealing principle	Soft						
Type of mounting	Optionally via through-hole or on manifold rail						
Standard nominal flow rate qN [l/min]	1000	1300	1300	1200	1000		
Type of actuation	Electrical						
Mounting position	Optional						
Exhaust function	With flow control						
Pneumatic port 1, 2, 3	G1/4	G1/4	G1/4	G1/4	G1/4	G1/4	G1/4
4, 5	-	-	G1/4	G1/4	G1/4	G1/4	G1/4
Pilot air port 12/14	M5						
Pilot exhaust air port 82/84	M5						

## ATEX

Type	VUVS-L...-EX2
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T4 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T115°C X Dc
Explosion-proof ambient temperature rating	10°C <= Ta <= +60°C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

# Solenoid valves VUVS-L, size 25

**FESTO**

Data sheet

Technical data – 3/2-way valves				
Order code for valves	M32C	M32U		
Normal position	Closed	Open		
Stable position	Monostable	Monostable		
Reset method	Pneumatic spring	Mechanical spring	Pneumatic spring	Mechanical spring
Switching times in [ms]	On	13	11	12
	Off	26	40	26
	Change-over	–	–	–
Product weight excluding solenoid coil [g]	244	244	244	244
Product weight including solenoid coil [g]	297	297	297	297

Technical data – 5/2-way valves				
Order code for valves	M52	B52		
Normal position	–	–		
Stable position	Monostable	Bistable		
Reset method	Pneumatic spring	Mechanical spring		
Switching times in [ms]	On	19	12	–
	Off	35	47	–
	Change-over	–	–	11
Product weight excluding solenoid coil [g]	311	311	322	
Product weight including solenoid coil [g]	363	363	428	

Technical data – 5/3-way valves				
Order code for valves	P53C	P53U	P53E	
Normal position/mid-position	Closed	Pressurised	Exhausted	
Stable position	Monostable			
Reset method	Mechanical spring			
Switching times in [ms]	On	13	14	14
	Off	42	48	48
	Change-over	26	25	25
Product weight excluding solenoid coil [g]	324	324	324	
Product weight including solenoid coil [g]	430	430	430	

Safety data				
Max. positive test pulse 0 signal [μs]	2000 (valves with VACF-B-....-1)			
Max. negative test pulse 1 signal [μs]	3600 (valves with VACF-B-....-1)			
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27			
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6			

# Solenoid valves VUVS-L, size 25

Data sheet

**FESTO**

Operating and environmental conditions				
Order code for valves	M32	M52	B52	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure with internal pilot air supply [bar]	2.5 ... 10		1.5 ... 10	2.5 ... 10
Operating pressure with external pilot air supply [bar]	-0.9 ... +10			
Pilot pressure [bar]	2.5 ... 10		1.5 ... 10	2.5 ... 10
Ambient temperature [°C]	-10 ... +60			
Temperature of medium [°C]	-10 ... +60			
Approval	c UL us - Recognized (OL)			
Maritime classification <sup>1)</sup>	See certificate (only for VUVS-...-F8 and VUVS-...-F8-...-B2)			
Corrosion resistance class CRC <sup>2)</sup>	2			

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) ➔ Certificates.

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Electrical		
	With solenoid coil	Without solenoid coil
Electrical connection	Plug connector type C, plug connector type B	Via solenoid coil ➔ Internet: vacf
Operating voltage [V DC]	12, und 24 ±10%	
	[V AC]	24, 110, 120, 230, 240 ±10%
Permissible voltage fluctuations [%]	10	
Power (24V DV) [W]	3.3	
Duty cycle [%]	100	
Degree of protection to EN 60529	IP65 with plug socket	

Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Piston spool	Wrought aluminium alloy
Screws in	Galvanised steel
Note on materials	RoHS-compliant


# Solenoid valves VUVS-L, size 25

FESTO

Data sheet

## Dimensions

3/2-way valves, with solenoid coil



[1] Solenoid coil interface  
type B/type C

[4] Port 10/12 for pilot air supply


[6] Port 82 for pilot exhaust air

[7] For screw M4

[2] Location for inscription label

Download CAD data ➔ [www.festo.com](http://www.festo.com)

3/2-way valves, without solenoid coil



Type	B1	B2	B3	B4	B5	B6	D1	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-L25-M32...-...D-G14-...	26.5	20.2	-	1.9	1.9	22	G1/4	-	M5	8	50.5	28.2	8	57.2	45.2
VUVS-L25-M32...-...ZD-G14-...				4.5				M5							

Type	L2	L4	L5	L6	L7	L8	L9	L11	L12	L14	L15	L16	L17	L19
VUVS-L25-M32...-...D-G14-...	129.2	128.1	123.8	94.8	53.3	25	34.4	33.3	-	65.8	41.3	13	50.4	59.3
VUVS-L25-M32...-...ZD-G14-...									20.3					


# Solenoid valves VUVS-L, size 25

Data sheet

FESTO


## Dimensions

5/2-way single solenoid valves, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way single solenoid valves, without solenoid coil



[1] Solenoid coil interface  
type B/type C

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply

[5] Port 84 for pilot exhaust air

[7] For screw M4

[2] Location for inscription label

Type	B1	B2	B3	B4	B5	B6	D1	D2	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-L25-M52-...D-G14-...	26.5	20.2	—	1.9	1.9	22	G1/4	—	—	M5	8	50.5	28.2	8	57.2	45.2
VUVS-L25-M52-...ZD-G14-...			4.5					M5	M5							

Type	L2	L4	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-L25-M52-...D-G14-...	162.2	161.1	156.8	127.8	53.3	25	34.4	—	33.3	—	90.3	65.8	41.3	13	50.4	30.8	59.3
VUVS-L25-M52-...ZD-G14-...								111.3		20.3							




# Solenoid valves VUVS-L, size 25

FESTO

Data sheet

## Dimensions

5/3-way valves and 5/2-way valves, double solenoid, with solenoid coil




[1] Solenoid coil interface  
type B/type C

[2] Location for inscription label

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply

Download CAD data → [www.festo.com](http://www.festo.com)

5/3-way valves and 5/2-way valves, double solenoid, without solenoid coil



Type	B1	B2	B3	B4	B5	B6	D1	D2	D3	D4	D5	H1
VUVS-L25-P53...-MD-G14-...	26.5	20.2	–	1.9	1.9	22	G1/4	–	–	M5	8	50.5
VUVS-L25-P53...-MZD-G14-...			4.5							M5	M5	
VUVS-L25-B52-D-G14-...			–							–	–	
VUVS-L25-B52-ZD-G14-...			4.5							M5	M5	

Type	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6	L7	L8
VUVS-L25-P53...-MD-G14-...	28.2	8	57.2	45.2	200.3	166	198.2	164.9	160.6	131.6	53.3	25
VUVS-L25-P53...-MZD-G14-...												
VUVS-L25-B52-D-G14-...												
VUVS-L25-B52-ZD-G14-...												

Type	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-L25-P53...-MD-G14-...	33.3	–	33.3	–	90.3	65.8	41.3	13	50.4	30.8	59.3
VUVS-L25-P53...-MZD-G14-...		111.3		20.3							
VUVS-L25-B52-D-G14-...		–		–							
VUVS-L25-B52-ZD-G14-...		111.3		20.3							

# Solenoid valves VUVS-L, size 25


Accessories

**FESTO**

## Dimensions

Foot mounting

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1	D2	D3	H1	H2	H3	H4
VAME-B10-25-A	VUVS-L20-B52/P53	24	15.8	13.3	4.2	4.2	5.2	130	122.5	91
	VUVS-L20-M52									80.5
	VUVS-L20-M32									

Type	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14
VAME-B10-25-A	VUVS-L20-B52/P53	48.5	41.5	25	11	2.5	210.2	–	210.2	210.2
	VUVS-L20-M52							178.7	172	172
	VUVS-L20-M32								138.9	138.9

Type	H15	L1	L2	L3	L4	L5	L6	L7	L8	L9
VAME-B10-25-A	VUVS-L20-B52/P53	123	55	49.4	40.4	25	40	20	23.5	200.3
	VUVS-L20-M52									162.2
	VUVS-L20-M32									129


# Solenoid valves VUVS-L, size 25

FESTO

Accessories

## Dimensions

Wall mounting



[1] Mounting hole for size 20

[2] Mounting hole size 25

[3] Mounting hole for size 30

Type	B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-L25-B52/P53	10	M3	M4	M5	35	20	10	11.5	9.7
	VUVS-L25-M52									8.7
	VUVS-L25-M32									





Type	H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	VUVS-L25-B52/P53	32.8	17.7	50	40	20	100.2	100.2	65.8
	VUVS-L25-M52							62	65.8
	VUVS-L25-M32							28.9	-

# Solenoid valves VUVS-L, size 25

Accessories

**FESTO**

## ★ Core product range

Ordering data		Code	Valve function	Part no.	Type	
3/2-way valve with solenoid coil (24 V DC)						
	Monostable, normally closed, type C					
	M32C-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	★ 575475	VUVS-L25-M32C-AD-G14-F8-1C1		
	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	★ 575477	VUVS-L25-M32C-MD-G14-F8-1C1		
5/2-way valve with solenoid coil (24 V DC)						
	Single solenoid, type C					
	M52-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	★ 575503	VUVS-L25-M52-AD-G14-F8-1C1		
	M52-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	★ 575511	VUVS-L25-M52-MD-G14-F8-1C1		
	Bistable, type C					
	B52	Internal pilot air supply, direction of flow not reversible	★ 575518	VUVS-L25-B52-D-G14-F8-1C1		
5/3-way valve with solenoid coil (24 V DC)						
	Mid-position closed, type C					
	P53C	Mechanical spring return, internal pilot air supply, direction of flow not reversible	★ 575525	VUVS-L25-P53C-MD-G14-F8-1C1		




Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 25

**FESTO**


Accessories

Ordering data		Code	Valve function	Part no.	Type	
3/2-way valve without solenoid coil						
	M32C-A	Monostable, normally closed Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575471	VUVS-L25-M32C-AD-G14-F8		
		Pneumatic spring return, external pilot air supply, direction of flow reversible	575472	VUVS-L25-M32C-AZD-G14-F8		
	M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575473	VUVS-L25-M32C-MD-G14-F8		
		Mechanical spring return, external pilot air supply, direction of flow reversible	575474	VUVS-L25-M32C-MZD-G14-F8		
	Monostable, normally open					
		M32U-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575486	VUVS-L25-M32U-AD-G14-F8	
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575487	VUVS-L25-M32U-AZD-G14-F8	
		M32U-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575488	VUVS-L25-M32U-MD-G14-F8	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575489	VUVS-L25-M32U-MZD-G14-F8		
3/2-way valve with solenoid coil (24 V DC)						
	M32C-A	Monostable, normally closed, type C Pneumatic spring return, external pilot air supply, direction of flow reversible	575476	VUVS-L25-M32C-AZD-G14-F8-1C1		
	M32C-M	Mechanical spring return, external pilot air supply, direction of flow reversible	575478	VUVS-L25-M32C-MZD-G14-F8-1C1		
	Single solenoid, normally closed, type B					
		M32C-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575479	VUVS-L25-M32C-AD-G14-F8-1B2	
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575480	VUVS-L25-M32C-AZD-G14-F8-1B2	
		M32C-M	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575481	VUVS-L25-M32C-MD-G14-F8-1B2	
			Mechanical spring return, external pilot air supply, direction of flow reversible	575482	VUVS-L25-M32C-MZD-G14-F8-1B2	

# Solenoid valves VUVS-L, size 25

Accessories




**FESTO**

Ordering data		Code	Valve function	Part no.	Type	
3/2-way valve with solenoid coil (24 V DC)						
			Monostable, normally open, type C			
	M32U-A		Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575490	VUVS-L25-M32U-AD-G14-F8-1C1	
	M32U-A		Pneumatic spring return, external pilot air supply, direction of flow reversible	575491	VUVS-L25-M32U-AZD-G14-F8-1C1	
	M32U-M		Mechanical spring return, internal pilot air supply, direction of flow not reversible	575492	VUVS-L25-M32U-MD-G14-F8-1C1	
	M32U-M		Mechanical spring return, external pilot air supply, direction of flow reversible	575493	VUVS-L25-M32U-MZD-G14-F8-1C1	
	Monostable, normally open, type B					
	M32U-A		Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575494	VUVS-L25-M32U-AD-G14-F8-1B2	
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575495	VUVS-L25-M32U-AZD-G14-F8-1B2	
M32U-M		Mechanical spring return, internal pilot air supply, direction of flow not reversible	575496	VUVS-L25-M32U-MD-G14-F8-1B2		
		Mechanical spring return, external pilot air supply, direction of flow reversible	575497	VUVS-L25-M32U-MZD-G14-F8-1B2		

# Solenoid valves VUVS-L, size 25

**FESTO**



Accessories

Ordering data		Code	Valve function	Part no.	Type
5/2-way valve without solenoid coil					
	Monostable	M52-A	Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575501	VUVS-L25-M52-AD-G14-F8
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575502	VUVS-L25-M52-AZD-G14-F8
	M52-M		Mechanical spring return, internal pilot air supply, direction of flow not reversible	575509	VUVS-L25-M52-MD-G14-F8
			Mechanical spring return, external pilot air supply, direction of flow reversible	575510	VUVS-L25-M52-MZD-G14-F8
	Bistable				
		B52	Internal pilot air supply, direction of flow not reversible	575516	VUVS-L25-B52-D-G14-F8
			External pilot air supply, direction of flow reversible	575517	VUVS-L25-B52-ZD-G14-F8
5/2-way valve with solenoid coil (24 V DC)					
	Single solenoid, type C				
	M52-A		Pneumatic spring return, external pilot air supply, direction of flow reversible	575504	VUVS-L25-M52-AZD-G14-F8-1C1
			Mechanical spring return, external pilot air supply, direction of flow reversible	575512	VUVS-L25-M52-MZD-G14-F8-1C1
	Single solenoid, type B				
	M52-A		Pneumatic spring return, internal pilot air supply, direction of flow not reversible	575505	VUVS-L25-M52-AD-G14-F8-1B2
			Pneumatic spring return, external pilot air supply, direction of flow reversible	575506	VUVS-L25-M52-AZD-G14-F8-1B2
	M52-M		Mechanical spring return, internal pilot air supply, direction of flow not reversible	575513	VUVS-L25-M52-MD-G14-F8-1B2
			Mechanical spring return, external pilot air supply, direction of flow reversible	575514	VUVS-L25-M52-MZD-G14-F8-1B2

# Solenoid valves VUVS-L, size 25

Accessories


**FESTO**

Ordering data		Code	Valve function	Part no.	Type	
5/2-way valve with solenoid coil (24 V DC)						
	Double solenoid, type C	B52	external pilot air supply, direction of flow reversible	575519	VUVS-L25-B52-ZD-G14-F8-1C1	
	Double solenoid, type B	B52	Internal pilot air supply, direction of flow not reversible	575520	VUVS-L25-B52-D-G14-F8-1B2	
			external pilot air supply, direction of flow reversible	575521	VUVS-L25-B52-ZD-G14-F8-1B2	
5/3-way valve without solenoid coil						
	Mid-position closed	P53C	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575523	VUVS-L25-P53C-MD-G14-F8	
			Mechanical spring return, external pilot air supply, direction of flow reversible	575524	VUVS-L25-P53C-MZD-G14-F8	
	Mid-position exhausted	P53E	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575537	VUVS-L25-P53E-MD-G14-F8	
			Mechanical spring return, external pilot air supply, direction of flow reversible	575538	VUVS-L25-P53E-MZD-G14-F8	
	Mid-position pressurised	P53U	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575530	VUVS-L25-P53U-MD-G14-F8	
			Mechanical spring return, external pilot air supply, direction of flow reversible	575531	VUVS-L25-P53U-MZD-G14-F8	

# Solenoid valves VUVS-L, size 25

**FESTO**

Accessories

Ordering data		Code	Valve function	Part no.	Type
5/3-way valve with solenoid coil (24 V DC)					
		P53C	Mid-position closed, type C Mechanical spring return, external pilot air supply, direction of flow reversible	575526	VUVS-L25-P53C-MZD-G14-F8-1C1
Mid-position exhausted, type C					
	P53E	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575539	VUVS-L25-P53E-MD-G14-F8-1C1	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575540	VUVS-L25-P53E-MZD-G14-F8-1C1	
Mid-position pressurised, type C					
	P53U	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575532	VUVS-L25-P53U-MD-G14-F8-1C1	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575533	VUVS-L25-P53U-MZD-G14-F8-1C1	
Mid-position closed, type B					
	P53C	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575527	VUVS-L25-P53C-MD-G14-F8-1B2	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575528	VUVS-L25-P53C-MZD-G14-F8-1B2	
Mid-position exhausted, type B					
	P53E	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575541	VUVS-L25-P53E-MD-G14-F8-1B2	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575542	VUVS-L25-P53E-MZD-G14-F8-1B2	
Mid-position pressurised, type B					
	P53U	Mechanical spring return, internal pilot air supply, direction of flow not reversible	575534	VUVS-L25-P53U-MD-G14-F8-1B2	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575535	VUVS-L25-P53U-MZD-G14-F8-1B2	

# Solenoid valves VUVS-L, size 25

Accessories


**FESTO**

Ordering data		Description	Part no.	Type
Solenoid coils for valves				
	Connection pattern type C, to DIN EN 175301-803	12 V DC	<b>8030810</b>	VACF-B-C1-5
		24 V DC	<b>8030811</b>	VACF-B-C1-1
		48 V DC	<b>8030812</b>	VACF-B-C1-7
		24 V AC/50-60 Hz	<b>8030813</b>	VACF-B-C1-1A
		48 V AC/50-60 Hz	<b>8030814</b>	VACF-B-C1-7A
		110/120 V AC/50-60 Hz	<b>8030815</b>	VACF-B-C1-16B
		230/240 V AC/50-60 Hz	<b>8030817</b>	VACF-B-C1-3W
	Connection pattern type B, industry standard	12 V DC	<b>8030801</b>	VACF-B-B2-5
		24 V DC	<b>8030802</b>	VACF-B-B2-1
		48 V DC	<b>8030803</b>	VACF-B-B2-7
		24 V AC/50-60 Hz	<b>8030804</b>	VACF-B-B2-1A
		48 V AC/50-60 Hz	<b>8030805</b>	VACF-B-B2-7A
		110/120 V AC/50-60 Hz	<b>8030806</b>	VACF-B-B2-16B
		230/240 V AC/50-60 Hz	<b>8030808</b>	VACF-B-B2-3W
Seal-SET for solenoid coil				
	Connection pattern type C to guarantee protection class IP67		<b>2643771</b>	VAMC-B10-C-B-S8
	Connection pattern type B to guarantee protection class IP67		<b>8034609</b>	VAMC-B10-B-B-S8
Cover cap				
	For manual override, non-detenting or covered		<b>8028240</b>	VAMC-B10-20-CH2

# Solenoid valves VUVS-L, size 25

**FESTO**

Accessories

Ordering data		Description	Part no.	Type
<b>Plug socket</b>				
	Connection pattern type C, to DIN EN 175301-803			
	3-pin, screw terminal	Cable fitting M12	0 ... 250 V AC/DC	IP65
		Cable fitting Pg7		539712 MSSD-EB-M12
	4-pin, insulation displacement connector	Cable fitting M14	0 ... 250 V AC/DC	IP67
	Angled plug, 3-pin	Cable fitting M12	0 ... 24 V DC	IP65
				570367 MSSD-EB-M12-24VDC-SD-EX
	Connection pattern type B, industry standard			
	3-pin, screw terminal	Cable fitting M16	0 ... 250 V AC/DC	IP65
		Cable fitting Pg9		539710 MSSD-F-M16
	3-pin, insulation displacement connector	-	0 ... 250 V AC/DC	IP67
<b>Adapters</b>				
	Socket, type C, to EN 175301-803	Plug connector M12x1, 2-pin, A-coded	12 ... 24 V AC/DC	IP65
<b>Plug socket with cable</b>				
	Connection pattern type C, to DIN EN 175301-803			
	Angled socket, 3-pin		24 V DC	LED
	Cable, open end, 3-wire		5 m	★ 151688 KMEB-1-24-2,5-LED
			10 m	151689 KMEB-1-24-5-LED
			230 V AC	-
	2.5 m		2.5 m	193457 KMEB-1-24-10-LED
			5 m	151690 KMEB-1-230AC-2,5
				151691 KMEB-1-230AC-5
	Connection pattern type B, industry standard			
	Angled socket, 3-pin		24 V DC	LED
	Cable, open end, 3-wire		5 m	★ 30935 KMF-1-24DC-2,5-LED
			10 m	30937 KMF-1-24DC-5-LED
			230 V AC	-
	2.5 m		2.5 m	193458 KMF-1-24-10-LED
			5 m	30936 KMF-1-230AC-2,5
				30938 KMF-1-230AC-5
<b>Illuminating seal</b>				
	Connection pattern type C, to DIN EN 175301-803		24 V DC	151717 MEB-LD-12-24DC
			230 V AC	151718 MEB-LD-230AC
	Connection pattern type B, industry standard		24 V DC	19143 MF-LD-12-24DC
			230 V AC	19144 MF-LD-230AC

Festo core product range

★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 25

Accessories

**FESTO**

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
Push-in fitting with internal hex					
	Connecting thread M5 for tubing O.D. Ø	4 mm	★ 153315	QSM-M5-4-I	10
	Connecting thread G1/4 for tubing O.D.	6 mm	★ 186108	QS-G1/4-6-I	10
		8 mm	★ 186110	QS-G1/4-8-I	10
		10 mm	★ 186112	QS-G1/4-10-I	10
Angled push-in fitting with external hex					
	Connecting thread G1/4 for tubing O.D.	6 mm	★ 186118	QSL-G1/4-6	10
			132051	QSL-G1/4-6-100	100
		8 mm	★ 186120	QSL-G1/4-8	10
			132052	QSL-G1/4-8-50	50
		10 mm	★ 186122	QSL-G1/4-10	10
132053	QSL-G1/4-10-50		50		
Angled push-in fitting, long, with external hex					
	Connecting thread G1/4 for tubing O.D.	6 mm	186129	QSLL-G1/4-6	10
		8 mm	186131	QSLL-G1/4-8	10
		10 mm	186133	QSLL-G1/4-10	10
Silencer					
	With connecting thread G, polymer design	G1/4	★ 2316	U-1/4	1
			534223	U-1/4-20	20
	With connecting thread G, metal design	G1/4	★ 6842	U-1/4-B	1
	With connecting thread G, sinter design, long	G1/4	★ 1205861	AMTE-M-LH-G14	20

1) Packaging unit quantity


Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 25

FESTO

Accessories

Ordering data		Description	Weight [g]	Part no.	Type
<b>Foot mounting</b>					
	With screw set for attaching the valve to the foot mounting	130		2293485	VAME-B10-25-A
<b>Wall mounting</b>					
	With screw set for mounting the valve on the wall mounting	53		576413	VAME-B10-20-W
<b>Set of spare parts</b>					
	Set comprising seals and screws	12		8035636	VAME-B10-25-MK
<b>Inscription label</b>					
	40 pieces in frame	-		565306	ASLR-C-E4

# Solenoid valves VUVS-L, size 30


Data sheet

**FESTO**

-  - Flow rate  
Up to 2300 l/min

-  - Valve width  
31 mm

-  - Voltage  
12, 24 V DC  
24, 110, 120, 230, 240 V AC



General technical data							
Valve function	3/2-way valve		5/2-way valve		5/3-way valve		
Order code for valves	M32C	M32U	M52	B52	P53C	P53U	P53E
Valve width [mm]	31						
Nominal width [mm]	9.4			8.9	8.1		
Design	Piston spool						
Flow direction	Reversible with external pilot air supply						
Pilot air supply	Internal or external						
Type of control	Piloted						
Manual override	Non-detenting, detenting						
Overlap	Positive overlap						
Sealing principle	Soft						
Type of mounting	Optionally via through-hole or on manifold rail						
Standard nominal flow rate qN [l/min]	2300	2300	2300	2000	1600	1600	
Type of actuation	Electrical						
Mounting position	Optional						
Exhaust function	With flow control						
Pneumatic port 1, 2, 3	G3/8	G3/8	G3/8	G3/8	G3/8	G3/8	
4, 5	-	-	G3/8	G3/8	G3/8	G3/8	
Pilot air port 12/14	G1/8						
Pilot exhaust air port 82/84	M5						

ATEX	
Type	VUVS-L...-EX2
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T4 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T115°C X Dc
Explosion-proof ambient temperature rating [°C]	10°C <= Ta <= +60°C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

# Solenoid valves VUVS-L, size 30

**FESTO**

Data sheet

Technical data – 3/2-way valves				
Order code for valves	M32C		M32U	
Normal position	Closed		Open	
Stable position	Monostable		Monostable	
Reset method	Pneumatic spring	Mechanical spring	Pneumatic spring	Mechanical spring
Switching times in [ms]	On	19	16	19
	Off	36	58	37
	Change-over	–	–	–
Product weight excluding solenoid coil	[g]	354	354	354
Product weight including solenoid coil	[g]	405	405	405

Technical data – 5/2-way valves				
Order code for valves	M52		B52	
Normal position	–		–	
Stable position	Monostable		Bistable	
Reset method	Pneumatic spring	Mechanical spring	–	
Switching times in [ms]	On	24	17	–
	Off	49	62	–
	Change-over	–	–	13
Product weight excluding solenoid coil	[g]	450	450	464
Product weight including solenoid coil	[g]	500	500	565

Technical data – 5/3-way valves				
Order code for valves	P53C		P53U	P53E
Normal position/midposition	Closed		Pressurised	Exhausted
Stable position	Monostable		–	
Reset method	Mechanical spring		–	
Switching times in [ms]	On	17	18	20
	Off	76	75	74
	Change-over	39	31	36
Product weight excluding solenoid coil	[g]	461	461	461
Product weight including solenoid coil	[g]	562	562	562

Safety data							
Max. positive test pulse 0 signal	[μs]	2000 (valves with VACF-B-....-1)					
Max. negative test pulse 1 signal	[μs]	3600 (valves with VACF-B-....-1)					
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27						
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6						

# Solenoid valves VUVS-L, size 30

Data sheet

**FESTO**

Operating and environmental conditions				
Order code for valves	M32	M52	B52	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure with internal pilot air supply [bar]	2.5 ... 10		1.5 ... 10	2.5 ... 10
Operating pressure with external pilot air supply [bar]	-0.9 ... +10			
Pilot pressure [bar]	2.5 ... 10		1.5 ... 10	2.5 ... 10
Ambient temperature [°C]	-10 ... +60			
Temperature of medium [°C]	-10 ... +60			
Approval	c UL us - Recognized (OL)			
Maritime classification <sup>1)</sup>	See certificate (only for VUVS-...-F8, VUVS-...-F8-...-A1 and VUVS-...-F8-...-B2)			
Corrosion resistance class CRC <sup>2)</sup>	2			

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) ➔ Certificates.

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Electrical		
	With solenoid coil	Without solenoid coil
Electrical connection	Plug connector type C, plug connector type B	Via solenoid coil ➔ Internet: vacf
Operating voltage [V DC]	12, und 24 ±10%	
	[V AC]	24, 110, 120, 230, 240 ±10%
Permissible voltage fluctuations [%]	10	
Power (24V DV) [W]	3.3	
Duty cycle [%]	100	
Degree of protection to EN 60529	IP65 with plug socket	

Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Piston spool	Wrought aluminium alloy
Screws	Steel, nickel-plated
Note on materials	RoHS-compliant


# Solenoid valves VUVS-L, size 30

FESTO

Data sheet –




## Dimensions

3/2-way valves, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

3/2-way valves, without solenoid coil



[1] Solenoid coil interface type

B/type C

[2] Location for inscription label

[4] Port 10/12 for pilot air supply

[6] Port 82 for pilot exhaust air

[7] For screw M5

Type	B1	B2	B3	B4	B5	D1	D3	D4	D5 ∅	H1	H2	H3	H4	H5
VUVS-L30-M32...-D-G38-...	31	23.3	–	2.5	2.5	G3/8	–	M5	8	57	31.8	9	63.7	51.6
VUVS-L30-M32...-ZD-G38-...			4.6				G1/8							

Type	L2	L4	L5	L6	L7	L8	L9	L11	L12	L14	L15	L16	L17	L19
VUVS-L30-M32...-D-G38-...	144.9	142.8	139.5	109.5	59.3	31	35.4	33.3	–	74.8	44.8	17	56	66.3
VUVS-L30-M32...-ZD-G38-...									20.8					


# Solenoid valves VUVS-L, size 30

Data sheet

FESTO


## Dimensions

5/2-way single solenoid valves, with solenoid coil



Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way single solenoid valves, without solenoid coil



[1] Solenoid coil interface  
type B/type C

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply

[5] Port 84 for pilot exhaust air

[7] For screw M5

[2] Location for inscription label

Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-L30-M52-...D-G38-...	31	23.3	–	2.5	2.5	G3/8	–	–	M5	8	57	31.8	9	63.7	51.6
VUVS-L30-M52-...ZD-G38-...			4.6				G1/8	G1/8							

Type	L2	L4	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-L30-M52-...D-G38-...	180.7	178.6	179.6	145.3	59.3	31	35.4	–	33.3	–	104.8	74.8	44.8	17	56	37.6	66.3
VUVS-L30-M52-...ZD-G38-...								128.8		20.8							


# Solenoid valves VUVS-L, size 30

FESTO

Data sheet

## Dimensions

5/3-way valves and 5/2-way valves, double solenoid, with solenoid coil




[1] Solenoid coil interface type  
B/type C

[2] Location for inscription label

[3] Port 14 for pilot air supply  
[4] Port 12 for pilot air supply

Download CAD data → [www.festo.com](http://www.festo.com)

5/3-way valves and 5/2-way valves, double solenoid, without solenoid coil



[5] Port 84 for pilot exhaust air  
[6] Port 82 for pilot exhaust air

[7] For screw M5

Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5	H1	H2	H3	H4	H5
VUVS-L30-P53...-MD-G38...	31	23.3	—	2.5	2.5	G3/8	—	—	M5	8	57	31.8	9	63.7	51.6
VUVS-L30-P53...-MZD-G38...			4.6				G1/8	G1/8							
VUVS-L30-B52-D-G38...			—				—	—							
VUVS-L30-B52-ZD-G38...			4.6				G1/8	G1/8							

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VUVS-L30-P53...-MD-G38...	220.3	185	216.2	182.9	179.6	149.6	59.3	31	35.4	—
VUVS-L30-P53...-MZD-G38...										128.8
VUVS-L30-B52-D-G38...										—
VUVS-L30-B52-ZD-G38...										128.8

Type	L11	L12	L13	L14	L15	L16	L17	L18	L19
VUVS-L30-P53...-MD-G38...	33.3	—	104.8	74.8	44.8	17	56	37.6	66.3
VUVS-L30-P53...-MZD-G38...		20.8							
VUVS-L30-B52-D-G38...		—							
VUVS-L30-B52-ZD-G38...		20.8							

# Solenoid valves VUVS-L, size 30


Accessories

**FESTO**

## Dimensions

Foot mounting

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1 ∅	D2 ∅	D3	D4	H1	H2	H3
VAME-B10-30-A	VUVS-L30-B52/P53	26.8	18.5	15.5	5.2	4.2	5.2	5.2	146	136.5
	VUVS-L30-M52									102.5
	VUVS-L30-M32									

Type	H4	H5	H7	H8	H9	H10	H11	H12	H13	H14
VAME-B10-30-A	VUVS-L30-B52/P53	112	50.5	31	11.5	3	231.2	231.2	231.2	231.2
	VUVS-L30-M52						197.2	191.5	191.5	
	VUVS-L30-M32							155.7	155.7	

Type	H15	L1	L3	L4	L5	L6	L7	L8	L9
VAME-B10-30-A	VUVS-L30-B52/P53	160	57	45.6	31	40	20	32	220.3
	VUVS-L30-M52								180.7
	VUVS-L30-M32								144.9

# Solenoid valves VUVS-L, size 30


FESTO

Accessories

## Dimensions

Wall mounting

Download CAD data → [www.festo.com](http://www.festo.com)



Type		B1	D1	D2	D3	H1	H2	H3	H4	H5	H6
VAME-B10-20-W	VUVS-L30-B52/P53	10	M3	M4	M5	35	20	10	11.5	9.7	8.7
	VUVS-L30-M52										
	VUVS-L30-M32										





Type		H7	H8	L1	L2	L3	L4	L5	L6	L7
VAME-B10-20-W	VUVS-L30-B52/P53	39.3	17.7	50	40	20	110.2	110.2	74.8	74.8
	VUVS-L30-M52									
	VUVS-L30-M32									

# Solenoid valves VUVS-L, size 30

Accessories

**FESTO**

## ★ Core product range

Ordering data		Code	Valve function	Part no.	Type
3/2-way valve with solenoid coil (24 V DC)					
	Monostable, normally closed, type C	M32C-A	Pneumatic spring return, Internal pilot air supply, direction of flow not reversible	★ 575568	VUVS-L30-M32C-AD-G38-F8-1C1
	M32C-M	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	★ 575570	VUVS-L30-M32C-MD-G38-F8-1C1	
5/2-way valve with solenoid coil (24 V DC)					
	Single solenoid, type C	M52-A	Pneumatic spring return, Internal pilot air supply, direction of flow not reversible	★ 575596	VUVS-L30-M52-AD-G38-F8-1C1
	M52-M	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	★ 575604	VUVS-L30-M52-MD-G38-F8-1C1	
	Bistable, type C	B52	Internal pilot air supply, direction of flow not reversible	★ 575611	VUVS-L30-B52-D-G38-F8-1C1
5/3-way valve with solenoid coil (24 V DC)					
	Mid-position closed, type C	P53C	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	★ 575618	VUVS-L30-P53C-MD-G38-F8-1C1




Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 30

**FESTO**


Accessories

Ordering data		Code	Valve function	Part no.	Type	
3/2-way valve without solenoid coil						
	M32C-A	Monostable, normally closed Pneumatic spring return, Internal pilot air supply, direction of flow not reversible Pneumatic spring return, External pilot air supply, direction of flow reversible	575564	VUVS-L30-M32C-AD-G38-F8 575565	VUVS-L30-M32C-AZD-G38-F8	
	M32C-M	Mechanical spring return, Internal pilot air supply, direction of flow not reversible Mechanical spring return, external pilot air supply, direction of flow reversible	575566	VUVS-L30-M32C-MD-G38-F8 575567	VUVS-L30-M32C-MZD-G38-F8	
	Monostable, normally open					
		M32U-A	Pneumatic spring return, Internal pilot air supply, direction of flow not reversible Pneumatic spring return, External pilot air supply, direction of flow reversible	575579	VUVS-L30-M32U-AD-G38-F8 575580	VUVS-L30-M32U-AZD-G38-F8
		M32U-M	Mechanical spring return, Internal pilot air supply, direction of flow not reversible Mechanical spring return, external pilot air supply, direction of flow reversible	575581	VUVS-L30-M32U-MD-G38-F8 575582	VUVS-L30-M32U-MZD-G38-F8
	3/2-way valve with solenoid coil (24 V DC)					
		M32C-A	Monostable, normally closed, type C Pneumatic spring return, External pilot air supply, direction of flow reversible	575569	VUVS-L30-M32C-AZD-G38-F8-1C1	
		M32C-M	Mechanical spring return, external pilot air supply, direction of flow reversible	575571	VUVS-L30-M32C-MZD-G38-F8-1C1	
Single solenoid, normally closed, type B						
	Pneumatic spring return, Internal pilot air supply, direction of flow not reversible Pneumatic spring return, External pilot air supply, direction of flow reversible	575572	VUVS-L30-M32C-AD-G38-F8-1B2 575573	VUVS-L30-M32C-AZD-G38-F8-1B2		
	Mechanical spring return, Internal pilot air supply, direction of flow not reversible Mechanical spring return, external pilot air supply, direction of flow reversible	575574	VUVS-L30-M32C-MD-G38-F8-1B2 575575	VUVS-L30-M32C-MZD-G38-F8-1B2		

# Solenoid valves VUVS-L, size 30

Accessories





**FESTO**

Ordering data		Code	Valve function	Part no.	Type	
3/2-way valve with solenoid coil (24 V DC)						
			Monostable, normally open, type C			
	M32U-A		Pneumatic spring return, Internal pilot air supply, direction of flow not reversible	575583	VUVS-L30-M32U-AD-G38-F8-1C1	
	M32U-A		Pneumatic spring return, External pilot air supply, direction of flow reversible	575584	VUVS-L30-M32U-AZD-G38-F8-1C1	
	M32U-M		Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575585	VUVS-L30-M32U-MD-G38-F8-1C1	
	M32U-M		Mechanical spring return, external pilot air supply, direction of flow reversible	575586	VUVS-L30-M32U-MZD-G38-F8-1C1	
	Monostable, normally open, type B					
	M32U-A		Pneumatic spring return, Internal pilot air supply, direction of flow not reversible	575587	VUVS-L30-M32U-AD-G38-F8-1B2	
			Pneumatic spring return, External pilot air supply, direction of flow reversible	575588	VUVS-L30-M32U-AZD-G38-F8-1B2	
M32U-M		Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575589	VUVS-L30-M32U-MD-G38-F8-1B2		
		Mechanical spring return, external pilot air supply, direction of flow reversible	575590	VUVS-L30-M32U-MZD-G38-F8-1B2		

# Solenoid valves VUVS-L, size 30

**FESTO**


Accessories

Ordering data		Code	Valve function	Part no.	Type	
5/2-way valve without solenoid coil						
	Monostable					
	M52-A	Pneumatic spring return, Internal pilot air supply, direction of flow not reversible		575594	VUVS-L30-M52-AD-G38-F8	
		Pneumatic spring return, External pilot air supply, direction of flow reversible		575595	VUVS-L30-M52-AZD-G38-F8	
	M52-M	Mechanical spring return, Internal pilot air supply, direction of flow not reversible		575602	VUVS-L30-M52-MD-G38-F8	
		Mechanical spring return, external pilot air supply, direction of flow reversible		575603	VUVS-L30-M52-MZD-G38-F8	
	Bistable					
		B52	Internal pilot air supply, direction of flow not reversible		575609	VUVS-L30-B52-D-G38-F8
		External pilot air supply, direction of flow reversible		575610	VUVS-L30-B52-ZD-G38-F8	
5/2-way valve with solenoid coil (24 V DC)						
	Single solenoid, type C					
	M52-A	Pneumatic spring return, External pilot air supply, direction of flow reversible		575597	VUVS-L30-M52-AZD-G38-F8-1C1	
		Mechanical spring return, external pilot air supply, direction of flow reversible		575605	VUVS-L30-M52-MZD-G38-F8-1C1	
	Single solenoid, type B					
	M52-A	Pneumatic spring return, Internal pilot air supply, direction of flow not reversible		575598	VUVS-L30-M52-AD-G38-F8-1B2	
		Pneumatic spring return, External pilot air supply, direction of flow reversible		575599	VUVS-L30-M52-AZD-G38-F8-1B2	
	M52-M	Mechanical spring return, Internal pilot air supply, direction of flow not reversible		575606	VUVS-L30-M52-MD-G38-F8-1B2	
		Mechanical spring return, external pilot air supply, direction of flow reversible		575607	VUVS-L30-M52-MZD-G38-F8-1B2	
	Bistable, type C					
	B52	external pilot air supply, direction of flow reversible		575612	VUVS-L30-B52-ZD-G38-F8-1C1	
	Double solenoid, type B					
	B52	Internal pilot air supply, direction of flow not reversible		575613	VUVS-L30-B52-D-G38-F8-1B2	
		external pilot air supply, direction of flow reversible		575614	VUVS-L30-B52-ZD-G38-F8-1B2	

# Solenoid valves VUVS-L, size 30

Accessories

**FESTO**

Ordering data		Code	Valve function	Part no.	Type	
5/3-way valve without solenoid coil						
	Mid-position closed	P53C	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575616	VUVS-L30-P53C-MD-G38-F8	
			Mechanical spring return, External pilot air supply, direction of flow reversible	575617	VUVS-L30-P53C-MZD-G38-F8	
	Mid-position exhausted					
		P53E	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575630	VUVS-L30-P53E-MD-G38-F8	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575631	VUVS-L30-P53E-MZD-G38-F8		
Mid-position pressurised						
	P53U	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575623	VUVS-L30-P53U-MD-G38-F8		
		Mechanical spring return, External pilot air supply, direction of flow reversible	575624	VUVS-L30-P53U-MZD-G38-F8		

# Solenoid valves VUVS-L, size 30

**FESTO**

Accessories

Ordering data		Code	Valve function	Part no.	Type
5/3-way valve with solenoid coil (24 V DC)					
		P53C	Mid-position closed, type C Mechanical spring return, External pilot air supply, direction of flow reversible	575619	VUVS-L30-P53C-MZD-G38-F8-1C1
Mid-position exhausted, type C					
	P53E	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575632	VUVS-L30-P53E-MD-G38-F8-1C1	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575633	VUVS-L30-P53E-MZD-G38-F8-1C1	
Mid-position pressurised, type C					
	P53U	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575625	VUVS-L30-P53U-MD-G38-F8-1C1	
		Mechanical spring return, External pilot air supply, direction of flow reversible	575626	VUVS-L30-P53U-MZD-G38-F8-1C1	
Mid-position closed, type B					
	P53C	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575620	VUVS-L30-P53C-MD-G38-F8-1B2	
		Mechanical spring return, External pilot air supply, direction of flow reversible	575621	VUVS-L30-P53C-MZD-G38-F8-1B2	
Mid-position exhausted, type B					
	P53E	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575634	VUVS-L30-P53E-MD-G38-F8-1B2	
		Mechanical spring return, external pilot air supply, direction of flow reversible	575635	VUVS-L30-P53E-MZD-G38-F8-1B2	
Mid-position pressurised, type B					
	P53U	Mechanical spring return, Internal pilot air supply, direction of flow not reversible	575627	VUVS-L30-P53U-MD-G38-F8-1B2	
		Mechanical spring return, External pilot air supply, direction of flow reversible	575628	VUVS-L30-P53U-MZD-G38-F8-1B2	

# Solenoid valves VUVS-L, size 30

Accessories

**FESTO**

Ordering data		Description	Part no.	Type		
Solenoid coils for valves						
	Connection pattern type C, to EN 175301-803	12 V DC	<b>8030810</b>	VACF-B-C1-5		
		24 V DC	<b>8030811</b>	VACF-B-C1-1		
		48 V DC	<b>8030812</b>	VACF-B-C1-7		
		24 V AC/50-60 Hz	<b>8030813</b>	VACF-B-C1-1A		
		48 V AC/50-60 Hz	<b>8030814</b>	VACF-B-C1-7A		
		110/120 V AC/50-60 Hz	<b>8030815</b>	VACF-B-C1-16B		
		230/240 V AC/50-60 Hz	<b>8030817</b>	VACF-B-C1-3W		
	Connection pattern type B, industry standard	12 V DC	<b>8030801</b>	VACF-B-B2-5		
		24 V DC	<b>8030802</b>	VACF-B-B2-1		
		48 V DC	<b>8030803</b>	VACF-B-B2-7		
		24 V AC/50-60 Hz	<b>8030804</b>	VACF-B-B2-1A		
		48 V AC/50-60 Hz	<b>8030805</b>	VACF-B-B2-7A		
		110/120 V AC/50-60 Hz	<b>8030806</b>	VACF-B-B2-16B		
		230/240 V AC/50-60 Hz	<b>8030808</b>	VACF-B-B2-3W		
Connection pattern type A, to EN 175301-803	12 V DC	<b>8030821</b>	VACF-A-A1-5			
	24 V DC	<b>8030822</b>	VACF-A-A1-1			
	48 V DC	<b>8030823</b>	VACF-A-A1-7			
	24 V AC/50-60 Hz	<b>8030824</b>	VACF-A-A1-1A			
	48 V AC/50-60 Hz	<b>8030825</b>	VACF-A-A1-7A			
	110/120 V AC, 50/60 Hz	<b>8030826</b>	VACF-A-A1-16B			
	230/240 V AC, 50/60 Hz	<b>8030828</b>	VACF-A-A1-3W			
Seal-SET for solenoid coil						
	Connection pattern type C to guarantee protection class IP67	<b>2643771</b>	VAMC-B10-C-B-S8			
	Connection pattern type B to guarantee protection class IP67	<b>8034609</b>	VAMC-B10-B-B-S8			
	Connection pattern type A to guarantee protection class IP67	<b>8034611</b>	VAMC-B10-A-B-S8			
Cover cap						
	For manual override, non-detenting or covered	<b>8028240</b>	VAMC-B10-20-CH2			
Plug socket						
	Connection pattern type C, to EN 175301-803					
	3-pin, screw terminal	Cable fitting M12	0 ... 250 V AC/DC	IP65	<b>539712</b>	MSSD-EB-M12
		Cable fitting Pg7			<b>★ 151687</b>	MSSD-EB
	4-pin, insulation displacement connector	Cable fitting M14	0 ... 250 V AC/DC	IP67	<b>192745</b>	MSSD-EB-S-M14
	3-pin, socket angled	Cable fitting M12	0 ... 24 V DC	IP65	<b>570367</b>	MSSD-EB-M12-24VDC-SD-EX
	Connection pattern type B, industry standard					
	3-pin, screw terminal	Cable fitting M16	0 ... 250 V AC/DC	IP65	<b>539710</b>	MSSD-F-M16
		Cable fitting Pg9			<b>★ 34431</b>	MSSD-F
	3-pin, insulation displacement connector	-	0 ... 250 V AC/DC	IP67	<b>192746</b>	MSSD-F-S-M16

Festo core product range


★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 30

**FESTO**

Accessories

Ordering data		Description	Part no.	Type
<b>Plug socket</b>				
	Connection pattern type A, to EN 175301-803			
	3-pin, socket angled	Cable fitting Pg9	0 ... 250 V AC/DC	IP65
	3-pin, socket angled	Cable fitting M16	0 ... 250 V AC/DC	IP65
	4-pin, socket angled	Cable connection, insulation displacement	0 ... 250 V AC/DC	IP67
<b>Adapters</b>				
	Socket, type C, to EN 175301-803	Plug connector M12x1, 2-pin, A-coded	12 ... 24 V AC/DC	IP65
<b>Plug socket with cable</b>				
	Connection pattern type C, to DIN EN 175301-803			
	Angled socket, 3-pin		24 V DC	LED
	Cable, open end, 3-wire		2.5 m	★ 151688 KMEB-1-24-2,5-LED
			5 m	151689 KMEB-1-24-5-LED
			10 m	193457 KMEB-1-24-10-LED
			230 V AC	–
			2.5 m	151690 KMEB-1-230AC-2,5
			5 m	151691 KMEB-1-230AC-5
	Connection pattern type B, industry standard			
	Angled socket, 3-pin		24 V DC	LED
	Cable, open end, 3-wire		2.5 m	★ 30935 KMF-1-24DC-2,5-LED
			5 m	30937 KMF-1-24DC-5-LED
			10 m	193458 KMF-1-24-10-LED
			230 V AC	–
			2.5 m	30936 KMF-1-230AC-2,5
			5 m	30938 KMF-1-230AC-5
<b>Connection pattern type A, to EN 175301-803</b>				
	Angled socket, 3-pin		24 V DC	LED
	Cable, open end, 3-wire		2.5 m	30931 KMC-1-24DC-2,5-LED
			5 m	30933 KMC-1-24DC-5-LED
			10 m	193459 KMC-1-24-10-LED
			230 V AC	–
			2.5 m	30932 KMC-1-230AC-2,5
			5 m	30934 KMC-1-230AC-5
<b>Illuminating seal</b>				
	Connection pattern type C, to DIN EN 175301-803		24 V DC	151717 MEB-LD-12-24DC
			230 V AC	151718 MEB-LD-230AC
	Connection pattern type B, industry standard		24 V DC	19143 MF-LD-12-24DC
			230 V AC	19144 MF-LD-230AC

Festo core product range


★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 30

Accessories

**FESTO**

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Push-in fitting with internal hex</b>					
	Connecting thread G1/8 for tubing O.D.	4 mm	<b>★ 186106</b>	QS-G1/8-4-I	<b>10</b>
			<b>133008</b>	QS-G1/8-4-I-100	<b>100</b>
<b>Angled push-in fitting with external hex</b>					
	Connecting thread for G3/8 for tubing O.D.	8 mm	<b>★ 186121</b>	QSL-G3/8-8	<b>10</b>
			<b>132055</b>	QSL-G3/8-8-50	<b>50</b>
		10 mm	<b>★ 186123</b>	QSL-G3/8-10	<b>10</b>
			<b>132056</b>	QSL-G3/8-10-20	<b>20</b>
		12 mm	<b>★ 186124</b>	QSL-G3/8-12	<b>10</b>
			<b>132057</b>	QSL-G3/8-12-20	<b>20</b>
<b>Angled push-in fitting, long, with external hex</b>					
	Connecting thread for G3/8 for tubing O.D.	8 mm	<b>186132</b>	QSLL-G3/8-8	<b>10</b>
		10 mm	<b>186134</b>	QSLL-G3/8-10	<b>10</b>
		12 mm	<b>186135</b>	QSLL-G3/8-12	<b>10</b>
<b>Silencer</b>					
	With connecting thread G, metal design	G3/8	<b>★ 6843</b>	U-3/8-B	<b>1</b>
	With connecting thread G, sinter design, long	G3/8	<b>★ 1205862</b>	AMTE-M-LH-G38	<b>10</b>

1) Packaging unit quantity


Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS-L, size 30

**FESTO**

Accessories

Ordering data		Description	Weight [g]	Part no.	Type
<b>Foot mounting</b>					
	With screw set for attaching the valve to the foot mounting	239		<b>8026337</b>	<b>VAME-B10-30-A</b>
<b>Wall mounting</b>					
	With screw set for mounting the valve on the wall mounting	53		<b>576413</b>	<b>VAME-B10-20-W</b>
<b>Set of spare parts</b>					
	Set comprising seals and screws	22		<b>8035637</b>	<b>VAME-B10-30-MK</b>
<b>Inscription label</b>					
	40 pieces in frame	-		<b>565306</b>	<b>ASLR-C-E4</b>

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS/valve manifold VTUS

Type code – Manifold block

**FESTO**

VABM	-	B10	-		-		-		-		-	
Valve manifold parts												
Manifold block	<b>VABM</b>											
Valve series												
VUVS		<b>B10</b>										
Valve width												
21 mm			<b>20</b>									
26.5 mm			<b>25</b>									
31 mm			<b>30</b>									
Version												
Common supply manifold				<b>-</b>								
Compact manifold block				<b>S</b>								
standard manifold block				<b>E</b>								
Extension module for standard manifold block				<b>EEE</b>								

Assembly	
<b>E</b>	Common supply manifold for mounting on one side
-	Standard mounting
Connection for valve function	
-	Manifold block for 5/2- and 5/3-way valves
<b>P3</b>	Manifold block for 3/2-way valves
<b>P53</b>	Common supply manifold
Number of valve positions	
<b>2 ... 10</b>	2 to 10
Pneumatic ports 1, 3, 5	
<b>G38</b>	G3/8
<b>G14</b>	G1/4
<b>G12</b>	G1/2
<b>G34</b>	G3/4

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Technical data – Manifold block, size 20

-  - Flow rate  
Up to 700 l/min



General technical data		Connection block standard		Extension module for standard manifold block		Manifold block compact		Common supply manifold on both sides / on one side			
For valve function		3/2	5/2, 5/3	3/2	5/2, 5/3	3/2	5/2, 5/3	3/2, 5/2, 5/3			
Grid dimension [mm]		22									
Type of mounting		Via through-hole									
Max. number of valve positions		10	10	2	2	10		10	4		
Connection 1		G3/8	G3/8	G3/8	G3/8	G1/4	G1/4	G3/8	G3/8		
Connection 3		G3/8	G3/8	G3/8	G3/8	G1/4	G1/4	–	–		
Connection 5		–	G3/8	–	G3/8	–	G1/4	–	–		
Connection 12		G1/8	G1/8	G1/8	G1/8	–	–	–	–		
Connection 14		–	G1/8	–	G1/8	–	–	–	–		
Corrosion resistance <sup>1)</sup>		2									

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Weight [g]									
Valve positions	2	3	4	5	6	7	8	9	10
Manifold block for 3/2-way valves, standard									
VABM-B10-20E-G38-...-P3	449	574	699	825	950	1075	1200	1326	1451
Manifold block, extension module for 3/2-way valves, standard									
VABM-B10-20EEE-G38-2-P3	324	–	–	–	–	–	–	–	–
Manifold block for 5/2- and 5/3-way valves, standard									
VABM-B10-20E-G38-...	680	866	1053	1239	1425	1612	1798	1985	2171
Manifold block, extension module for 5/2- and 5/3-way valves, standard									
VABM-B10-20EEE-G38-2	492	–	–	–	–	–	–	–	–
Manifold block for 3/2-way valves, compact									
VABM-B10-20S-G14-...-P3	280	360	441	521	601	681	762	842	922
Manifold block for 5/2- and 5/3-way valves, compact									
VABM-B10-20S-G14-...	344	439	535	630	726	821	917	1012	1108
Supply manifold for mounting on both sides									
VABM-B10-20-G38-...-P53	226	268	310	352	395	437	479	521	563
Supply manifold for mounting on one side									
VABM-B10-20-G38-2-P53-E	240	282	324	–	–	–	–	–	–

# Solenoid valves VUVS/valve manifold VTUS

Technical data – Manifold block, size 20

**FESTO**


## Materials

Manifold rail	Wrought aluminium alloy
Note on materials	RoHS-compliant

## Dimensions

Manifold block for 3/2-way valves, standard

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B11	B14	B15	B16	B22
VABM-B10-20E-G38-...-P3	75.5	53	66.5	63	50	24	12.5	11.5	25	5.5	31.5

Type	D1 Ø	D2	D4	H3	H4	H5	H6	H7	H9	L3	L4	L5	L9	T1
VABM-B10-20E-G38-...-P3	4.5	M4x6.5	M5	37	23.5	8.5	18	5	32	6	25	22	9.5	15.5

Valve positions	2	3	4	5	6	7	8	9	10
L1	72	94	116	138	160	182	204	226	248
L2	60	82	104	126	148	170	192	214	236

# Solenoid valves VUVS/valve manifold VTUS


FESTO

Technical data – Manifold block, size 20

## Dimensions

Manifold block, extension module for 3/2-way valves, standard

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B7	B6	B7	B8	B9	B16	H3
VABM-B10-20EEE-G38-2-P3	75.5	53	66.5	63	50	24	5.5	37

Type	H4	H5	H6	H7	H9	L1	L4	L5	L10
VABM-B10-20EEE-G38-2-P3	23.5	8.5	18	5	32	60	25	22	10

# Solenoid valves VUVS/valve manifold VTUS


Technical data – Manifold block, size 20

**FESTO**

## Dimensions

Manifold block for 5/2- and 5/3-way valves, standard

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B10	B11	B14	B15	B22
VABM-B10-20E-G38-...	110	100.5	97.5	73	81	55	29	12.5	42.5	25	20

Type	D1 Ø	D2	D4	H3	H4	H5	H6	H7	L3	L4	L5	L9	T1
VABM-B10-20E-G38-...	4.5	M4x6.5	M5	37	23.5	22	18	8.5	6	25	22	9.5	15.5

Valve positions	2	3	4	5	6	7	8	9	10
L1	72	94	116	138	160	182	204	226	248
L2	60	82	104	126	148	170	192	214	236

# Solenoid valves VUVS/valve manifold VTUS


FESTO

Technical data – Manifold block, size 20

## Dimensions

Manifold block, extension module for 5/2- and 5/3-way valves, standard

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B10	H3
VABM-B10-20EEE-G38-2	110	100.5	97.5	73	81	55	29	37

Type	H4	H5	H6	H7	L1	L4	L5	L10
VABM-B10-20EEE-G38-2	23.5	22	18	8.5	60	13	22	10

# Solenoid valves VUVS/valve manifold VTUS



Technical data – Manifold block, size 20

**FESTO**

## Dimensions

Manifold block for 3/2-way valves, compact

Download CAD data → [www.festo.com](http://www.festo.com)



[1] Ports 1 and 3: G1/4

Type	B4	B7	B8	B9	B11	B14	B15	B22	B23	B24
VABM-B10-20S-G14-...-P3	56.1	53.1	47	22	12.5	11.5	25	4	4.5	2



Type	D1 Ø	D2	H3	H4	H6	L3	L4	L5	L9
VABM-B10-20S-G14-...-P3	4.5	M4x6.5	33	9.7	18	6	25	22	9.5

Valve positions	2	3	4	5	6	7	8	9	10
L1	72	94	116	138	160	182	204	226	248
L2	60	82	104	126	148	170	192	214	236

## Dimensions

Manifold block for 5/2- and 5/3-way valves, compact

Download CAD data → [www.festo.com](http://www.festo.com)



[1] Ports 1, 3 and 5: G1/4

Type	B4	B7	B8	B9	B10	B11	B14	B15	B22	B23
VABM-B10-20S-G14-...	64.2	47	55.1	32.1	9.1	12.5	19.6	25	4	5

Type	D1 Ø	D2	H3	H4	H6	L3	L4	L5	L9
VABM-B10-20S-G14-...	4.5	M4x6.5	36	9.7	22.5	6	25	22	9.5

Valve positions	2	3	4	5	6	7	8	9	10
L1	72	94	116	138	160	182	204	226	248
L2	60	82	104	126	148	170	192	214	236

# Solenoid valves VUVS/valve manifold VTUS


FESTO

Technical data – Manifold block, size 20

## Dimensions

Common supply manifold for mounting on both sides

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B17	B18	B19	B20	B21	D1 Ø	D2	D3 Ø
VABM-B10-20-G38-...-P53	23	55	40	20	20	8.5	4.5	M4x6.5	5.2

Type	H3	H12	H16	L3	L4	L5	L7	L9	W1
VABM-B10-20-G38-...-P53	40	2	13	8	21	22	21	5	30°

Valve positions	2	3	4	5	6	7	8	9	10
L1	64	86	108	130	152	174	196	218	240
L2	90	112	134	156	178	200	222	244	266
L8	106	128	150	172	194	216	238	260	282

# Solenoid valves VUVS/valve manifold VTUS


Technical data – Manifold block, size 20

**FESTO**

## Dimensions

Common supply manifold, mounting on one side

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B17	B18	B19	B21	D1 Ø	D2	D3 Ø
VABM-B10-20-G38-2-P53-E	23	55	40	20	8.5	4.5	M4x6.5	5.2

Type	H3	H13	H14	L4	L5	L7	L9	W1
VABM-B10-20-G38-2-P53-E	40	106	90	21	22	50	5	30°





Valve positions	2	3	4
L1	64	86	108
L8	114	136	158

# Solenoid valves VUVS/valve manifold VTUS

FESTO

Ordering data – Manifold block, size 20

## Ordering data – Manifold block

	Description	Valve positions	Part no.	Type
<b>Standard manifold block</b>				
	For 3/2-way valves, incl. seals and screws for mounting valves  - Note • Blanking plugs for sealing the supply ports (1, 3 and 14) at one end are included in the scope of delivery. • Standard manifold block is not licensed for VUVS-LK solenoid valves!	2 3 4 5 6 7 8 9 10	576441 576442 576443 576444 576445 576446 576447 576448 576449	VABM-B10-20E-G38-2-P3 VABM-B10-20E-G38-3-P3 VABM-B10-20E-G38-4-P3 VABM-B10-20E-G38-5-P3 VABM-B10-20E-G38-6-P3 VABM-B10-20E-G38-7-P3 VABM-B10-20E-G38-8-P3 VABM-B10-20E-G38-9-P3 VABM-B10-20E-G38-10-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly  - Note • Blanking plugs for sealing the supply ports (1, 3, 5, 12 and 14) at one end are included in the scope of delivery. • Standard manifold block is not licensed for VUVS-LK solenoid valves!	2 3 4 5 6 7 8 9 10	576339 576340 576341 576342 576343 576344 576345 576346 576347	VABM-B10-20E-G38-2 VABM-B10-20E-G38-3 VABM-B10-20E-G38-4 VABM-B10-20E-G38-5 VABM-B10-20E-G38-6 VABM-B10-20E-G38-7 VABM-B10-20E-G38-8 VABM-B10-20E-G38-9 VABM-B10-20E-G38-10
<b>Extension module for standard manifold block</b>				
	For 3/2-way valves, incl. seals and screws for mounting valves	2	576490	VABM-B10-20EEE-G38-2-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly	2	576489	VABM-B10-20EEE-G38-2
<b>Compact manifold block</b>				
	For 3/2-way valves, incl. seals and screws for mounting valves  - Note Blanking plugs for sealing the supply ports (1, 3 and 14) at one end are included in the scope of delivery.	2 3 4 5 6 7 8 9 10	576465 576466 576467 576468 576469 576470 576471 576472 576473	VABM-B10-20S-G14-2-P3 VABM-B10-20S-G14-3-P3 VABM-B10-20S-G14-4-P3 VABM-B10-20S-G14-5-P3 VABM-B10-20S-G14-6-P3 VABM-B10-20S-G14-7-P3 VABM-B10-20S-G14-8-P3 VABM-B10-20S-G14-9-P3 VABM-B10-20S-G14-10-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly  - Note Blanking plugs for sealing the supply ports (1, 3, 5, 12 and 14) at one end are included in the scope of delivery.	2 3 4 5 6 7 8 9 10	576417 576418 576419 576420 576421 576422 576423 576424 576425	VABM-B10-20S-G14-2 VABM-B10-20S-G14-3 VABM-B10-20S-G14-4 VABM-B10-20S-G14-5 VABM-B10-20S-G14-6 VABM-B10-20S-G14-7 VABM-B10-20S-G14-8 VABM-B10-20S-G14-9 VABM-B10-20S-G14-10



Festo core product range

★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

## Solenoid valves VUVS/valve manifold VTUS

Ordering data – Manifold block, size 20

Ordering data		Description	Valve positions	Part no.	Type
<b>Supply manifold</b>					
	For mounting on both sides, incl. seals and screws for valve assembly	2	★ 576363	VABM-B10-20-G38-2-P53	
		3	576364	VABM-B10-20-G38-3-P53	
		4	★ 576365	VABM-B10-20-G38-4-P53	
		5	576366	VABM-B10-20-G38-5-P53	
		6	★ 576367	VABM-B10-20-G38-6-P53	
		7	576368	VABM-B10-20-G38-7-P53	
		8	★ 576369	VABM-B10-20-G38-8-P53	
		9	576370	VABM-B10-20-G38-9-P53	
		10	★ 576371	VABM-B10-20-G38-10-P53	
	For mounting on one side, incl. seals and screws for valve mounting	2	576414	VABM-B10-20-G38-2-P53-E	
		3	576415	VABM-B10-20-G38-3-P53-E	
		4	576416	VABM-B10-20-G38-4-P53-E	







### Note

Blanking plug for sealing the supply port (1) at one end included in the scope of delivery.

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Ordering data – Manifold block, size 20

Ordering data		Description	Weight [g]	Part no.	Type
<b>Cover plate</b>					
	For valve position on manifold block for 5/2-, 5/3-way valves	78		<b>★ 576410</b>	<b>VABB-B10-20-E</b>
	For valve position on manifold block for 3/2-way valves	56		<b>★ 576411</b>	<b>VABB-B10-20-E-P3</b>
	For valve position on common supply manifold	13		<b>★ 576409</b>	<b>VABB-B10-20-A</b>
<b>Supply plate</b>					
	For valve position on manifold block for 5/2-, 5/3-way valves	78		<b>576492</b>	<b>VABF-B10-20-P1A4-G18</b>
	For valve position on manifold block for 3/2-way valves	56		<b>576493</b>	<b>VABF-B10-20-P1A4-G18-P3</b>
<b>Supply plate</b>					
	For valve position on common supply manifold	13		<b>576491</b>	<b>VABF-B10-20-P1-G18</b>

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS/valve manifold VTUS

Ordering data – Manifold block, size 20

**FESTO**

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Push-in fitting with external hex</b>					
	Connecting thread M5 for tubing O.D.	12 mm	★ 186350	QS-G1/4-12	10
	Connecting thread for G3/8 for tubing O.D.	16 mm	★ 186347	QS-G3/8-16	1
<b>Push-in fitting with internal hex socket</b>					
	Connecting thread M5 for tubing O.D.	4 mm	★ 153315	QSM-M5-4-I	10
	Connecting thread G1/8 for tubing O.D.	4 mm	★ 186106	QS-G1/8-4-I	10
			133008	QS-G1/8-4-I-100	100
		6 mm	★ 186107	QS-G1/8-6-I	10
			133009	QS-G1/8-6-I-100	100
		8 mm	★ 186109	QS-G1/8-8-I	10
			133010	QS-G1/8-8-I-100	100
	Connecting thread G1/4 for tubing O.D.	8 mm	★ 186110	QS-G1/4-8-I	10
		10 mm	★ 186112	QS-G1/4-10-I	10
	Connecting thread for G3/8 for tubing O.D.	8 mm	★ 186111	QS-G3/8-8-I	10
		10 mm	★ 186113	QS-G3/8-10-I	10
		12 mm	★ 186114	QS-G3/8-12-I	10
<b>Angled push-in fitting with external hex</b>					
	Connecting thread G1/8 for tubing O.D.	4 mm	★ 186116	QSL-G1/8-4	10
			132048	QSL-G1/8-4-100	100
	6 mm	6 mm	★ 186117	QSL-G1/8-6	10
			132049	QSL-G1/8-6-100	100
	8 mm	8 mm	★ 186119	QSL-G1/8-8	10
			132050	QSL-G1/8-8-50	50
	Connecting thread G1/4 for tubing O.D.	8 mm	★ 186120	QSL-G1/4-8	10
			132052	QSL-G1/4-8-50	50
	10 mm	10 mm	★ 186122	QSL-G1/4-10	10
			132053	QSL-G1/4-10-50	50
	12 mm	12 mm	★ 186351	QSL-G1/4-12	10
			132054	QSL-G1/4-12-20	20
	Connecting thread for G3/8 for tubing O.D.	8 mm	★ 186121	QSL-G3/8-8	10
			132055	QSL-G3/8-8-50	50
	10 mm	10 mm	★ 186123	QSL-G3/8-10	10
			132056	QSL-G3/8-10-20	20
	12 mm	12 mm	★ 186124	QSL-G3/8-12	10
			132057	QSL-G3/8-12-20	20
		16 mm	★ 186348	QSL-G3/8-16	1
<b>Angled push-in fitting, long, with external hex</b>					
	Connecting thread G1/8 for tubing O.D.	4 mm	186127	QSLL-G1/8-4	10
			133015	QSLL-G1/8-4-100	100
	6 mm	6 mm	186128	QSLL-G1/8-6	10
			133016	QSLL-G1/8-6-100	100
	8 mm	8 mm	186130	QSLL-G1/8-8	10
			133017	QSLL-G1/8-8-100	100

1) Packaging unit quantity


Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ☆ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Ordering data – Manifold block, size 20

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Silencer</b>					
	With connecting thread G, polymer design	G1/8	<b>★ 2307</b>	<b>U-1/8</b>	<b>1</b>
		G1/4	<b>★ 534222</b>	<b>U-1/8-50</b>	<b>50</b>
	With connecting thread G, metal design	G3/8	<b>★ 2316</b>	<b>U-1/4</b>	<b>1</b>
			<b>★ 534223</b>	<b>U-1/4-20</b>	<b>20</b>
	With connecting thread G, sinter design, long	G1/4	<b>★ 1205861</b>	<b>AMTE-M-LH-G14</b>	<b>20</b>
		G3/8	<b>★ 1205862</b>	<b>AMTE-M-LH-G38</b>	<b>10</b>
<b>Blanking plug</b>					
	With connecting thread	G1/8	<b>★ 3568</b>	<b>B-1/8</b>	<b>10</b>
			<b>534213</b>	<b>B-1/8-100</b>	<b>100</b>
		G1/4	<b>★ 3569</b>	<b>B-1/4</b>	<b>10</b>
			<b>534214</b>	<b>B-1/4-50</b>	<b>50</b>
		G3/8	<b>★ 3570</b>	<b>B-3/8</b>	<b>10</b>
			<b>534215</b>	<b>B-3/8-20</b>	<b>20</b>
<b>Separator</b>					
	For creating pressure zones	G1/8	<b>569995</b>	<b>VABD-8-B</b>	<b>1</b>
		G1/4	<b>569996</b>	<b>VABD-10-B</b>	<b>1</b>
		G3/8	<b>574483</b>	<b>VABD-14-B</b>	<b>1</b>
<b>H-rail mounting</b>					
	For mounting the valve manifold on standard H-rail TH 35-7,5 or TH 35-15, to EN 60715		<b>★ 569998</b>	<b>VAME-T-M4</b>	<b>2</b>

1) Packaging unit quantity

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS/valve manifold VTUS

Technical data – Manifold block, size 25

**FESTO**

-  - Flow rate  
Up to 1300 l/min



General technical data		Connection block standard		Extension module for standard manifold block		Manifold block compact		Common supply manifold on both sides	
Valve function		3/2	5/2, 5/3	3/2	5/2, 5/3	3/2	5/2, 5/3	3/2, 5/2, 5/3	on one side
Grid dimension [mm]		27.5							
Type of mounting		Via through-hole						Via mounting bracket	
Max. number of valve positions		10	10	2	2	10		10	4
Connection 1	G1/2	G1/2	G1/2	G1/2	G3/8	G3/8	G1/2	G1/2	
Connection 3	G1/2	G1/2	G1/2	G1/2	G3/8	G3/8	–	–	
Connection 5	–	G1/2	–	G1/2	–	G3/8	–	–	
Connection 12	G1/8	G1/8	G1/8	G1/8	–	–	–	–	
Connection 14	–	G1/8	–	G1/8	–	–	–	–	
Corrosion resistance <sup>1)</sup>	2								

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Weight [g]									
Valve positions	2	3	4	5	6	7	8	9	10
Manifold block for 3/2-way valves, standard									
VABM-B10-25E-G12-...-P3	726	960	1194	1428	1662	1896	2130	2364	2598
Manifold block, extension module for 3/2-way valves, standard									
VABM-B10-25EEE-G12-2-P3	340	–	–	–	–	–	–	–	–
Manifold block for 5/2- and 5/3-way valves, standard									
VABM-B10-25E-G12-...	927	1224	1521	1818	2115	2412	2709	3006	3303
Manifold block, extension module for 5/2- and 5/3-way valves, standard									
VABM-B10-25EEE-G12-2	258	–	–	–	–	–	–	–	–
Manifold block for 3/2-way valves, compact									
VABM-B10-25S-G38-...-P3	369	488	607	726	845	964	1083	1202	1321
Manifold block for 5/2- and 5/3-way valves, compact									
VABM-B10-25S-G38-...	438	579	720	861	1002	1143	1284	1425	1566
Supply manifold for mounting on both sides									
VABM-B10-25-G38-...-P53	258	340	422	504	586	668	750	832	914
Supply manifold for mounting on one side									
VABM-B10-25-G38-2-P53-E	258	340	422	–	–	–	–	–	–

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Technical data – Manifold block, size 25


## Materials

Manifold rail	Wrought aluminium alloy
Note on materials	RoHS-compliant

## Dimensions

Manifold block for 3/2-way valves, standard

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B11	B14	B15	B16	B22
VABM-B10-25E-G12-...-P3	93	67.5	80.5	78	62	30	16	14	32	6	37

Type	D1 Ø	D2	D4	H3	H4	H5	H6	H7	H9	L3	L4	L5	L9	T1
VABM-B10-25E-G12-...-P3	5.5	M4x9	M5	45	25	9	22	5	39	6	29.8	27.5	9.5	18

Valve positions	2	3	4	5	6	7	8	9	10
L1	87	114.5	142	169.5	197	224.5	252	279.5	307
L2	75	102.5	130	157.5	185	212.5	240	267.5	295

# Solenoid valves VUVS/valve manifold VTUS


Technical data – Manifold block, size 25

**FESTO**

## Dimensions

Manifold block, extension module for 3/2-way valves, standard

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B16	H3
VABM-B10-25EEE-G12-2-P3	93	67.5	80.5	78	62	30	6	45

Type	H4	H5	H6	H7	H9	L4	L5	L10	L1
VABM-B10-25EEE-G12-2-P3	25	9	22	5	39	18.8	27.5	9	76

# Solenoid valves VUVS/valve manifold VTUS


FESTO

Technical data – Manifold block, size 25

## Dimensions

Manifold block for 5/2- and 5/3-way valves, standard

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B10	B11	B14	B15	B22
VABM-B10-25E-G12...	126	119	113.5	80	95	63	31	16	47	32	27

Type	D1 Ø	D2	D4	H3	H4	H5	H6	H7	L3	L4	L5	L9	T1
VABM-B10-25E-G12...	5.5	M4x9	M5	45	25	22	22	9	6	29.8	27.5	10.5	18

Valve positions	2	3	4	5	6	7	8	9	10
L1	87	114.5	142	169.5	197	224.5	252	279.5	307
L2	75	102.5	130	157.5	185	212.5	240	267.5	295

# Solenoid valves VUVS/valve manifold VTUS


Technical data – Manifold block, size 25

**FESTO**

## Dimensions

Manifold block, extension module for 5/2- and 5/3-way valves, standard

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B10	H3
VABM-B10-25EEE-G12-2	110	100.5	97.5	73	81	55	29	37

Type	H4	H5	H6	H7	L1	L4	L5	L10
VABM-B10-25EEE-G12-2	23.5	22	18	8.5	60	13	22	10

# Solenoid valves VUVS/valve manifold VTUS


FESTO

Technical data – Manifold block, size 25

## Dimensions

Manifold block for 3/2-way valves, compact

Download CAD data ➔ [www.festo.com](http://www.festo.com)




Type	B4	B7	B8	B9	B11	B14	B15	B22	B23
VABM-B10-25S-G38-...-P3	70.3	67.3	58.8	30	16	14	32	6.5	5
Type	D1 Ø	D2	H3	H4	H6	L3	L4	L5	L9
VABM-B10-25S-G38-...-P3	5.5	M4x9	34	13.5	20	6	29.8	27.5	9.5
Valve positions	2	3	4	5	6	7	8	9	10
L1	87	114.5	142	169.5	197	224.5	252	279.5	307
L2	75	102.5	130	157.5	185	212.5	240	267.5	295

## Dimensions

Manifold block for 5/2- and 5/3-way valves, compact

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B7	B8	B9	B10	B11	B14	B15	B22	B23
VABM-B10-25S-G38-...	80.5	61.5	69	40.3	11.5	16	24.3	32	6.5	8
Type	D1 Ø	D2	H3	H4	H6	L3	L4	L5	L9	
VABM-B10-25S-G38-...	5.5	M4x9	34	13.5	20	6	29.8	27.5	9.5	
Valve positions	2	3	4	5	6	7	8	9	10	
L1	87	114.5	142	169.5	197	224.5	252	279.5	307	
L2	75	102.5	130	157.5	185	212.5	240	267.5	295	

# Solenoid valves VUVS/valve manifold VTUS


Technical data – Manifold block, size 25

**FESTO**

## Dimensions

Common supply manifold for mounting on both sides

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B17	B18	B19	B20	B21	D1 Ø	D2	D3 Ø
VABM-B10-25-G12-...-P53	28.7	75	60	35	27.5	11.4	4.5	M4x9	6.6

Type	H3	H12	H16	L3	L4	L5	L7	L9	W1
VABM-B10-25-G12-...-P53	52	2	19	8	29.8	27.5	24	6	30°

Valve positions	2	3	4	5	6	7	8	9	10
L1	87	114.5	142	169.5	197	224.5	252	279.5	307
L2	119	146.5	174	201.5	229	256.5	284	311.5	339
L8	135	162.5	190	217.5	245	272.5	300	327.5	355

# Solenoid valves VUVS/valve manifold VTUS


FESTO

Technical data – Manifold block, size 25

## Dimensions

Common supply manifold, mounting on one side

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B17	B18	B19	B21	D1 Ø	D2	D3 Ø
VABM-B10-25-G12-...-P53-E	28.7	80	60	35	11.4	4.5	M4x9	6.6

Type	H3	H13	H14	L4	L5	L7	L9	W1
VABM-B10-25-G12-...-P53-E	52	128	112	29.8	27.5	64	6	30°





Valve positions	2	3	4
L1	87	114.5	142
L8	151	178.5	206

# Solenoid valves VUVS/valve manifold VTUS

Ordering data – Manifold block, size 25

**FESTO**

## Ordering data – Manifold block

	Description	Valve positions	Part no.	Type
<b>Standard manifold block</b>				
	For 3/2-way valves, incl. seals and screws for mounting valves  - Note <ul style="list-style-type: none"><li>• Blanking plugs for sealing the supply ports (1, 3 and 14) at one end are included in the scope of delivery.</li><li>• Standard manifold block is not licensed for VUVS-LK solenoid valves!</li></ul>	2 3 4 5 6 7 8 9 10	8026279 8026280 8026281 8026282 8026283 8026284 8026285 8026286 8026287	VABM-B10-25E-G12-2-P3 VABM-B10-25E-G12-3-P3 VABM-B10-25E-G12-4-P3 VABM-B10-25E-G12-5-P3 VABM-B10-25E-G12-6-P3 VABM-B10-25E-G12-7-P3 VABM-B10-25E-G12-8-P3 VABM-B10-25E-G12-9-P3 VABM-B10-25E-G12-10-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly  - Note <ul style="list-style-type: none"><li>• Blanking plugs for sealing the supply ports (1, 3, 5, 12 and 14) at one end are included in the scope of delivery.</li><li>• Standard manifold block is not licensed for VUVS-LK solenoid valves!</li></ul>	2 3 4 5 6 7 8 9 10	8026243 8026244 8026245 8026246 8026247 8026248 8026249 802625 8026251	VABM-B10-25E-G12-2 VABM-B10-25E-G12-3 VABM-B10-25E-G12-4 VABM-B10-25E-G12-5 VABM-B10-25E-G12-6 VABM-B10-25E-G12-7 VABM-B10-25E-G12-8 VABM-B10-25E-G12-9 VABM-B10-25E-G12-10
<b>Extension module for standard manifold block</b>				
	For 3/2-way valves, incl. seals and screws for mounting valves	2	8026316	VABM-B10-25EEE-G12-2-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly	2	8026315	VABM-B10-25EEE-G12-2
<b>Compact manifold block</b>				
	For 3/2-way valves, incl. seals and screws for mounting valves  - Note <ul style="list-style-type: none"><li>Blanking plugs for sealing the supply ports (1, 3 and 14) at one end are included in the scope of delivery.</li></ul>	2 3 4 5 6 7 8 9 10	★ 8026297 8026298 ★ 8026299 8026300 ★ 8026301 8026302 ★ 8026303 8026304 ★ 8026305	VABM-B10-25S-G38-2-P3 VABM-B10-25S-G38-3-P3 VABM-B10-25S-G38-4-P3 VABM-B10-25S-G38-5-P3 VABM-B10-25S-G38-6-P3 VABM-B10-25S-G38-7-P3 VABM-B10-25S-G38-8-P3 VABM-B10-25S-G38-9-P3 VABM-B10-25S-G38-10-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly  - Note <ul style="list-style-type: none"><li>Blanking plugs for sealing the supply ports (1, 3, 5, 12 and 14) at one end are included in the scope of delivery.</li></ul>	2 3 4 5 6 7 8 9 10	★ 8026261 8026262 ★ 8026263 8026264 ★ 8026265 8026266 ★ 8026267 8026268 ★ 8026269	VABM-B10-25S-G38-2 VABM-B10-25S-G38-3 VABM-B10-25S-G38-4 VABM-B10-25S-G38-5 VABM-B10-25S-G38-6 VABM-B10-25S-G38-7 VABM-B10-25S-G38-8 VABM-B10-25S-G38-9 VABM-B10-25S-G38-10



Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Ordering data – Manifold block, size 25

Ordering data		Description	Valve posi-tions	Part no.	Type
<b>Supply manifold</b>					
		For mounting on both sides, incl. seals and screws for valve assembly	2 3 4 5 6 7 8 9 10	<b>8026219</b> <b>8026220</b> <b>8026221</b> <b>8026222</b> <b>8026223</b> <b>8026224</b> <b>8026225</b> <b>8026226</b> <b>8026227</b>	VABM-B10-25-G12-2-P53 VABM-B10-25-G12-3-P53 VABM-B10-25-G12-4-P53 VABM-B10-25-G12-5-P53 VABM-B10-25-G12-6-P53 VABM-B10-25-G12-7-P53 VABM-B10-25-G12-8-P53 VABM-B10-25-G12-9-P53 VABM-B10-25-G12-10-P53
		For mounting on one side, incl. seals and screws for valve mounting	2 3 4	<b>8026237</b> <b>8026238</b> <b>8026239</b>	VABM-B10-25-G12-2-P53-E VABM-B10-25-G12-3-P53-E VABM-B10-25-G12-4-P53-E

- - Note

Blanking plug for sealing the supply port (1) at one end included in the scope of delivery.





Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ☆ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS/valve manifold VTUS

Ordering data – Manifold block, size 25

**FESTO**

Ordering data		Description	Weight [g]	Part no.	Type
<b>Cover plate</b>					
	For valve position on manifold block for 3/2-way valves	84		<b>★ 8026210</b>	<b>VABB-B10-25-E-P3</b>
	For valve position on manifold block for 5/2-, 5/3-way valves	117		<b>★ 8026209</b>	<b>VABB-B10-25-E</b>
	For valve position on common supply manifold	28		<b>★ 8026208</b>	<b>VABB-B10-25-A</b>
<b>Supply plate</b>					
	For valve position on manifold block for 3/2-way valves	80		<b>8026319</b>	<b>VABF-B10-25-P1A4-G14-P3</b>
	For valve position on manifold block for 5/2-, 5/3-way valves	110		<b>8026318</b>	<b>VABF-B10-25-P1A4-G14</b>
<b>Supply plate</b>					
	For valve position on common supply manifold	26		<b>8026317</b>	<b>VABF-B10-25-P1-G14</b>

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Ordering data – Manifold block, size 25

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Push-in fitting with external hex</b>					
	Connecting thread for G3/8 for tubing O.D.	16 mm	★ 186347	QS-G3/8-16	1
	Connecting thread G1/2 for tubing O.D.	16 mm	★ 186105	QS-G1/2-16	1
			132047	QS-G1/2-16-20	20
<b>Push-in fitting with internal hex socket</b>					
	Connecting thread M5 for tubing O.D.	4 mm	★ 153315	QSM-M5-4-I	10
	Connecting thread G1/8 for tubing O.D.	6 mm	★ 186107	QS-G1/8-6-I	10
			133009	QS-G1/8-6-I-100	100
	Connecting thread G1/4 for tubing O.D.	6 mm	★ 186108	QS-G1/4-6-I	10
		8 mm	★ 186110	QS-G1/4-8-I	10
		10 mm	★ 186112	QS-G1/4-10-I	10
	Connecting thread G3/8 for tubing O.D.	8 mm	★ 186111	QS-G3/8-8-I	10
		10 mm	★ 186113	QS-G3/8-10-I	10
		12 mm	★ 186114	QS-G3/8-12-I	10
	Connecting thread G1/2 for tubing O.D.	12 mm	★ 186115	QS-G1/2-12-I	1
<b>Angled push-in fitting with external hex</b>					
	Connecting thread G1/4 for tubing O.D.	6 mm	★ 186118	QSL-G1/4-6	10
			132051	QSL-G1/4-6-100	100
	8 mm	8 mm	★ 186120	QSL-G1/4-8	10
			132052	QSL-G1/4-8-50	50
	10 mm	10 mm	★ 186122	QSL-G1/4-10	10
			132053	QSL-G1/4-10-50	50
	Connecting thread G3/8 for tubing O.D.	8 mm	★ 186121	QSL-G3/8-8	10
			132055	QSL-G3/8-8-50	50
	10 mm	10 mm	★ 186123	QSL-G3/8-10	10
			132056	QSL-G3/8-10-20	20
	12 mm	12 mm	★ 186124	QSL-G3/8-12	10
			132057	QSL-G3/8-12-20	20
	16 mm	16 mm	★ 186348	QSL-G3/8-16	1
	Connecting thread G1/2 for tubing O.D.	12 mm	★ 186125	QSL-G1/2-12	1
			132058	QSL-G1/2-12-20	20
	16 mm	16 mm	★ 186126	QSL-G1/2-16	1
			132059	QSL-G1/2-16-20	20
<b>Angled push-in fitting, long, with external hex</b>					
	Connecting thread G1/4 for tubing O.D.	6 mm	186129	QSLL-G1/4-6	10
		8 mm	186131	QSLL-G1/4-8	10
		10 mm	186133	QSLL-G1/4-10	10

1) Packaging unit quantity

# Solenoid valves VUVS/valve manifold VTUS

Ordering data – Manifold block, size 25

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Silencer</b>					
	With connecting thread G, polymer design	G1/4	<b>2316</b> 534223	<b>U-1/4</b> <b>U-1/4-20</b>	<b>1</b> <b>20</b>
		G3/8	534224	<b>U-3/8-20</b>	<b>20</b>
	With connecting thread G, metal design	G3/8	<b>6843</b>	<b>U-3/8-B</b>	<b>1</b>
		G1/2	<b>6844</b>	<b>U-1/2-B</b>	<b>1</b>
	With connecting thread G, sinter design, long	G3/8	<b>1205862</b>	<b>AMTE-M-LH-G38</b>	<b>10</b>
		G1/2	<b>1205863</b>	<b>AMTE-M-LH-G12</b>	<b>10</b>
<b>Blanking plug</b>					
	With connecting thread	G1/8	<b>3568</b> 534213	<b>B-1/8</b> <b>B-1/8-100</b>	<b>10</b> <b>100</b>
		G3/8	<b>3570</b> 534215	<b>B-3/8</b> <b>B-3/8-20</b>	<b>10</b> <b>20</b>
		G1/2	<b>3571</b> 534216	<b>B-1/2</b> <b>B-1/2-20</b>	<b>10</b> <b>20</b>
<b>Separator</b>					
	For creating pressure zones	G1/8	<b>569995</b>	<b>VABD-8-B</b>	<b>1</b>
		G3/8	<b>574483</b>	<b>VABD-14-B</b>	<b>1</b>
		G1/2	<b>8022483</b>	<b>VABD-17.5-B</b>	<b>1</b>
<b>H-rail mounting</b>					
	For mounting the valve manifold on standard H-rail TH 35-7,5 or TH 35-15, to EN 60715		<b>2636436</b>	<b>VAME-T-M5</b>	<b>2</b>

1) Packaging unit quantity

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Technical data – Manifold block, size 30

-  - Flow rate  
Up to 2300 l/min



General technical data		Connection block standard		Extension module for standard manifold block		Manifold block compact		Common supply manifold on both sides / on one side			
For valve function		3/2	5/2, 5/3	3/2	5/2, 5/3	3/2	5/2, 5/3	3/2, 5/2, 5/3			
Grid dimension [mm]	32										
Type of mounting	Via through-hole										
Max. number of valve positions	10	10	2	2	10	10	10	4			
Connection 1	G3/4	G3/4	G3/4	G3/4	G1/2	G1/2	G3/4	G3/4			
Connection 3	G3/4	G3/4	G3/4	G3/4	G1/2	G1/2	–	–			
Connection 5	–	G3/4	–	G3/4	–	G1/2	–	–			
Connection 12	G1/8	G1/8	G1/8	G1/8	–	–	–	–			
Connection 14	–	G1/8	–	G1/8	–	–	–	–			
Corrosion resistance class CRC <sup>1)</sup>	2										

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Weight [g]									
Valve positions	2	3	4	5	6	7	8	9	10
Manifold block for 3/2-way valves, standard									
VABM-B10-30E-G34-...-P3	1411	1828	2245	2662	3079	3496	3913	4330	4747
Manifold block, extension module for 3/2-way valves, standard									
VABM-B10-30EEE-G34-2-P3	1111	–	–	–	–	–	–	–	–
Manifold block for 5/2- and 5/3-way valves, standard									
VABM-B10-30E-G34-...	1722	2213	2703	3194	3684	4175	4665	5156	5646
Manifold block, extension module for 5/2- and 5/3-way valves, standard									
VABM-B10-30EEE-G34-2	1318	–	–	–	–	–	–	–	–
Manifold block for 3/2-way valves, compact									
VABM-B10-30S-G12-...-P3	652	872	1093	1313	1533	1753	1973	2193	2413
Manifold block for 5/2- and 5/3-way valves, compact									
VABM-B10-30S-G12-...	759	1013	1267	1522	1776	2030	2285	2539	2793
Supply manifold for mounting on both sides									
VABM-B10-30-G34-...-P53	818	977	1135	1293	1452	1610	1768	1927	2085
Supply manifold for mounting on one side									
VABM-B10-30-G34-2-P53-E	852	1011	1169	–	–	–	–	–	–

# Solenoid valves VUVS/valve manifold VTUS

Technical data – Manifold block, size 30

**FESTO**


## Materials

Manifold rail	Wrought aluminium alloy
Note on materials	RoHS-compliant

## Dimensions

Manifold block for 3/2-way valves, standard

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B11	B14	B15	B16	B22
VABM-B10-30E-G34-...-P3	108.2	79	93.2	94.7	75.7	36.2	19	17.2	38	6.5	44.5

Type	D1 Ø	D2	D4	H3	H4	H5	H6	H7	H9	L3	L4	L5	L9	T1
VABM-B10-30E-G34-...-P3	6.3	M5x11	M5	61	35	9	28.5	6.5	54.5	7.5	34	32	12	18

Valve positions	2	3	4	5	6	7	8	9	10
L1	100	132	164	196	228	260	292	324	356
L2	85	117	149	181	213	245	277	309	341

# Solenoid valves VUVS/valve manifold VTUS


FESTO

Technical data – Manifold block, size 30

## Dimensions

Manifold block, extension module for 3/2-way valves, standard

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B16	H3
VABM-B10-30EEE-G34-2-P3	108.2	79	93.2	94.7	75.7	36.2	6.5	61

Type	H4	H5	H6	H7	H9	L4	L5	L10	L1
VABM-B10-30EEE-G34-2-P3	35	9	28.5	6.5	54.5	19	32	15	85

# Solenoid valves VUVS/valve manifold VTUS


Technical data – Manifold block, size 30

FESTO

## Dimensions

Manifold block for 5/2- and 5/3-way valves, standard

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B10	B11	B14	B15	B22
VABM-B10-30E-G34-...	144	137	129	104	111.5	72	32.5	19	53	38	30

Type	D1 Ø	D2	D4	H3	H4	H5	H6	H7	L3	L4	L5	L9	T1
VABM-B10-30E-G34-...	6.3	M5x11	M5	61	35	22	28.5	9	7.5	34	32	12	18

Valve positions	2	3	4	5	6	7	8	9	10
L1	100	132	164	196	228	260	292	324	356
L2	85	117	149	181	213	245	277	309	341

# Solenoid valves VUVS/valve manifold VTUS


**FESTO**

Technical data – Manifold block, size 30

## Dimensions

Manifold block, extension module for 5/2- and 5/3-way valves, standard

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B5	B6	B7	B8	B9	B10	H3
VABM-B10-30EEE-G34-2	144	137	129	104	111.5	72	32.5	61

Type	H4	H5	H6	H7	L1	L4	L5	L10
VABM-B10-30EEE-G34-2	35	22	28.5	9	85	19	32	15

# Solenoid valves VUVS/valve manifold VTUS


Technical data – Manifold block, size 30

**FESTO**

## Dimensions

Manifold block for 3/2-way valves, compact

Download CAD data → [www.festo.com](http://www.festo.com)




Type	B4	B7	B8	B9	B11	B14	B15	B22	B23
VABM-B10-30S-G12-...-P3	83	80	69.4	36	19	17	38	7	8
Type	D1 Ø	D2	H3	H4	H6	L3	L4	L5	L9
VABM-B10-30S-G12-...-P3	6.3	M5x11	42.5	17.5	26	7.5	38	32	12
Valve positions	2	3	4	5	6	7	8	9	10
L1	100	132	164	196	228	260	292	324	356
L2	85	117	149	181	213	245	277	309	341

## Dimensions

Manifold block for 5/2- and 5/3-way valves, compact

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B4	B7	B8	B9	B10	B11	B14	B15	B22	B23
VABM-B10-30S-G12-...	94	77	80.4	47	13.6	19	28	38	6.5	10
Type	D1 Ø	D2	H3	H4	H6	L3	L4	L5	L9	
VABM-B10-30S-G12-...	6.3	M5x11	42.5	17.5	26	7.5	34	32	12	
Valve positions	2	3	4	5	6	7	8	9	10	
L1	100	132	164	196	228	260	292	324	356	
L2	85	117	149	181	213	245	277	309	341	

# Solenoid valves VUVS/valve manifold VTUS


FESTO

Technical data – Manifold block, size 30

## Dimensions

Common supply manifold for mounting on both sides

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B17	B18	B19	B20	B21	D1 Ø	D2	D3 Ø
VABM-B10-30-G34-...-P53	34	85	65	35	33.5	13	5.5	M5x11	8.6

Type	H3	H12	H16	L3	L4	L5	L7	L9	W1
VABM-B10-30-G34-...-P53	65	2.5	19.5	9	34	32	26	10	30°

Valve positions	2	3	4	5	6	7	8	9	10
L1	100	132	164	196	228	260	292	324	356
L2	134	166	198	230	262	294	326	358	390
L8	152	184	216	248	280	312	344	376	408

# Solenoid valves VUVS/valve manifold VTUS


Technical data – Manifold block, size 30

**FESTO**

## Dimensions

Common supply manifold, mounting on one side

Download CAD data ➔ [www.festo.com](http://www.festo.com)



Type	B4	B17	B18	B19	B21	D1 Ø	D2	D3Ø
VABM-B10-30-G34-...-P53-E	34	85	65	35	13	5.5	M5x11	8.6

Type	H3	H13	H14	L4	L5	L7	L9	W1
VABM-B10-30-G34-...-P53-E	65	146	128	34	32	74	10	30°





Valve positions	2	3	4
L1	100	132	164
L8	168	200	232

# Solenoid valves VUVS/valve manifold VTUS

FESTO

Ordering data – Manifold block, size 30

## Ordering data – Manifold block

	Description	Valve positions	Part no.	Type
Standard manifold block				
	For 3/2-way valves, incl. seals and screws for mounting valves  - Note • Blanking plugs for sealing the supply ports (1, 3 and 14) at one end are included in the scope of delivery. • Standard manifold block is not licensed for VUVS-LK solenoid valves!	2 3 4 5 6 7 8 9 10	8026395 8026396 8026397 8026398 8026399 8026400 8026401 8026402 8026403	VABM-B10-30E-G34-2-P3 VABM-B10-30E-G34-3-P3 VABM-B10-30E-G34-4-P3 VABM-B10-30E-G34-5-P3 VABM-B10-30E-G34-6-P3 VABM-B10-30E-G34-7-P3 VABM-B10-30E-G34-8-P3 VABM-B10-30E-G34-9-P3 VABM-B10-30E-G34-10-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly  - Note • Blanking plugs for sealing the supply ports (1, 3, 5, 12 and 14) at one end are included in the scope of delivery. • Standard manifold block is not licensed for VUVS-LK solenoid valves!	2 3 4 5 6 7 8 9 10	8026359 8026360 8026361 8026362 8026363 8026364 8026365 8026366 8026367	VABM-B10-30E-G34-2 VABM-B10-30E-G34-3 VABM-B10-30E-G34-4 VABM-B10-30E-G34-5 VABM-B10-30E-G34-6 VABM-B10-30E-G34-7 VABM-B10-30E-G34-8 VABM-B10-30E-G34-9 VABM-B10-30E-G34-10
Extension module for standard manifold block				
	For 3/2-way valves, incl. seals and screws for mounting valves	2	8026432	VABM-B10-30EEE-G34-2-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly	2	8026431	VABM-B10-30EEE-G34-2
Compact manifold block				
	For 3/2-way valves, incl. seals and screws for mounting valves  - Note Blanking plugs for sealing the supply ports (1, 3 and 14) at one end are included in the scope of delivery.	2 3 4 5 6 7 8 9 10	8026413 8026414 8026415 8026416 8026417 8026418 8026419 8026420 8026421	VABM-B10-30S-G12-2-P3 VABM-B10-30S-G12-3-P3 VABM-B10-30S-G12-4-P3 VABM-B10-30S-G12-5-P3 VABM-B10-30S-G12-6-P3 VABM-B10-30S-G12-7-P3 VABM-B10-30S-G12-8-P3 VABM-B10-30S-G12-9-P3 VABM-B10-30S-G12-10-P3
	For 5/2 and 5/3-way valves, incl. seals and screws for valve assembly  - Note Blanking plugs for sealing the supply ports (1, 3, 5, 12 and 14) at one end are included in the scope of delivery.	2 3 4 5 6 7 8 9 10	8026377 8026378 8026379 8026380 8026381 8026382 8026383 8026384 8026385	VABM-B10-30S-G12-2 VABM-B10-30S-G12-3 VABM-B10-30S-G12-4 VABM-B10-30S-G12-5 VABM-B10-30S-G12-6 VABM-B10-30S-G12-7 VABM-B10-30S-G12-8 VABM-B10-30S-G12-9 VABM-B10-30S-G12-10



Festo core product range

★ Generally ready for shipping ex works in 24 hours

★ Generally ready for shipping ex works in 5 days

## Solenoid valves VUVS/valve manifold VTUS

Ordering data – Manifold block, size 30

Ordering data		Description	Valve positions	Part no.	Type
<b>Supply manifold</b>					
	For mounting on both sides, incl. seals and screws for valve assembly	2 3 4 5 6 7 8 9 10	<b>★ 8026338</b> <b>8026339</b> <b>★ 8026340</b> <b>8026341</b> <b>★ 8026342</b> <b>8026343</b> <b>★ 8026344</b> <b>8026345</b> <b>★ 8026346</b>	<b>VABM-B10-30-G34-2-P53</b> <b>VABM-B10-30-G34-3-P53</b> <b>VABM-B10-30-G34-4-P53</b> <b>VABM-B10-30-G34-5-P5</b> <b>VABM-B10-30-G34-6-P53</b> <b>VABM-B10-30-G34-7-P53</b> <b>VABM-B10-30-G34-8-P53</b> <b>VABM-B10-30-G34-9-P53</b> <b>VABM-B10-30-G34-10-P53</b>	
	For mounting on one side, incl. seals and screws for valve mounting	2 3 4	<b>8026356</b> <b>8026357</b> <b>8026358</b>	<b>VABM-B10-30-G34-2-P53-E</b> <b>VABM-B10-30-G34-3-P53-E</b> <b>VABM-B10-30-G34-4-P53-E</b>	







### Note

Blanking plug for sealing the supply port (1) at one end included in the scope of delivery.

## Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Ordering data – Manifold block, size 30

Ordering data		Description	Weight [g]	Part no.	Type
<b>Cover plate</b>					
	For valve position on manifold block for 3/2-way valves	128		<b>8026336</b>	<b>VABB-B10-30-E-P3</b>
	For valve position on manifold block for 5/2-, 5/3-way valves	179		<b>8026335</b>	<b>VABB-B10-30-E</b>
	For valve position on common supply manifold	43		<b>8026334</b>	<b>VABB-B10-30-A</b>
<b>Supply plate</b>					
	For valve position on manifold block for 3/2-way valves	121		<b>8026435</b>	<b>VABF-B10-30-P1A4-G38-P3</b>
	For valve position on manifold block for 5/2-, 5/3-way valves	167		<b>8026434</b>	<b>VABF-B10-30-P1A4-G38</b>
<b>Supply plate</b>					
	For valve position on common supply manifold	40		<b>8026433</b>	<b>VABF-B10-30-P1-G38</b>

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ☆ Generally ready for shipping ex works in 5 days

# Solenoid valves VUVS/valve manifold VTUS

Ordering data – Manifold block, size 30

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Push-in fitting with internal hex</b>					
	Connecting thread G1/8 for tubing O.D.	4 mm	★ 186106	QS-G1/8-4-I	10
			133008	QS-G1/8-4-I-100	100
	Connecting thread G3/8 for tubing O.D.	6 mm	★ 186107	QS-G1/8-6-I	10
			133009	QS-G1/8-6-I-100	100
	Connecting thread G1/2 for tubing O.D.	8 mm	★ 186111	QS-G3/8-8-I	10
			186113	QS-G3/8-10-I	10
			186114	QS-G3/8-12-I	10
	Connecting thread G1/2 for tubing O.D.	12 mm	★ 186115	QS-G1/2-12-I	1
<b>Push-in fitting with external hex</b>					
	Connecting thread G1/2 for tubing O.D.	16 mm	★ 186105	QS-G1/2-16	1
			132047	QS-G1/2-16-20	20
<b>Angled push-in fitting with external hex</b>					
	Connecting thread G3/8 for tubing O.D.	8 mm	★ 186121	QSL-G3/8-8	10
			132055	QSL-G3/8-8-50	50
		10 mm	★ 186123	QSL-G3/8-10	10
			132056	QSL-G3/8-10-20	20
		12 mm	★ 186124	QSL-G3/8-12	10
			132057	QSL-G3/8-12-20	20
	Connecting thread G1/2 for tubing O.D.		★ 186125	QSL-G1/2-12	1
	12 mm	132058	QSL-G1/2-12-20	20	
		★ 186126	QSL-G1/2-16	1	
	16 mm	132059	QSL-G1/2-16-20	20	
<b>Angled push-in fitting, long, with external hex</b>					
	Connecting thread G1/2 for tubing O.D.	8 mm	186132	QSLL-G3/8-8	10
		10 mm	186134	QSLL-G3/8-10	10
		12 mm	186135	QSLL-G3/8-12	10
<b>Barbed fitting with external hex</b>					
	Connecting thread G3/4 for tubing I.D. Aluminium design	13 mm	3612	N-3/4-P-13	1
		19 mm	3613	N-3/4-P-19	1
	Connecting thread G3/4 for tubing I.D. Brass design	13 mm	15637	N-3/4-P-13-MS	1
		19 mm	15638	N-3/4-P-19-MS	1

1) Packaging unit quantity

# Solenoid valves VUVS/valve manifold VTUS

**FESTO**

Ordering data – Manifold block, size 30

Ordering data		Description	Part no.	Type	PE <sup>1)</sup>
<b>Silencer</b>					
	With connecting thread G, polymer design	G3/8	<b>534224</b>	<b>U-3/8-20</b>	<b>20</b>
	With connecting thread G, metal design	G1/2	<b>★ 6844</b>	<b>U-1/2-B</b>	<b>1</b>
		G3/4	<b>6845</b>	<b>U-3/4-B</b>	<b>1</b>
		G3/8	<b>★ 6843</b>	<b>U-3/8-B</b>	<b>1</b>
	With connecting thread G, sinter design, long	G1/2	<b>★ 1205863</b>	<b>AMTE-M-LH-G12</b>	<b>10</b>
		G3/4	<b>1205864</b>	<b>AMTE-M-LH-G34</b>	<b>10</b>
<b>Blanking plug</b>					
	With connecting thread	G1/8	<b>★ 3568</b>	<b>B-1/8</b>	<b>10</b>
			<b>534213</b>	<b>B-1/8-100</b>	<b>100</b>
		G1/2	<b>★ 3571</b>	<b>B-1/2</b>	<b>10</b>
			<b>534216</b>	<b>B-1/2-20</b>	<b>20</b>
		G3/4	<b>★ 3572</b>	<b>B-3/4</b>	<b>10</b>
<b>Separator</b>					
	For creating pressure zones	G1/8	<b>569995</b>	<b>VABD-8-B</b>	<b>1</b>
		G1/2	<b>8022483</b>	<b>VABD-17.5-B</b>	<b>1</b>
		G3/4	<b>8022484</b>	<b>VABD-22.7-B</b>	<b>1</b>
<b>H-rail mounting</b>					
	For size 30, for mounting on standard H-rails TH 35-7.5 or TH 35-15 to EN 60715		<b>3488412</b>	<b>VAME-T-M6</b>	<b>2</b>

1) Packaging unit quantity

Festo core product range

 Generally ready for shipping ex works in 24 hours

 Generally ready for shipping ex works in 5 days