

SAFETY POS. SWITCH W. SEPARATE ACTUATOR, 5 DIRECT.OF APPROACH MOLDED-PLASTIC ENCLOSURE, ACC. TO EN50047, ASISAFE INTEGRATED AS-I STATUS:1:F-IN1 , 2:F-IN2 3:AS-I/FAULT SLOW-ACTION CONTACTS 2NC, W/ M12 CONNECTOR 4-POLE CHANNEL 1 ON NC,CHANNEL 2 ON NC

Product designation		position switch with separate actuator with ASIsafe
Manufacturer article number		
<ul style="list-style-type: none"> of the optional actuators 		3SE5000-0AV01 standard actuator, 3SE5000-0AV02 actuator with vertical fixing, 3SE5000-0AV03 actuator with transverse fixing, 3SE5000-0AV04 radius actuator left, 3SE5000-0AV05 universal actuator, 3SE5000-0AV06 radius actuator right

General technical data:		
Product function		
<ul style="list-style-type: none"> positive opening 		Yes
Insulation voltage		
<ul style="list-style-type: none"> Rated value 	V	30
Degree of pollution		class 3
Shock resistance		30g / 11 ms
Vibration resistance		0.35 mm / 5g
Surge voltage resistance Rated value	kV	0.8
Mechanical service life (switching cycles)		
<ul style="list-style-type: none"> typical 		1 000 000
Material of the enclosure of the switch head		plastic enclosure
Protection class IP		IP65
Equipment marking		
<ul style="list-style-type: none"> acc. to DIN EN 61346-2 acc. to DIN EN 81346-2 		B B
Active principle		mechanical
Repeat accuracy	mm	0.1
Minimum actuating force in activation direction	N	20

Enclosure:		
Design of the housing		block, narrow
Material of the enclosure		plastic
Design of the housing acc. to standard		Yes

Drive Head:		
Design of the operating mechanism		5 directions of approach
Design of the switching function		positive opening

Connections/ Terminals:		
Type of electrical connection		M12 plug, fixed, 4-pole

Mechanical data:		
Design of plug-in connection		M12 plug, 4-pole: Pin 1 = ASI+ , Pin 2 = not assigned, Pin 3= ASI-, Pin 4 = not assigned

Ambient conditions:		
Ambient temperature		
<ul style="list-style-type: none"> during operation 	°C	-25 ... +60
<ul style="list-style-type: none"> during storage 	°C	-40 ... +80

Supply voltage:		
Type of voltage of the supply voltage		
<ul style="list-style-type: none"> of the optional LED indicator 		DC
Supply voltage		
<ul style="list-style-type: none"> of LED 	V	24

Installation/ mounting/ dimensions:		
mounting position		any
Mounting type		screw fixing

Certificates/ approvals:		
General Product Approval	Declaration of Conformity	Test Certificates



[Special Test Certificate](#)

UL

EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)



<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SF12341QV401BA1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SF12341QV401BA1/all>



last modified:

09.03.2015