

TINA-Y-SS

~16° smooth spot beam. Assembly with holder, installation tape and pins.

SPECIFICATION:

Dimensions Ø 16.1 mm Height 10 mm Fastening tape, pin yes 🕕 **ROHS** compliant



MATERIALS:

Component	Type	Material	Colour	Finish
TINA-Y-SS	Single lens	PMMA	clear	gloss
TINA-Y-HLD	Holder	PC	black	gloss
TINA-Y-TAPE	Tape	Acrylic foam		


ORDERING INFORMATION:

» Box size: 476 x 273 x 197 mm

Component	Qty in box	MOQ	MPQ	Box weight (kg)
CA18103_TINA-Y-SS	3900	300	300	5.7




PRODUCT DATASHEET CA18103_TINA-Y-SS




See also our general installation guide: www.ledil.com/installation_guide



OPTICAL RESULTS (MEASURED):












LED XHP35.2 HI $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 22.0° / 46.0° Efficiency 83 % Peak intensity 3.8 cd/lm LEDs/each optic Light colour White


Required components:



CREE - LED

LED XHP50.3 HI FWHM / FWTM 24.0° / 48.0° Efficiency 82 % Peak intensity 3.4 cd/lm LEDs/each optic 1 White Light colour

Required components:




CREE + LED

LED XM-L RGBW (XMLDCL HD)

FWHM / FWTM 30.0° / 50.0° Efficiency 85 % Peak intensity 2.7 cd/lm LEDs/each optic Light colour **RGBW**

Required components:




CREE & LED

XM-L RGBW (XMLDCL HI)

FWHM / FWTM 20.0° / 38.0° Efficiency 85 % Peak intensity 5.3 cd/lm LEDs/each optic **RGBW** Light colour

Required components:








LED XM-L3 FWHM / FWTM 21.0° / 42.0° Efficiency 80 % Peak intensity 4 cd/lm LEDs/each optic Light colour White


Required components:



CREE - LED

LED XP-E2 FWHM / FWTM 12.0° / 24.0° Efficiency 88 % Peak intensity 13 cd/lm LEDs/each optic 1 White Light colour


Required components:



CREE \$\(\preceq\) LED

LED XP-G2 FWHM / FWTM 15.0° / 28.0° Efficiency 87 % Peak intensity 9 cd/lm LEDs/each optic Light colour White


Required components:



CREE - LED

XP-P FWHM / FWTM 12.0° / 22.0° Efficiency 89 % Peak intensity 15.1 cd/lm LEDs/each optic White Light colour

Required components:








LED XQ-E HD $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 12.0° / 24.0° Efficiency 87 %

Peak intensity 12.7 cd/lm LEDs/each optic

Light colour White Required components:




CREE - LED

LED XQ-E HI FWHM / FWTM 12.0° / 22.0° Efficiency 87 %

Peak intensity 15.2 cd/lm LEDs/each optic 1 White Light colour

Required components:




LUMILEDS

LED LUXEON 5050 Round LES

FWHM / FWTM 28.0° / 56.0° Efficiency 80 % Peak intensity 2.4 cd/lm LEDs/each optic 1 Light colour White


Required components:



MUMILEDS

LED LUXEON 5050 Square LES

FWHM / FWTM 26.0° / 56.0° Efficiency 78 % Peak intensity 2.5 cd/lm LEDs/each optic White Light colour Required components:






White



LED LUXEON C $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 14.0° / 26.0° Efficiency 79 % Peak intensity 10.8 cd/lm LEDs/each optic


Light colour Required components:



LUMILEDS


LED LUXEON MZ FWHM / FWTM 24.0° / 47.0° Efficiency 81 % Peak intensity 3.4 cd/lm LEDs/each optic 1 White Light colour

Required components:




LUMILEDS

LUXEON TX LED FWHM / FWTM 15.0° / 30.0° Efficiency 84 % Peak intensity 8 cd/lm LEDs/each optic 1 Light colour White Required components:



WNICHIA


LED NV4WB35AM FWHM / FWTM 24.0° / 46.0° Efficiency 85 % Peak intensity 3.7 cd/lm LEDs/each optic White Light colour Required components:








LED NVSW219F $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 18.0° / 33.0° Efficiency 87 % Peak intensity 6.6 cd/lm LEDs/each optic Light colour White



WNICHIA

Required components:


LED NVSxE21A FWHM / FWTM 16.0° / 34.0° Efficiency 79 % Peak intensity 7 cd/lm LEDs/each optic 1 White Light colour Required components:



OSRAM Opto Semiconductor

OSLON Square CSSRM2/CSSRM3 LED


FWHM / FWTM 16.0° / 32.0° Efficiency 86 % Peak intensity 7.5 cd/lm LEDs/each optic 1 Light colour White Required components:



OSRAM

LED OSLON SSL 150 FWHM / FWTM 13.0° / 25.0° Efficiency 88 %

Peak intensity 13 cd/lm LEDs/each optic White Light colour Required components:






SAMSUNG

LED LH351C
FWHM / FWTM 19.0° / 36.0°
Efficiency 87 %
Peak intensity 5.9 cd/lm
LEDs/each optic 1
Light colour White

Required components:





PRODUCT DATASHEET CA18103_TINA-Y-SS

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy