

### Product type designation

Product description

### PROFIBUS PCF Fiber Optic standard cable

PCF fiber-optic cable with plastic cladding, preferred length, preassembled

SIMATIC NET, PROFIBUS PCF FIBER OPTIC, WITH 4 PCF BFOC CONNECTORS L = 75 M



Suitability for use	Cable for indoor applications
Version of the assembled FO cable	Assembled with four BFOC connectors
Cable designation	I-V(ZN)Y 2K 200/230
Cable length	75 m

### Optical data

Damping ratio per length	
<ul style="list-style-type: none"> <li>• at 650 nm / maximum</li> <li>• at 660 nm / maximum</li> </ul>	10 dB/km
Bandwidth length product	
<ul style="list-style-type: none"> <li>• at 650 nm</li> </ul>	17 GHz·m

### Mechanical data

Number of fibers / per FOC core	1
Number of FO cores / per FOC cable	2
Version of the FO conductor fiber	Step index fiber 200/230 µm
Outer diameter	
<ul style="list-style-type: none"> <li>• of the optical fibers</li> <li>• of the optical fiber sheath</li> <li>• of the FOC core sheath</li> </ul>	200 µm 230 µm 2.2 mm
Symmetrical deviation / of the outer diameter of the FOC core sheath	0.1 mm
Outer diameter / of the cable	4.7 mm
Material	

<ul style="list-style-type: none"> <li>• of the fiber-optic cable core</li> <li>• of the optical fiber sheath</li> <li>• of the FOC core sheath</li> <li>• of the fiber-optic cable sheath</li> <li>• of the strain relief</li> </ul>	Quartz glass fluoridated special polymer PVC PVC Kevlar fibers
Color	
<ul style="list-style-type: none"> <li>• of the FOC core sheath</li> <li>• of cable sheath</li> </ul>	Orange/black Violet
Bending radius	
<ul style="list-style-type: none"> <li>• with single bend / minimum permissible</li> <li>• with multiple bends / minimum permissible</li> </ul>	47 mm 70 mm
Tensile load / during operation / maximum	200 N
Short-term shear force per length	100 N/cm
Weight per length	22 kg/km

#### Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> <li>• during installation</li> </ul>	-30 ... +70 °C -30 ... +70 °C -30 ... +70 °C -5 ... +50 °C
Burning behavior	Flame-resistant acc. to IEC 60332-1-2
Chemical resistance	
<ul style="list-style-type: none"> <li>• to mineral oil</li> <li>• to grease</li> </ul>	Conditional resistance Conditional resistance
Radiological resistance / to UV radiation	Not resistant
Protection class IP	IP20

#### Product properties, functions, components / general

Product property	
<ul style="list-style-type: none"> <li>• halogen-free</li> <li>• silicon-free</li> </ul>	No Yes
Product component / Rodent protection	No
Cable length	
<ul style="list-style-type: none"> <li>• for PCF FOC / with PROFIBUS / maximum</li> </ul>	400 m

#### Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> <li>• RoHS conformity</li> </ul>	Yes

#### Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> <li>• to website: Selector SIMATIC NET SELECTION TOOL</li> <li>• to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

**last modified:**

16.03.2015