

BUILT-IN LUMINAIRE STEADY BURNING LIGHT, 12 - 230V UC, RED



Figure similar

### General technical data:

<b>Product designation</b>		blinklight lamp
<b>Type of voltage</b>		AC/DC
<ul style="list-style-type: none"> <li>• of the operating voltage</li> </ul>		
<b>Operating voltage</b>		
<ul style="list-style-type: none"> <li>• for DC Rated value</li> </ul>	V	12 ... 240
<ul style="list-style-type: none"> <li>• with AC at 50 Hz Rated value</li> </ul>	V	12 ... 240
<ul style="list-style-type: none"> <li>• with AC at 60 Hz Rated value</li> </ul>	V	12 ... 240
<b>Active power consumption</b>	W	5

### Mechanical data:

<b>Product component Light source</b>		No
<b>Mounting type</b>		Bayonet
<b>Outer diameter of the signal column element</b>	mm	75

### Lamp:

<b>Mounting type</b>		BA 15d
<b>Design of the optical signal</b>		continous light
<b>Type of light source</b>		filament lamp / LED

### Ambient conditions:

<b>Ambient temperature during operation</b>	°C	-20 ... +60
<b>Protection class IP</b>		IP65
<b>Depth</b>	mm	31
<b>Height</b>	mm	66
<b>Width</b>	mm	75

Certificates/ approvals:

General Product Approval

EMC

Declaration of Conformity



Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=8WD53001AB>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8WD53001AB>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=8WD53001AB&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=8WD53001AB&lang=en)



SIEMENS

last modified:

15.01.2015