

EU Type Examination Certificate

This is to certify that:

JSP Limited
Worsham Mill
Minster Lovell
Witney, Oxford
OX29 0TA
United Kingdom

Holds Certificate Number:

CE 676976

In respect of:

Industrial Safety Helmets to EN 397:2012 + A1:2012 Plus Additional Assessments to EN 50365:2002

on the basis that BSI carried out the relevant Type Examination procedures under the requirements with the Regulation (EU) 2016/425 of the European Parliament and Council relating to Personal Protective Equipment Regulation (PPE) Annex V (Module B) and meets the relevant health and safety requirements specified in Annex II

For and on behalf of BSI, a Notified
Body for the above Regulation
(Notified Body Number 2797):



Denelise L'Ecluse, Managing Director Assurance - Continental
Europe

First Issued: 2017-06-29

Latest Issue: 2023-01-05

Effective Date: 2023-01-05

Expiry Date: 2028-04-20



Page: 1 of 12

EU Type Examination Certificate

No. CE 676976

Product Details:

Product type: Industrial safety helmets.

Models: See below.

Technical Specifications: Harmonized European Standard EN 397:2012+A1:2012
Harmonized European Standard EN 50365:2002
JSP Technical Specification TS 03:02-18

Classifications: See Model Specific Details.

Product Assessments

The product assessments for the helmets were based on the requirements of the following Technical Specifications:
BS EN 397:2012+A1:2012, the English language version of EN 397:2012+A1:2012,
BS EN 50365:2002, the English language version of EN 50365:2002, electrically insulating helmets for use on low voltage installations and JSP Technical Specification for Industrial Safety Helmets.
The JSP Technical Specification TS 03:02-18 details a very low temperature shock absorption and penetration performance option, the requirements are as detailed in EN 397:2012+A1:2012 but at the lower temperature of -40°C. This option is indicated by the symbol -40°C.

Products certified to EN 397:2012+A1:2012 and EN 50365:2002:

Invincible® EVO®2/Mk 2 EVO®	Invincible® EVO®3/Mk 3 EVO®	Invincible® EVO® 6100 FB
Invincible® EVO® Force 9/EVO®4	Invincible® EVO® Force 9+/EVO®5	Invincible® EVOLITE®
EVO®5 E-Xtra™	Mk® 7.0	

Products certified to EN 397:2012+A1:2012:

Invincible® Mk®2	Invincible® Mk®3	Invincible® Mk®7 Hi-Temp 150
------------------	------------------	------------------------------

First Issued: 2017-06-29
Latest Issue: 2023-01-05

Effective Date: 2023-01-05
Expiry Date: 2028-04-20

Page: 2 of 12

This certificate has been issued by and remains the property of BSI Group The Netherlands B.V., John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands and should be returned immediately upon request.
To check its validity telephone +31 20 3460780. An electronic certificate can be authenticated [online](#).

BSI Group The Netherlands B.V., registered in the Netherlands under number 33264284, at John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands
A member of BSI Group of Companies.

EU Type Examination Certificate

No. CE 676976

Performance options

The following performance options are applicable to some models within the product range, see Model Specific Details section.

Options/Attributes

- BS EN 397 - Very low temperature shock absorption and penetration performance
- BS EN 397 - Very high temperature
- BS EN 397 - Electrical insulation properties
- BS EN 397 - Molten metal splash
- BS EN 397 - Lateral deformation
- JSP TS - Very low temperature shock absorption and penetration performance

BS EN 50365:2002, electrically insulating helmets for use on low voltage installations.

Product Marking Symbol

- 20°C or -30°C
- +150°C
- 440V a.c.
- MM
- LD
- 40°C (encompasses the -20°C and -30°C options of EN 397).
- Class 0 and Double Triangle

First Issued: 2017-06-29
Latest Issue: 2023-01-05

Effective Date: 2023-01-05
Expiry Date: 2028-04-20

EU Type Examination Certificate

No. CE 676976

Model Specific Details:

Products Certified to EN 397:2012+A1:2012, and EN 50365:2002:

Model:	Invincible® EVO® 2/Mk2 EVO®
Size range:	53 – 64cm.
Shell material:	High Density Polyethylene.
Shell options:	Vented or non-vented shell, each type with micro (short) or mid (standard) length peak.
Headband/nape strap:	Low and High Density Polyethylene options.
Cradle:	6 point system with Low Density Polyethylene Star.
Headband adjustment system:	Slip Ratchet type.
EN 397 options:	-30°C, 440 V a.c. (1) and MM.
EN 50365 classification:	Class 0 (1).
Additional items:	Fabric sweatband 2 and 4 point chinstrap system.

(1) Vented shell variants do not have the EN 397 electrical insulation properties or the EN 50365 options.

First Issued: 2017-06-29
Latest Issue: 2023-01-05

Effective Date: 2023-01-05
Expiry Date: 2028-04-20

EU Type Examination Certificate

No. CE 676976

Products Certified to EN 397:2012+A1:2012 and EN 50365:2002 (continued):

Model:	Invincible® EVO®3/Mk3 EVO®
Size range:	53 – 64cm.
Shell material:	High Density Polyethylene.
Shell options:	Vented or non-vented shell, each type with micro (short) or mid (standard) length peak.
Headband/nape strap:	Low and High Density Polyethylene options.
Cradle:	6 point textile tapes system.
Headband adjustment system:	Slip Ratchet or Wheel Ratchet type.
EN 397 options:	-30°C, 440 V a.c. (1) and MM.
EN 50365 classification:	Class 0 (1).
JSP TS option:	-40°C.
Additional items:	Fabric sweatband. 2 and 4 point chinstrap system.

(1) Vented shell variants do not have the EN 397 electrical insulation properties or the EN 50365 options.

Model:	Invincible® EVO® 6100FB
Size range:	53 – 64cm.
Shell material:	High Density Polyethylene.
Shell options:	Vented or non-vented shell, full brim.
Headband/nape strap:	Low and High Density Polyethylene options.
Cradle:	6 point textile tapes system.
Headband adjustment system:	Slip Ratchet and Wheel Ratchet type.
EN 397 options:	-30°C, 440V a.c. (1) and MM.
EN 50365 classification:	Class 0 (1).
JSP TS option:	-40°C.
Additional items:	Fabric sweatband. 2 and 4 point chinstrap systems. Requirements of the Technical Specifications are met with the harness orientated within the shell in either of two positions as selected by the end user enabling the helmet to be worn 'back to front' if required.

(1) Vented shell variants do not have the EN 397 electrical insulation properties or the EN 50365 options.

First Issued: 2017-06-29

Effective Date: 2023-01-05

Latest Issue: 2023-01-05

Expiry Date: 2028-04-20

Page: 5 of 12

This certificate has been issued by and remains the property of BSI Group The Netherlands B.V., John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands and should be returned immediately upon request.
To check its validity telephone +31 20 3460780. An electronic certificate can be authenticated [online](#).

BSI Group The Netherlands B.V., registered in the Netherlands under number 33264284, at John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands
A member of BSI Group of Companies.

EU Type Examination Certificate

No. CE 676976

Products Certified to EN 397:2012+A1:2012 and EN 50365:2002 (continued):

Model:	Invincible® EVO® Force 9 and name only variant Invincible® EVO®4
Size range:	53 – 64cm.
Shell material:	Acrylonitrile Butadiene Styrene.
Shell options:	Vented or non-vented shell, each type with micro (short) or mid (standard) length peak.
Headband/nape strap:	Low and High Density Polyethylene options.
Cradle:	6 point system with Low Density Polyethylene Star.
Headband adjustment system:	Slip Ratchet type.
EN 397 options:	-30°C, 440V a.c. (1), MM and LD.
JSP TS option:	-40°C.
EN 50365 classification:	Class 0 (1).
Additional items:	Fabric sweatband. 2 and 4 point chinstrap system.

Model:	Invincible® EVO® Force 9+ and name only variant Invincible® EVO®5
Size range:	53 – 64cm.
Shell material:	Acrylonitrile Butadiene Styrene.
Shell options:	Vented or non-vented shell, each type with micro (short) or mid (standard) length peak.
Headband/nape strap:	Low and High Density Polyethylene options.
Cradle:	6 point textile tapes system.
Headband adjustment system:	Slip Ratchet or Wheel Ratchet type.
EN 397 options:	-30°C, 440V a.c. (1), MM and LD.
JSP TS option:	-40°C.
EN 50365 classification:	Class 0 (1).
Additional items:	Fabric sweatband. 2 and 4 point chinstrap system.

(1) Vented shell variants do not have the EN 397 electrical insulation properties or the EN 50365 options.

First Issued: 2017-06-29

Latest Issue: 2023-01-05

Effective Date: 2023-01-05

Expiry Date: 2028-04-20

Page: 6 of 12

This certificate has been issued by and remains the property of BSI Group The Netherlands B.V., John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands and should be returned immediately upon request.
To check its validity telephone +31 20 3460780. An electronic certificate can be authenticated [online](#).

BSI Group The Netherlands B.V., registered in the Netherlands under number 33264284, at John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands
A member of BSI Group of Companies.

EU Type Examination Certificate

No. CE 676976

Products Certified to EN 397:2012+A1:2012 and EN 50365:2002 (continued):

Model:	Invincible® EVOLITE®
Size range:	53 – 64cm.
Shell material:	Acrylonitrile Butadiene Styrene.
Shell options:	Vented or non-vented shell, each type with micro (short) or mid (standard) length peak.
Headband/nape strap:	Low and High Density Polyethylene options.
Cradle:	6 point textile tapes system.
Headband adjustment system:	Slip Ratchet or Wheel Ratchet type.
EN 397 options:	-30°C, LD, 440V a.c. (1) and MM.
EN 50365 classification:	Class 0 (1).
JSP TS option:	-40°C.
Additional items:	Fabric sweatband. 2 and 4 point chinstrap system.

(1) Vented shell variants do not have the EN 397 electrical insulation properties or the EN 50365 options.

Model:	EVO®5 E-Xtra™
Size range:	53 – 64cm.
Shell material:	Acrylonitrile Butadiene Styrene with EPP flame retardent liner.
Shell options:	Vented or non-vented shell, each type with micro (short) or mid (standard) length peak.
Headband/nape strap:	High Density Polyethylene.
Cradle:	6 point textile tapes system.
Headband adjustment system:	HDPE Wheel Ratchet type.
EN 397 options:	-30°C, LD, 440V a.c. and MM.
EN 50365 classification:	Class 0.
JSP TS option:	-40°C.
Additional items:	Fabric sweatband.

First Issued: 2017-06-29

Latest Issue: 2023-01-05

Effective Date: 2023-01-05

Expiry Date: 2028-04-20

Page: 7 of 12

This certificate has been issued by and remains the property of BSI Group The Netherlands B.V., John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands and should be returned immediately upon request.
To check its validity telephone +31 20 3460780. An electronic certificate can be authenticated [online](#).

EU Type Examination Certificate

No. CE 676976

Products Certified to EN 397:2012+A1:2012 and EN 50365:2002 (continued):

Model:	Mk® 7.0
Size range:	53 – 64cm.
Shell material:	High Density Polyethylene.
Shell options:	Vented (small or large) or non-vented shell, each type with micro (short) or mid (standard) length peak.
Headband/nape strap:	Low Density Polyethylene.
Cradle:	6 point webbing system.
Headband adjustment system:	Wheel Ratchet type.
EN 397 options:	-30°C, 440V a.c. (1) and MM.
EN 50365 classification:	Class 0 (2).
JSP TS option:	-40°C.
Additional items:	Fabric sweatband. 2 and 4 point chinstrap system.

- (1) Small vented shell variant do not have the EN 397 electrical insulation properties.
- (2) Large vented shell variant do not have the EN 397 electrical insulation properties or the EN 50365 options.

First Issued: 2017-06-29
Latest Issue: 2023-01-05

Effective Date: 2023-01-05
Expiry Date: 2028-04-20

EU Type Examination Certificate

No. CE 676976

Products Certified to EN 397:2012+A1:2012:

Model:	Invincible® Mk®2
Size range:	53 – 61cm.
Shell material:	High Density Polyethylene.
Shell options:	Short or standard length peak.
Headband/nape strap:	Low Density Polyethylene.
Cradle:	6 point system with Low Density Polyethylene Star.
Headband adjustment system.	Slip Ratchet type.
EN 397 options:	-20°C and 440V a.c.
Additional configuration:	End user assembled version available.

Model:	Invincible® Mk®2 Linesman
Size range:	53 – 61cm.
Shell material:	High density polyethylene.
Shell option:	Short length peak.
Headband/nape strap:	Low density polyethylene.
Cradle:	6 point system with Low Density Polyethylene Star.
Headband adjustment system:	Slip Ratchet type.
Auxiliary retention system:	Tubular nylon chinstrap/nape strap with acetal buckle and nylon adjuster.
EN 397 options:	-20°C and 440V a.c.
Additional configuration:	End user assembled version available.

First Issued: 2017-06-29
Latest Issue: 2023-01-05

Effective Date: 2023-01-05
Expiry Date: 2028-04-20

Page: 9 of 12

This certificate has been issued by and remains the property of BSI Group The Netherlands B.V., John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands and should be returned immediately upon request.
To check its validity telephone +31 20 3460780. An electronic certificate can be authenticated [online](#).

BSI Group The Netherlands B.V., registered in the Netherlands under number 33264284, at John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands
A member of BSI Group of Companies.

EU Type Examination Certificate

No. CE 676976

Products Certified to EN 397:2012+A1:2012 (Continued):

Model: Invincible® Mk®3
Size range: 53 – 63cm.
Shell material: High Density Polyethylene.
Shell options: Short or standard length peak.
Headband/nape strap: Low Density Polyethylene.
Cradle: 6 point textile tapes system.
Headband adjustment system. Slip Ratchet or Wheel Ratchet type.
EN 397 options: -20°C and 440V a.c.

Model: Invincible® Mk®3 Linesman
Size range: 53 – 63cm.
Shell material: High Density Polyethylene.
Shell options: Short length peak.
Headband/nape strap: Low Density Polyethylene.
Cradle: 6 point textile tapes system.
Adjustment system. Slip Ratchet or Wheel Ratchet type.
Auxiliary retention system: Tubular nylon chinstrap/nape strap with acetal buckle and nylon adjuster.
EN 397 options: -20°C and 440V a.c.

First Issued: 2017-06-29
Latest Issue: 2023-01-05

Effective Date: 2023-01-05
Expiry Date: 2028-04-20

Page: 10 of 12

This certificate has been issued by and remains the property of BSI Group The Netherlands B.V., John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands and should be returned immediately upon request.
To check its validity telephone +31 20 3460780. An electronic certificate can be authenticated [online](#).

BSI Group The Netherlands B.V., registered in the Netherlands under number 33264284, at John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands
A member of BSI Group of Companies.

EU Type Examination Certificate

No. CE 676976

Products Certified to EN 397:2012+A1:2012 (continued):

Model:	Invincible® Mk®7 Hi-Temp 150
Size range:	53 – 63cm.
Shell options:	Vented or non-vented shell, each type with short or standard length peak.
Shell material:	Glass Fibre Re-enforced Polyamide.
Headband/napestrap:	Low Density Polyethylene.
Cradle:	6 point textile tapes system with high temperature webbing clips.
Headband adjustment system:	Slip Ratchet or Wheel Ratchet type.
EN 397 options:	-30°C, +150°C, LD, and MM.
JSP TS option:	-40°C.
Additional items:	Leatherette sweatband.

All Accessories & Replacements Parts associated with the helmet models are available on JSP's website.

First Issued: 2017-06-29
Latest Issue: 2023-01-05

Effective Date: 2023-01-05
Expiry Date: 2028-04-20

EU Type Examination Certificate

No. CE 676976

Certification Administration Details:

Technical File References: AJE160-000-000, AJA160-000-000, AHB010-000-100, AKJ240-000-100, AHN170-000-100

Certificate Amendment Record:

Issue date:	Comments:	BSI Internal Project No:
29 th June 2017	First Issue to the PPE Regulation 2016/425 EU. Product initially approved to Article 10 of the PPE Directive 89/686/EEC on BSI issued certificate CE 00279	0086:17:8764894
April 2018	Addition of Evolite® and Invincible® helmets.	0086:18:8849241
November 2019	Addition of Molten Metal claim to Invincible® Mk®7	2797:19:3050787
March 2020	Addition of EVO®5 E-Xtra™	2797:20:3123380
February 2021	Addition of MK® 7.0	2797:21:3166050
January 2023	Certificate issue - 5-year certificate renewal under PPE regulation (EU) 425/2016 - Invincible® MK 7 removed	2797:23:3756115

Certificate Validity

The Certificate holder is responsible for ensuring that the Notified Body is advised of changes to any aspect of the overall processes utilised in the manufacture of the product, failure to do so could invalidate the Certificate in respect of product manufactured following the introduction of such changes.

Monitoring of Manufactured PPE

The validity is also dependent upon the maintenance of the EU Conformity to Type Based on Quality Assurance of the Production Process, Annex VIII (Module D) as referenced on BSI issued certificate CE 690890.

First Issued: 2017-06-29
Latest Issue: 2023-01-05

Effective Date: 2023-01-05
Expiry Date: 2028-04-20